



Tel-Splice Connectors

- Economical and reliable
- Available in several configurations for different applications

Tel-Splice connectors provide an economical and reliable means of splicing telephone cable conductors.

Advantages

- Durable – Highly resistant to moisture and chemical attack; flame retardant models available.
- Economical – Lower applied cost; IDC (installation displacement connectors), gas tight connections, no prestripping required, means minimal operator preparation.
- Versatile – Available filled or unfilled; color coded for easy identification: 2-wire, 3-wire, half-tap, and Clear & Cap in loose piece or welded sticks.

Applications

- Load Coils
- Stub Cables
- Ready Access Terminals
- Trunk and Tool Cables

Technical Specifications

108-6021 all 2 wire, 3 wire, and 1/2 tap

versions, except Flame Retardant

108-6042 all Flame Retardant versions

108-6075 Clear & Cap

MSDS for filled product 125-6332

100/Box	500/Tub	1,000/Tub	Cartridge*		Welded Sticks		Description	Product Sealant ³	Housing Color	Contact Material ⁴	Max. OD (in - mm)
			56/Cart. ¹	72/Cart. ¹	20/Stick ²	15/Stick ²					
1-552795-2		552795-2		552966-2	1389031-2		2-Wire	F	Translucent ⁶	PBTP	0.080-2.03
1-552795-4		552795-4		552966-4	1389031-1			D	Yellow ⁵	PBTP	0.080-2.03
1-553395-1				552966-5				D	Clear F/R ⁶	PBTP	0.080-2.03
1-552678-2	552678-2		552965-2		1389032-2		3-Wire	F	Translucent ⁶	PBTP	0.080-2.03
1-552678-4	552678-4		552965-4		1389032-1			D	Yellow	PBTP	0.080-2.03
1-553759-1			406908-1		1389032-3			D	Clear F/R ⁶	PBTP	0.080-2.03
558050-1								F	Translucent UV	PBTP	0.080-2.03
1-552678-7								F	Red	PBTP	0.080-2.03
1-553017-2		553017-2		553744-2	1389030-2			F	Translucent Blue ⁵	PBTP	0.080-2.03
1-553017-7								F	Green	PBTP	0.080-2.03
1-553017-4		553017-4		553744-4	1389030-1			D	Yellow	PBTP	0.080-2.03
1-553397-1		553397-1		553744-5	1389030-3			D	Clear F/R ⁶	PBTP	0.080-2.03
5-554374-1		5-554374-3		554897-1	1479842-2		Clear & Cap	F	Green	N/A	0.080-2.03
		5-554374-7		554897-2				D	Green	N/A	0.080-2.03

*Note: Available only to customers with appropriate cartridge tooling.

1 - Must be ordered in multiples of 25 cartridges

2 - Must be ordered in multiples of 10 sticks

3 - F=Filled; D=Dry

4 - PBTP=Phosphor Bronze Tin Plated


5 - RUS Listed

6 - UL Listed, File No. E81956

Operating temperature for Tel-Splice 2-wire, 3-wire, and 1/2 tap is -40°C to 90°C except for Flame Retardant (F/R) versions which have a range of -40°C to 100°C

Conductor range is 19 AWG - 26 AWG.

Maximum insulation O.D. for Tel-Splice connector is 0.080"/2.03mm



Welded Tel-Splice

Cartridge convenience without the cartridge

Item Description

Economy (E.T.) Tool

Spring loaded handles not shown



Part Number

231839-1

790162-1

Crimp Handle Gauge

Note: Used to check proper crimp height of terminated connectors.



230495-1

Tel-Splice Connector Applicator (For Welded Sticks)

2-wire, 1/2 tap sticks

3-wire sticks



1490017-1

1490018-1

Tel-Splice Connector Applicator Kit

Includes one 1490017-1 and 1490018-1 in one convenient package

1583100-1

Technical Documents

Instruction Sheets: 408-3183, 408-4235, 408-6502, 408-6506, 408-8588, 408-3030, 408-309, 408-308
(US Half Tap only)

Application Specifications: 114-21003 (2-Wire), 114-6010 (TS-2, Half-Tap)

Tyco Electronics Corporation
8000 Purfoy Road
Fuquay Varina, NC 27526-9349
Tel 919-557 8900
Fax 919-557 8498
www.tycoelectronics.com
www.telecomosp.com

Tel-Splice, TE logo, and Tyco Electronics are trademarks.

While Tyco Electronics has made every reasonable effort to ensure the accuracy of the information in this document, Tyco Electronics does not guarantee that it is error-free, nor does Tyco Electronics make any other representation, warranty or guarantee that the information is accurate, correct, reliable or current. Tyco Electronics reserves the right to make any adjustments to the information contained herein at any time without notice. Tyco Electronics expressly disclaims all implied warranties regarding the information contained herein, including, but not limited to, any implied warranties of merchantability or fitness for a particular purpose. The dimensions in this document are for reference purposes only and are subject to change without notice. Specifications are subject to change without notice. Consult Tyco Electronics for the latest dimensions and design specifications.