

SuperTan® Extended (10004) Capacitors, Wet Tantalum Capacitors with Hermetic Seal



FEATURES

- Ultra high capacitance
- All tantalum, hermetically sealed case
- Utilizes proven Vishay SuperTan® technology
- High and stable capacitance
- High reliability, rugged design
- Axial through-hole terminations: Standard tin/lead (Sn/Pb)

PERFORMANCE CHARACTERISTICS

Operating Temperature: - 55 °C to + 85 °C (to + 125 °C with voltage derating)

Capacitance Tolerance: At 120 Hz, + 25 °C. ± 20 % standard. ± 10 % available as special.

DC Leakage Current (DCL Max.): At + 25 °C and above: Leakage current shall not exceed the values listed in the Standard Ratings tables.

Life Test: Capacitors are capable of withstanding a 2000 h life test at a temperature of + 85 °C at the applicable rated DC working voltage.


ORDERING INFORMATION

10004	-29	K	S
DSCC DRAWING NUMBER	DASH NUMBER	CAPACITANCE TOLERANCE	
		K = ± 10 % M = ± 20 %	S = Sleeved U = Unsleeved

DEFENSE SUPPLY CENTER, COLUMBUS
COLUMBUS, OHIO

Drawing no.
10004

DIMENSIONS in inches [millimeters]

				
CASE CODE	D ± 0.016 [0.41]	MAX. INSULATED (DIA.)	L ₁ + 0.031 [0.79] UNINSULATED	E ± 0.250 [6.35] MAX.
T1	0.188 [4.78]	0.219 [5.56]	0.453 [11.51]	1.500 [38.10]
T2	0.281 [7.14]	0.312 [7.92]	0.641 [16.28]	2.250 [57.15]
T3	0.375 [9.52]	0.406 [10.31]	0.766 [19.46]	2.250 [57.15]
T4	0.375 [9.52]	0.406 [10.31]	1.062 [26.97]	2.250 [57.15]

Notes

- Material at egress is Tantalum
- Insulation sleeving will lap over the ends of the capacitor case
- Tinned nickel leads, solderable and weldable
- Approx. weight: T1: 2.3 g, T2: 5.7 g, T3: 9.4 g, T4: 14.8 g



STANDARD RATINGS

CAPACITANCE (μ F)	VOLTAGE	CASE CODE	MAX. ESR AT 120 Hz (Ω)	TYP. ESR AT 1 kHz (Ω)	MAX. DCL AT		MAX. CAPACITANCE CHANGE AT			Z - 55 °C (Ω)	AC RIPPLE 85 °C 40 kHz mA RMS	PART NUMBER
					+ 25 °C (μ A)	+ 85 °C/ + 125 °C (μ A)	- 55 °C (%)	+ 85 °C (%)	+ 125 °C (%)			
10 V _{DC} AT + 85 °C, SURGE = 11.5 V _{DC} ; 7 V _{DC} AT + 125 °C												
4700	10	T3	0.35	< 0.200	16	100	- 80	10	20	3.50	4000	10004-01(1)(2)
10 000	10	T4	0.25	< 0.100	25	150	- 85	20	35	3.00	5000	10004-02(1)(2)
16 V _{DC} AT + 85 °C, SURGE = 18.4 V _{DC} ; 11 V _{DC} AT + 125 °C												
3300	16	T3	0.35	< 0.200	16	100	- 80	10	15	3.50	4000	10004-03(1)(2)
6000	16	T4	0.30	< 0.150	25	150	- 80	15	20	3.00	4500	10004-04(1)(2)
25 V _{DC} AT + 85 °C, SURGE = 28.8 V _{DC} ; 15 V _{DC} AT + 125 °C												
4000	25	T4	0.35		25	125	- 80	15	20	5.00	4250	10004-05(1)(2)
30 V _{DC} AT + 85 °C, SURGE = 34.5 V _{DC} ; 20 V _{DC} AT + 125 °C												
3300	30	T4	0.35	< 0.200	25	125	- 80	20	25	4.00	2750	10004-06(1)(2)
35 V _{DC} AT + 85 °C, SURGE = 40.3 V _{DC} ; 22 V _{DC} AT + 125 °C												
2800	35	T4	0.35	< 0.200	25	125	- 80	20	30	4.50	4000	10004-07(1)(2)
50 V _{DC} AT + 85 °C, SURGE = 57.5 V _{DC} ; 30 V _{DC} AT + 125 °C												
1500	50	T4	0.35	< 0.215	15	110	- 70	20	20	6.00	3500	10004-08(1)(2)
2200	50	T4	0.60	< 0.400	25	125	- 80	25	30	4.50	3000	10004-15(1)(2)
60 V _{DC} AT + 85 °C, SURGE = 69 V _{DC} ; 40 V _{DC} AT + 125 °C												
1000	60	T4	0.50	< 0.300	20	120	- 40	10	15	5.50	3500	10004-09(1)(2)
75 V _{DC} AT + 85 °C, SURGE = 86.3 V _{DC} ; 50 V _{DC} AT + 125 °C												
180	75	T2	1.50	< 0.500	5	25	- 35	15	20	30.00	2000	10004-10(1)(2)
470	75	T3	0.60	< 0.325	25	100	- 45	10	25	10.00	3000	10004-11(1)(2)
750	75	T4	0.50	< 0.400	20	120	- 35	10	15	6.50	3500	10004-12(1)(2)
100 V _{DC} AT + 85 °C, SURGE = 115 V _{DC} ; 65 V _{DC} AT + 125 °C												
400	100	T4	0.70	< 0.400	10	120	- 40	6	12	15.00	3000	10004-13(1)(2)
125 V _{DC} AT + 85 °C, SURGE = 144 V _{DC} ; 85 V _{DC} AT + 125 °C												
240	125	T4	0.80	< 0.600	15	150	- 35	6	12	20.00	2500	10004-14(1)(2)

Note

- Part number definitions:
 - (1) K = 10 %
M = 20 %
 - (2) S = Sleeved or insulated
U = Unsleeved

RIPPLE CURRENT MULTIPLIERS VS. FREQUENCY, TEMPERATURE AND APPLIES PEAK VOLTAGE

FREQUENCY OF APPLIED RIPPLE CURRENT		120 Hz				800 Hz				1 kHz				10 kHz				40 kHz				100 kHz			
AMBIENT STILL AIR TEMP. IN °C		≤ 55	85	105	125	≤ 55	85	105	125	≤ 55	85	105	125	≤ 55	85	105	125	≤ 55	85	105	125	≤ 55	85	105	125
% of 85 °C rated peak voltage	100 %	0.60	0.39	-	-	0.71	0.43	-	-	0.72	0.46	-	-	0.88	0.55	-	-	1.0	0.63	-	-	1.1	0.69	-	-
	90 %	0.60	0.46	-	-	0.71	0.55	-	-	0.72	0.55	-	-	0.88	0.67	-	-	1.0	0.77	-	-	1.1	0.85	-	-
	80 %	0.60	0.52	0.35	-	0.71	0.62	0.42	-	0.72	0.62	0.42	-	0.88	0.76	0.52	-	1.0	0.87	0.59	-	1.1	0.96	0.65	-
	70 %	0.60	0.58	0.44	-	0.71	0.69	0.52	-	0.72	0.70	0.52	-	0.88	0.85	0.64	-	1.0	0.97	0.73	-	1.1	1.07	0.80	-
	66 2/3 %	0.60	0.60	0.46	0.27	0.71	0.71	0.55	0.32	0.72	0.72	0.55	0.32	0.88	0.88	0.68	0.40	1.0	1.0	0.77	0.45	1.1	1.1	0.85	0.50



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and/or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

Material Category Policy

Vishay Intertechnology, Inc. hereby certifies that all its products that are identified as RoHS-Compliant fulfill the definitions and restrictions defined under Directive 2011/65/EU of The European Parliament and of the Council of June 8, 2011 on the restriction of the use of certain hazardous substances in electrical and electronic equipment (EEE) - recast, unless otherwise specified as non-compliant.

Please note that some Vishay documentation may still make reference to RoHS Directive 2002/95/EC. We confirm that all the products identified as being compliant to Directive 2002/95/EC conform to Directive 2011/65/EU.

Vishay Intertechnology, Inc. hereby certifies that all its products that are identified as Halogen-Free follow Halogen-Free requirements as per JEDEC JS709A standards. Please note that some Vishay documentation may still make reference to the IEC 61249-2-21 definition. We confirm that all the products identified as being compliant to IEC 61249-2-21 conform to JEDEC JS709A standards.