

COMPANY LOGO—

ETC. —

COLUMN 2—

COLUMN 1 —

ROW B-1

$$R \sqcup W \quad A \vdash$$

. 100
2. 54

100
2.54

DIM D

DIM G _____

DIM E	_____
1-10	1-10

OVERALL LENGTH

—DIM L_____

NOTE 2 & 3

NOTE 6

-NOTE 6

MATING LENGTH
 $.318 \pm .010$ ____
 8.08 ± 0.25 ____

$$\begin{array}{r} .350 \\ 8.89 \end{array}$$
$$\begin{array}{r} .09 \\ 2.3 \end{array}$$

93° MAX ALL
DIRECTIONS

— .025
0.64^{REF}

⊕ ∅. 025/. 64 (S)
AT TIPS

SECTION Y-Y

mat'l. code				surface ISO 1902 ✓		tolerance ISO 406 ISO 1101		projection 		product family HEADERS	
ltr	ecn no.	dr	date	tolerances unless otherwise specified					title		
N	V20311	JWB	3/16/92	angles		$\pm .01 / \pm .03$		INCH/MM 	VERTICAL 2-ROW GUIDE PIN		
P	V41750	MDF	11/15/94	linear		$\pm .005 / \pm .005 / \pm .01$			(SLOTTED) HEADER-PRESS FIT TAILS		
R	V50831	HTB	6/12/95	0° ±2'		$\pm .0004 / \pm .0004 / \pm .005$		scale 2:1			
S	V71449	HTB	10/7/97	dr	M. FETROW	11/14/94			dwg no. sheet 1 of 3 size A		
T	M05-0089	AHS	5/19/05	engr	L. FYE	11/14/94			67289		
U	M07-0116	MGT	2/19/07	chr	L. FYE	11/14/94					
V	M09-0059	MHT	4/16/09	appd	L. FYE	11/14/94					
sheet index	revision	v	v	v							
	sheet	1	2	3							

PRODUCT NUMBER NOTE 5, 7	SIZE NOTE 5	TAIL LENGTH DIM H	DIM D	DIM G	DIM E	OVERALL LENGTH DIM L	PLATING NOTE 11
67289-XXX	2 x XXX	.177/4.50	NOTE 4	.37/9.4+D DIM	.40/10.2+D DIM	.48/12.2+D DIM	30u"/.76u MIN Au OVER 50u"/1.27u Ni
67290-XXX		.177/4.50					15u"/.38u MIN Au OVER 50u"/1.27u Ni
67291-XXX		.177/4.50					GOLD FLASH OVER 50u"/1.27u Ni
67292-XXX		.177/4.50					120u"/3.05u 93/7 Sn/Pb OVER 50u"/1.27u Ni
67958-XXX		.310/7.90					30u"/.76u MIN Au OVER 50u"/1.27u Ni
67961-XXX		.310/7.90					15u"/.38u MIN Au OVER 50u"/1.27u Ni
68251-XXX		.680/17.30					30u"/.76u MIN Au OVER 50u"/1.27u Ni
68509-XXX		.480/12.20					30u"/.76u MIN Au OVER 50u"/1.27u Ni
68521-XXX		.480/12.20					30u"/.76u MIN GXT™ OVER 50u"/1.27u Ni
68830-XXX		.680/17.30					15u"/.38u MIN Au OVER 50u"/1.27u Ni
68831-XXX		.480/12.20					15u"/.38u MIN Au OVER 50u"/1.27u Ni
68832-XXX		.310/7.90					15u"/.38u MIN GXT™ OVER 50u"/1.27u Ni
68833-XXX		.310/7.90					30u"/.76u MIN GXT™ OVER 50u"/1.27u Ni
68834-XXX		.177/4.50					15u"/.38u MIN GXT™ OVER 50u"/1.27u Ni
68835-XXX		.177/4.50					30u"/.76u MIN GXT™ OVER 50u"/1.27u Ni
68836-XXX		.680/17.30					30u"/.76u MIN GXT™ OVER 50u"/1.27u Ni
68837-XXX		.680/17.30					15u"/.38u MIN GXT™ OVER 50u"/1.27u Ni
68838-XXX		.480/12.20					15u"/.38u MIN GXT™ OVER 50u"/1.27u Ni
69275-XXX		.310/7.90					GOLD FLASH OVER 50u"/1.27u Ni
69276-XXX		.310/7.90					120u"/3.05u 93/7 Sn/Pb OVER 50u"/1.27u Ni
69277-XXX		.480/12.20					GOLD FLASH OVER 50u"/1.27u Ni
69278-XXX		.480/12.20					120u"/3.05u 93/7 Sn/Pb OVER 50u"/1.27u Ni
69279-XXX		.680/17.30					GOLD FLASH OVER 50u"/1.27u Ni
69280-XXX		.680/17.30					120u"/3.05u 93/7 Sn/Pb OVER 50u"/1.27u Ni
69283-XXX		.177/4.50					DUPLEX 15u"/.38u Au & 100u"/1.27u 60/40 SnPb OVER 50u"/1.27u Ni
69284-XXX		.177/4.50					DUPLEX 30u"/.76u Au & 100u"/1.27u 60/40 SnPb OVER 50u"/1.27u Ni
69285-XXX		.310/7.90					DUPLEX 15u"/.38u Au & 100u"/1.27u 60/40 SnPb OVER 50u"/1.27u Ni
69286-XXX		.310/7.90					DUPLEX 30u"/.76u Au & 100u"/1.27u 60/40 SnPb OVER 50u"/1.27u Ni
69287-XXX		.480/12.20					DUPLEX 15u"/.38u Au & 100u"/1.27u 60/40 SnPb OVER 50u"/1.27u Ni
69288-XXX		.480/12.20					DUPLEX 30u"/.76u Au & 100u"/1.27u 60/40 SnPb OVER 50u"/1.27u Ni
69289-XXX		.680/17.30					DUPLEX 15u"/.38u Au & 100u"/1.27u 60/40 SnPb OVER 50u"/1.27u Ni
69290-XXX	2 x XXX	.680/17.30	NOTE 4	.37/9.4+D DIM	.40/10.2+D DIM	.48/12.2+D DIM	DUPLEX 30u"/.76u Au & 100u"/1.27u 60/40 SnPb OVER 50u"/1.27u Ni

NOTES:

- ① MOLDING MATERIAL: HI-TEMP RESIN
PER UL 94V-0
COLOR: NATURAL
- ② TERMINAL MATERIAL: 3/4 HARD PHOS BRONZE
UNS C5100.
3. PIN RETENTION TO BE 3 LBS/1.36 KG
MIN PER PIN IN EITHER DIRECTION.
- ④ DIM D =(NO. OF COLUMNS-1)TIMES .100/2.54
- ⑤ -XXX REPRESENTS NO. OF COLUMNS
(i.e. 2X5 PART IS -005)
-001 THRU -004 ARE NOT AVAILABLE
-005 THRU -050 ARE AVAILABLE
- ⑥ FLATNESS IS MEASURED FROM THE BOTTOM
OF THE END STANDOFFS.
- ⑦ ADD "LF" SUFFIX AT THE END OF PART NUMBER FOR LEAD FREE OPTION.
- ⑧ IF "LF" P/N THE PRODUCT MEETS EUROPEAN UNION
DIRECTIVES AND OTHER COUNTRY REGULATION AS
DESCRIBED IN GS-22-008.
- ⑩ THE PRODUCT IS NOT INTENDED TO BE EXPOSED
TO A MANUFACTURING SOLDER PROCESS.
- ⑪ PLATING OPTIONS:
MAY BE EITHER GOLD OR GXT PLATED AT MANUFACTURER'S OPTION.

mat'l. code		surface ISO 1302	tolerance ISO 1101	projection	product family HEADERS
ltr	ecn no	dr	date	tolerances unless otherwise specified	title
v				angles linear	VERTICAL 2-ROW GUIDE PIN
				0°±2'	(SLOTTED) HEADER-PRESS FIT TAILS
				dr	scale 2:1
				engr	dwg no
				chr	sheet 2 of 3
				appd	size
					A3
sheet	revision				type
index	sheet				Product Customer Drawing

form: A3



FCIconnect.com

Copyright FCI

1			2			3			4			5			6		
PRODUCT NUMBER NOTE 5, 7		SIZE NOTE 5	TAIL LENGTH DIM H	DIM D	DIM G	DIM E	OVERALL LENGTH DIM L	PLATING NOTE 11									
67289-XXXLF	2 x XXX	.177/4.50	NOTE 4	.37/9.4+D DIM	.40/10.2+D DIM	.48/12.2+D DIM	30u"/.76u MIN Au OVER 50u"/1.27u Ni										
67290-XXXLF		.177/4.50					15u"/.38u MIN Au OVER 50u"/1.27u Ni										
67291-XXXLF		.177/4.50					GOLD FLASH OVER 50u"/1.27u Ni										
67292-XXXLF		.177/4.50					100u"/2.54u Sn OVER 50u"/1.27u Ni										
67958-XXXLF		.310/7.90					30u"/.76u MIN Au OVER 50u"/1.27u Ni										
67961-XXXLF		.310/7.90					15u"/.38u MIN Au OVER 50u"/1.27u Ni										
68251-XXXLF		.680/17.30					30u"/.76u MIN Au OVER 50u"/1.27u Ni										
68509-XXXLF		.480/12.20					30u"/.76u MIN Au OVER 50u"/1.27u Ni										
68521-XXXLF		.480/12.20					30u"/.76u MIN GXT™ OVER 50u"/1.27u Ni										
68830-XXXLF		.680/17.30					15u"/.38u MIN Au OVER 50u"/1.27u Ni										
68831-XXXLF		.480/12.20					15u"/.38u MIN Au OVER 50u"/1.27u Ni										
68832-XXXLF		.310/7.90					15u"/.38u MIN GXT™ OVER 50u"/1.27u Ni										
68833-XXXLF		.310/7.90					30u"/.76u MIN GXT™ OVER 50u"/1.27u Ni										
68834-XXXLF		.177/4.50					15u"/.38u MIN GXT™ OVER 50u"/1.27u Ni										
68835-XXXLF		.177/4.50					30u"/.76u MIN GXT™ OVER 50u"/1.27u Ni										
68836-XXXLF		.680/17.30					30u"/.76u MIN GXT™ OVER 50u"/1.27u Ni										
68837-XXXLF		.680/17.30					15u"/.38u MIN GXT™ OVER 50u"/1.27u Ni										
68838-XXXLF		.480/12.20					15u"/.38u MIN GXT™ OVER 50u"/1.27u Ni										
69275-XXXLF		.310/7.90					GOLD FLASH OVER 50u"/1.27u Ni										
69276-XXXLF		.310/7.90					100u"/2.54u Sn OVER 50u"/1.27u Ni										
69277-XXXLF		.480/12.20					GOLD FLASH OVER 50u"/1.27u Ni										
69278-XXXLF		.480/12.20					100u"/2.54u Sn OVER 50u"/1.27u Ni										
69279-XXXLF		.680/17.30					GOLD FLASH OVER 50u"/1.27u Ni										
69280-XXXLF		.680/17.30					100u"/2.54u Sn OVER 50u"/1.27u Ni										
69283-XXXLF		.177/4.50					DUPLEX 15u"/.38u Au & 100u"/2.54u Sn OVER 50u"/1.27u Ni										
69284-XXXLF		.177/4.50					DUPLEX 30u"/.76u Au & 100u"/2.54u Sn OVER 50u"/1.27u Ni										
69285-XXXLF		.310/7.90					DUPLEX 15u"/.38u Au & 100u"/2.54u Sn OVER 50u"/1.27u Ni										
69286-XXXLF		.310/7.90					DUPLEX 30u"/.76u Au & 100u"/2.54u Sn OVER 50u"/1.27u Ni										
69287-XXXLF		.480/12.20					DUPLEX 15u"/.38u Au & 100u"/2.54u Sn OVER 50u"/1.27u Ni										
69288-XXXLF		.480/12.20					DUPLEX 30u"/.76u Au & 100u"/2.54u Sn OVER 50u"/1.27u Ni										
69289-XXXLF		.680/17.30					DUPLEX 15u"/.38u Au & 100u"/2.54u Sn OVER 50u"/1.27u Ni										
69290-XXXLF	2 x XXX	.680/17.30	NOTE 4	.37/9.4+D DIM	.40/10.2+D DIM	.48/12.2+D DIM	DUPLEX 30u"/.76u Au & 100u"/2.54u Sn OVER 50u"/1.27u Ni										

mat'l. code		surface		tolerance		projection		product family	
ISO 1902		ISO 406		ISO 1101				HEADERS	
tolerances unless otherwise specified		linear		XX±.01/XX±0.3		INCH/MM		title	
V		angles		XXX±.005/XXX±0.13		scale 2:1		VERTICAL 2-ROW GUIDE PIN	
		0° ±2°		XXXX±.0020/XXX±0.05				(SLOTTED) HEADER-PRESS FIT TAILS	
		dr		M. FETROW		11/14/94		dwg no	
		engr		L. FYE		11/14/94		sheet 3 of 3	
		chr		L. FYE		11/14/94		size	
		appd		L. FYE		11/14/94		A3	
sheet		revision						type	
index		sheet						Product Customer Drawing	

1	2	3	4	5	6
---	---	---	---	---	---

form A3

form: A3