

GaAs SP2T 2.8V High Power Switch

DC - 3 GHz

V 1.00

MASWSS0029

Features


- Low Voltage Operation: 2.8V
- High IP3: +60 dBm
- Low Insertion Loss: 0.40 dB at 1 GHz
- High Isolation: 24.5 dB at 1 GHz
- Miniature Package: SOT-26
- 0.5 micron GaAs PHEMT Process

Description

M/A-COM's MASWSS0029 is a GaAs PHEMT MMIC single pole two throw (SP2T) high power switch in a low cost miniature SOT-26 package. The MASWSS0029 is ideally suited for applications where high power, low control voltage, low insertion loss, high isolation, small size and low cost are required. Typical applications are for CDMA handset systems that connect separate transceiver and/or GPS functions to a common antenna, as well as other related handset and general purpose applications. This part can be used in all systems operating up to 3 GHz requiring high power at low control voltage.

The MASWSS0029 is fabricated using a 0.5 micron gate length GaAs PHEMT process. The process features full passivation for performance and reliability.

SOT-26 Plastic Package



Electrical Specifications: $T_A = 25^\circ\text{C}$, $Z_0 = 50 \text{ Ohms}^1$

Parameter	Test Conditions	Frequency	Units	Min.	Typ.	Max.
Insertion Loss ²	$V_c = 0 \text{ V}$, 2.8 V	DC – 1 GHz	dB	—	0.40	0.65
		1 – 2 GHz	dB	—	0.50	—
		2 - 3 GHz	dB	—	0.60	—
Isolation	$V_c = 0 \text{ V}$, 2.8 V	DC – 1 GHz	dB	23	24.5	—
		1 – 2 GHz	dB	—	18.5	—
		2 - 3 GHz	dB	—	13	—
Return Loss	$V_c = 0 \text{ V}$, 2.8 V	DC – 2 GHz	dB	—	20	—
		2 - 3 GHz	dB	—	16	—
IP3	$V_c = 0 \text{ V}$, 2.8 V Two Tone, +29 dBm Total Pin, 1 MHz Spacing	0.05 - 3 GHz	dBm	—	60	—
P0.1dB	$V_c = 0 \text{ V}$, 3 V	—	dBm	—	34	—
Trise, Tfall	10% to 90% RF, 90% to 10% RF	—	nS	—	200	—
Ton, Toff	50% control to 90% RF, and 50% control to 10% RF	—	nS	—	250	—
Transients	In Band	—	mV	—	14	—
Gate Leakage	$V_c = 2.8 \text{ V}$	—	uA	—	—	100

1. External DC blocking capacitors are required on all RF ports.

2. Insertion Loss can be optimized by varying the DC blocking capacitor value, e.g. 1000 pF for 100 MHz - 500 MHz, 39 pF for 0.5 GHz - 3 GHz.


Pin Configuration

PIN No.	PIN Name	Description
1	RF1	RF Port 1
2	GND	RF Ground
3	RF2	RF Port 2
4	V2	Control 2
5	RFC	RF Common Port
6	V1	Control 1

Static Sensitivity

Gallium Arsenide Integrated Circuits are sensitive to electrostatic discharge (ESD) and can be damaged by static electricity. Proper ESD control techniques should be used when handling these devices.

Functional Schematic



Absolute Maximum Ratings³

Parameter	Absolute Maximum
Max Input Power (0.5 - 3 GHz, 3 V Control)	+35 dBm
Operating Voltage	+8.5 volts
Operating Temperature	-40°C to +85°C
Storage Temperature	-65°C to +150°C

3. Exceeding any one or combination of these limits may cause permanent damage to this device.

Truth Table

V1	V2	ANT- RF1	ANT - RF2
+2.8V	0V	On	Off
0V	+2.8V	Off	On

M/A-COM Inc. and its affiliates reserve the right to make changes to the product(s) or information contained herein without notice. M/A-COM makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does M/A-COM assume any liability whatsoever arising out of the use or application of any product(s) or information.



Visit www.macom.com for additional data sheets and product information.

■ **North America:** Tel. (800) 366-2266
 ■ **Asia/Pacific:** Tel.+81-44-844-8296, Fax +81-44-844-8298
 ■ **Europe:** Tel. +44 (1344) 869 595, Fax+44 (1344) 300 020


tyco / Electronics

M/A-COM

Typical Performance Curves

Insertion Loss vs. Frequency,
25°C, 39 pFIsolation vs. Frequency,
25°C, 39 pF

SOT-26 Plastic Package

Ordering Information⁴

Part Number	Package
MASWSS0029	SOT-26 6-lead Plastic Package
MASWSS0029TR	1000 piece reel
MASWSS0029SMB	Sample Test Board

4. Reference Application Note M513 for reel size information.

M/A-COM Inc. and its affiliates reserve the right to make changes to the product(s) or information contained herein without notice. M/A-COM makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does M/A-COM assume any liability whatsoever arising out of the use or application of any product(s) or information.

Visit www.macom.com for additional data sheets and product information.

■ North America: Tel. (800) 366-2266
 ■ Asia/Pacific: Tel.+81-44-844-8296, Fax +81-44-844-8298
 ■ Europe: Tel. +44 (1344) 869 595, Fax+44 (1344) 300 020

tyco / Electronics

M/A-COM