



Off-white, RAL 9002
Black, RAL 9005




XS



M



L/XL



THE PRODUCT

The idea of giving greater expression to ergonomic requirements was the starting point of the development of the SMART-CASE.

And so the design follows the touch sensation of the human being, thus facilitating natural sequences of hand movements.

Benefit from the outstanding balance between design and technical sophistication.

YOUR ADVANTAGE

Convincing ergonomics; unique design.

Ideal for remote controls, with cables or with battery compartment.

Cable glands for sizes M, L and XL for cables $\varnothing$ 3.4 - 5.9 mm. Cable gland already included (TPE, standard colour volcano, NCS S 5502-G).

Optionally in material permeable to infra-red signals from stock. For utmost efficiency the front face is polished.

Recessed operating area to protect the membrane keyboard (M/L/XL).

Fastening pillars and fixing supports for PCBs and components.

APPLICATIONS

Remote controls of all types, wireless or with cable connection.

Especially suitable for use in hospitals and social fields as well as in industry and households.

PROTECTION CLASS IP 65

With sealing (accessories) sizes L and XL versions without battery compartment.

MAX. SIZE OF PCB

SMART-CASE	L x W/W ₂ in mm	
	base part	top part
XS	46 x 29/18	—
M	58 x 38/30	63 x 40/31
L	88 x 50/42	117 x 51/37
XL	127 x 60/50	78 x 60/56 + 50 x 55/47

(cutouts of pillars and battery compartment not taken into consideration)

ENCLOSURES

SMART-CASE	Outside dim. in mm			Version / Equipment (dim. in mm)			ABS (UL 94 HB) off-white	Part-No. ABS (UL 94 HB) black	PMMA (plexiglass®) black*1
	L	W	H	battery comp.	cable gland ø	max. dim. keypad			
XS	58	35,6	19	—	—	without recessed area	A 90 64 107	A 90 64 109	A 90 64 209
M	96	47	24	I 2 x AAA	—	without recessed area	A 90 66 107	A 90 66 109	A 90 66 209
	96	47	24	II 2 x AAA	—	74.60 x 39.85	A 90 66 117	A 90 66 119	A 90 66 219
	96	47	24	III —	approx. 5.0 - 5.9	74.60 x 39.85	A 90 66 127	A 90 66 129	—
	96	47	24	IV —	approx. 4.2 - 5.0	74.60 x 39.85	A 90 66 137	A 90 66 139	—
	96	47	24	V —	approx. 3.4 - 4.2	74.60 x 39.85	A 90 66 147	A 90 66 149	—
	140	62.7	30.5	I 2 x AA / 1 x 9 V	—	103.95 x 50.95	A 90 67 107	A 90 67 109	A 90 67 209
L	140	62.7	30.5	II —	—	103.95 x 50.95	A 90 67 117	A 90 67 119	A 90 67 219
	140	62.7	30.5	III —	approx. 5.0 - 5.9	103.95 x 50.95	A 90 67 127	A 90 67 129	—
	140	62.7	30.5	IV —	approx. 4.2 - 5.0	103.95 x 50.95	A 90 67 137	A 90 67 139	—
	140	62.7	30.5	V —	approx. 3.4 - 4.2	103.95 x 50.95	A 90 67 147	A 90 67 149	—
	168	74.4	35.4	I 2 x AA / 1 x 9 V	—	110.60 x 61.05	A 90 68 107	A 90 68 109	A 90 68 209
	168	74.4	35.4	II —	—	110.60 x 61.05	A 90 68 117	A 90 68 119	A 90 68 219
XL	168	74.4	35.4	III —	approx. 5.0 - 5.9	110.60 x 61.05	A 90 68 127	A 90 68 129	—
	168	74.4	35.4	IV —	approx. 4.2 - 5.0	110.60 x 61.05	A 90 68 137	A 90 68 139	—
	168	74.4	35.4	V —	approx. 3.4 - 4.2	110.60 x 61.05	A 90 68 147	A 90 68 149	—

ACCESSORIES

Article	For enclosure SMART-CASE	Version / Application	Part-No.
① Set of battery clips	M	tin-plated, for 2 x 1.5 V micro cells (AAA)	A 91 66 001
	L, XL	tin-plated, for 2 x 1.5 V mignon cells (AA)	A 91 90 002
② Battery contact	M	tin-plated, for a serial connection when using the set of batt. clips	A 91 66 002
③ Battery holder	M	clamps down securely 2 x AAA	A 91 66 003
④ Plug-in contact	L, XL	for one 9 V flat battery (PP3)	A 91 60 003
⑤ Sealing	L	for versions II-V, for a higher protection class (IP 65)	A 91 67 002
	XL	for versions II-V, for a higher protection class (IP 65)	A 91 68 002
⑥ Set of strain relief	M, L, XL & station	for strain relief of cable connected applications	A 91 66 004
⑦ Key ring	XS	nickel-plated, ø 20.5 mm	A 91 64 001
			off-white black
⑧ Belt / pocket clip	M, L, XL	PA 6, 2 mounting holes ø 4.2 mm necessary	A 91 67 017 A 91 67 019
⑨ Holding clamp	M, L, XL	up to ø 32 mm, ABS, mounting holes ø 4.2 mm necessary	A 91 67 027 A 91 67 029
⑩ Holder	M	ABS, also suitable for cable connected applications	A 91 66 307 A 91 66 309
	L	ABS, also suitable for cable connected applications	A 91 67 307 A 91 67 309
	XL	ABS, also suitable for cable connected applications	A 91 68 307 A 91 68 309
⑪ Adhesive foil for holder	holder M	double-sided adhesive foil with foam carrier	A 91 66 005
	holder L	double-sided adhesive foil with foam carrier	A 91 67 005
	holder XL	double-sided adhesive foil with foam carrier	A 91 68 005
⑫ Station	M	ABS, desk case application (available from December 2009)	A 91 66 037 A 91 66 039
	L	ABS, desk case application (available from December 2009)	A 91 67 037 A 91 67 039
	XL	ABS, desk case application (available from January 2010)	A 91 68 037 A 91 68 039
⑬ Contacts (bore holes necessary)	M, L, XL	contact pin, female for the case, gold-plated, < 15 A, 1-pole	A 91 93 030
	M, L, XL	spring contact, male for the station, gold-plated, < 15 A, 1-pole	A 91 93 031



*1 sizes M, L & XL only the bottom parts made of PMMA, top part is made of ABS (UL 94 HB); cases made of PMMA (plexiglass®) not comparable to cases made of ABS in terms of mechanical load-bearing capacity

NEW PRODUCT