

Technical drawing of a mechanical part, showing side and end views with dimensions in inches and millimeters.

Side View Dimensions:

- Top width: $\pm .010$ [± 0.25]
- Top width: $.280$ [7.11]
- Top width: $\pm .010$ [± 0.25]
- Top width: $.280$ [7.11]
- Left height: $\pm .010$ [± 0.25]
- Left height: $.530$ [13.46]
- Right height: $\pm .015$ [± 0.38]
- Right height: $.730$ [18.54]
- Bottom hole diameter: $\varnothing .144$ [$\varnothing 3.66$]

End View Dimensions:

- Top width: $\pm .010$ [± 0.25]
- Top width: $.230$ [5.84]
- Inner diameter: $\varnothing .135$ [$\varnothing 3.43$] I.D.

1. ACCOMMODATES WIRE RANGE 12/10 AWG

<h1>KEYSTONE ELECTRONICS CORP.</h1> <p>ASTORIA, N.Y. 11105-2017</p>			
PART NAME <h2>SNAP-SPADE TERMINAL</h2>			
MATERIAL <h2>.040 [1.02] TH'K COPPER</h2>			
FINISH <h2>TIN PLATE</h2>		DRN BY <h2>BOONE</h2>	DATE <h2>11.5.07</h2>
		APP'D <h2>LN</h2>	SCALE <h2>2X</h2>
TOLERANCES INCH [MM] DECIMAL $\pm .005$ [± 0.15] ANGULAR $\pm 1^\circ$ UNLESS OTHERWISE SPECIFIED		CODE <h2>C/M</h2>	DWG NO. <h1>8260</h1>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Keystone Electronics:](#)

[8260](#)