

**Part Number: 73811-1002**

Image not available

Status: Inactive
Series: [73811](#)
Category: Memory Module Sockets

Series image - Reference only

Mates With Part(s):
EIA 364 standard 1.27mm thick PCB module

Part Detail**General**

Status	Inactive
Category	Memory Module Sockets
Series	73811
Component Type	Socket
JEDEC Outline	N/A
Obsolete Date	2004/01/01
Product Name	RIMM

Physical

Circuits (Loaded)	168
Durability (mating cycles max)	25
Entry Angle	Vertical (Top Entry)
Keying to Mating Part	Yes
Material - Plating Mating	Gold
PCB Retention	None
PCB Thickness - Recommended	2.40mm
Packaging Type	Tray
Pitch - Mating Interface	1.00mm
Temperature Range - Operating	-40°C to +85°C
Termination Interface: Style	Through Hole

Electrical**(Please review the Product Specification for specific details.)**

Current - Maximum per Contact	0.5A
Voltage - Maximum	100V
Voltage Key	N/A

Material Info**Application Tooling**

Tooling specifications and manuals are found by selecting the products below.

Crimp Height Specifications are then contained in the Application Tooling Specification document.

Previously Available Application Tooling

[Check our list of old tooling that used to be available for this part](#)