


REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	F1	REDRAWN PER ECO-17-007400	15DEC2017	RS	DR

AMP WIRE RANGE	 Listed FILE E13288	 LR7189 Certified
16-14 AWG SOLID OR STRANDED	16-14 AWG SOLID OR STRANDED	16-14 AWG SOLID OR STRANDED



1 FOR $\varnothing 2.921[\varnothing.115]$ TO $\varnothing 4.318[\varnothing.170]$ WIRE INSULATION.

2 BODY MATERIAL THICKNESS: $0.787 \pm 0.051[.031 \pm .002]$


3 APPLIES FROM EDGE OF METAL WIRE BARREL TO CENTER OF STUD HOLE.

4 STAMP AMP 16-14* APPROX AS SHOWN.

5 MATERIAL:
BODY & SLEEVE: COPPER PER ASTM B152
INSULATION: NYLON

6 FINISH:
BODY & SLEEVE: TIN PLATE PER ASTM B545
INSULATION: COLOR-BLUE.

5000	ON TAPE	2-320306-1
1000	LOOSE PIECE	320306
QTY	PACKAGE TYPE	PART NO

DIMENSIONS: mm [INCHES]		DWN RAVI S	15DEC2017	MATERIAL 5		FINISH 6					
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± 0.127[.005] 4 PLC ± - ANGLES ± 5°		CHK ROHDE DANIEL F	15DEC2017	TE TE Connectivity							
		APVD ROHDE DANIEL F	15DEC2017								
		PRODUCT SPEC UL 486 A-B		NAME WIRE TERMINAL, P.I.D.G - HOOK, WIRE SIZE: 16-14							
		APPLICATION SPEC 114-2157									
		WEIGHT —		SIZE A4		CAGE CODE 00779		DRAWING NO C-320306		RESTRICTED TO —	
		CUSTOMER DRAWING						SCALE 4:1		SHEET 1 of 1	

