





REV.	DATE	DESCRIPTION
A	06/05/03	UPDATE DRAWING FORMAT



RECOMMENDED CABLE STRIPPING DIM'S



NOTE:

1. CRIMPED FERRULE
HEX CRIMP SIZE .255"
2. CRIMPED CONTACT PIN
HEX CRIMP SIZE .043"

				UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007" .315 – 1.180 = ± 0.015" 1.180 – 4.724 = ± 0.020" DO NOT SCALE DRAWING	APPROVALS		DATE		Amphenol Connex				
8					DRAWN	G.R.S.	06/05/03						
7					CHECKED								
6						ISSUED				PART DESCRIPTION BNC CRIMP PLUG (FOR BELDEN 1506A CABLE)			
5						SHEET	1 OF 1						
4	FERRULE	COPPER	NICKEL		1					PART NO. 112975			
3	INSULATOR	TEFLON	NATURAL		1								
2	CONTACT PIN	BRASS	GOLD	1					DWG. NO. 112975.DWG REV. A SIZE A SCALE NA				
1	BODY	BRASS	NICKEL	1									
DESCRIPTION		MATERIAL	FINISH	QTY			CAD FILE C:/112/112975.DWG						

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[112975](#)