



N=Number of poles



P.C.B. LAYOUT



SIGN	DATE	DESCRIPTION	APPROVER

THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!

Material

- Terminal body(Contact pin) : Brass
- Surface of solder tail : Tin plated
- Wire guard : Stainless steel
- Insulator (housing):Thermoplastic (UL94 V-0)

Electrical cULus

- Voltage rating:150V
- Current rating:4A
- Wire range:
 - Solid wire(AWG):22-28
 - Stranded wire(AWG):22-28
- Wire strip length:6-7mm
- Withstanding Voltage:1.3KV
- Operating temperature: -30°C to +105°C
- Soldering temperature: 250°C±10°C/5 Sec
- Safety Approval : 

RoHS Compliant

PART NUMBER:

OSTHEXX4040

No. of Poles
02 2 Poles
03 3 Poles
...
24 24 Poles

COLOR
0 Black
4 Orange (Standard)
5 Green
6 Blue
8 Grey



ON-SHORE TECHNOLOGY, INC.

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF ON-SHORE TECHNOLOGY, INC. AND SHALL NOT BE REPRODUCED, COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF ON-SHORE TECHNOLOGY, INC.

TITLE		OSTHE 2.5mm Series with Lever					
PART NO.	OSTHEXX4040			DWG NO.	OSTHEXX4040.DWG		
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.			
Shi jun 2006.11.01	Marvin 2006.07.03	Marvin 2006.07.03	Marvin 2006.07.03				
SHEET: 01/01					UNIT: mm	Tolerance	
					SCALE: NONE	X. ±0.50	
					REV: C	X.X ±0.30	
						X.XX ±0.10	
						X° ±1°	