




THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PANDUIT PART NUMBER	MAXIMUM BUNDLE DIAMETER	PKG QTY	LENGTH	
			" L" +/- .3" [7]	
MLT4DSH-Q	4" [102]	25	29.5"	[749]
MLT6DSH-Q	6" [152]	25	41.5"	[1054]
MLT8DSH-Q	8" [203]	25	53.5"	[1359]

BROKEN EDGES TO ELIMINATE SHARPNESS

SECTION A - A
SCALE 4:1



BODY WRAPS AROUND BUNDLE TWO TIMES
PASSING THROUGH THE HEAD TWICE
(NOT TO SCALE)

NOTES:

1. APPLICATION TOOL - RT2HT, RT2HTN
2. MINIMUM LOOP TENSILE STRENGTH - 1200 LBS. (5340 NEWTONS) WHEN TESTED ON A 3" MANDREL.
3. [] DENOTES DIMENSION IN MILLIMETERS
4. MATERIAL: 304 STAINLESS STEEL
5. GREEN COLOR STRIPE IDENTIFIER FOR DOUBLE WRAP PRODUCT

PANDUIT CORP. TINLEY PARK, ILLINOIS

METAL LOCKING TIE
SUPER HEAVY-DUTY DOUBLE LOOP

UNLESS OTHERWISE SPECIFIED,
DIMENSIONAL TOLERANCES ARE:
(.XX) ± .02 (XXXX) ± N/A
(.XXX) ± .010 ANGLES ± 2°

UNLESS OTHERWISE SPECIFIED,
ALL DIMENSIONS ARE GIVEN
IN INCHES, THIRD ANGLE PROJECTION.

06A	09/09	MIM	CCH	REPLACED EASY-THREAD HEAD DESIGN WITH THE ORIGINAL CONVENTIONAL HEAD DESIGN
REV	DATE	BY	CHK	DESCRIPTION

DRAWN BY MIM	MAT'L: SEE NOTES	SCALE FULL	
DATE 08/29/08		DRAWING NO.	DWG
CHK'D SKB		N41165BS_DC	A SIZE

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panduit:

[MLT4DSH-Q](#) [MLT6DSH-Q](#) [MLT8DSH-Q](#)