



THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION


© COPYRIGHT - BY TYCO ELECTRONICS CORPORATION. ALL INTERNATIONAL RIGHTS RESERVED.

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
DF	X0						
			A	REV PER ECO-08-029134	01JUN10	PY	JG

ASSEMBLED VIEW




RECOMMENDED STRIP LENGTH
SCALE: N.T.S.



- FOR USE WITH RG-316 DB COAX CABLE.
- FERRULE CRIMPING TOOL: AMP TOOL #608650-1, DANIEL'S DIE Y159 OR .197x.375.
- CONTACT CRIMPING TOOL:M22520/2-01 OR AMP TOOL NUMBER 601966-1, SETTING NUMBER 5. DANIELS POSITIONER PART NO. K345 OR AMP TOOL NO. 1-601966-6.
- SEE I.S.2348.
- DANIELS MANUFACTURING CORP
2266 FRANKLIN ROAD
BLOOMFIELD HILLS, MI 48013
- △ OUTER JACKET OF CABLE MUST BE TRIMMED TO ALLOW PROPER INTER-PIN CONTACT LOCATION AFTER FERRULE CRIMP OPERATION.
- PARTS SHIPPED UNASSEMBLED AND CABLE IS SUPPLIED BY CUSTOMER.

225790-8

PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN C.C.THOMAS 9-25-92		 Tyco Electronics Corporation Harrisburg, PA 17105-3608							
		CHK J.CABARLO 10-13-92									
DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME		CONNECTOR,COAXIAL,RF PIN SIZE 5, ARINC (HEX CRIMP)					
		APVD —		PRODUCT SPEC —							
		—									
		APPLICATION SPEC —									
MATERIAL		FINISH		SIZE	CAGE CODE	DRAWING NO		RESTRICTED TO			
SEE CALLOUTS		SEE CALLOUTS		WEIGHT —	A2	00779	C=225790-8		—		
CUSTOMER DRAWING				SCALE		5:1		SHEET		1 of 1	
								REV		A	