




MATERIAL NO.	ENGINEERING NO.	ELECTRICAL RATING
1300190023	43305	VOLTAGE: 600VAC, CURRENT: 25 AMPS



CONDUIT OPENING
1/2 - 14 PIPE THRD.



MOUNTING PLAN

ITEM	QTY.	DESCRIPTION	MATERIAL	FINISH
11	A/R	OVERMOLD	PVC	ORANGE
10	4	LOCKWASHER	STEEL	ZINC PLATED
9	2	SCREW, 1/4-20 X 1.00"-ROUND HEAD	STEEL	ZINC PLATED
8	2	SCREW, 1/4-20 X 3/8"-ROUND HEAD	STEEL	ZINC PLATED
7	1	GASKET	NEOPRENE	
6	1	PLATE	ALUMINUM	
5	1	MOUNTING SHELL	ALUMINUM	
4	1	MOUNTING BASE	ALUMINUM	
3	4	6-32 SCREW	BRASS	
2	4	FLAT WASHER	FIBRE	
1	4	SOCKET ASSEMBLY	BRASS	

NEW SALES DOC EC NO: IPG2013-0880 DRAWN BY: DRWINRSTONE 2013/01/21 CHKD.K.: JOZWIK 2013/01/25 APPR: JFMURPHY 2013/03/01 A	QUALITY SYMBOLS ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE IN/MM		SCALE 1:1	DESIGN UNITS INCH	THIRD ANGLE PROJECTION	
		mm INCH		DRAWN BY: RSTONE DATE: 2013/01/21		TITLE DIE BLOCK-CAST RECEPT. FEMALE STATIONARY CONN. 4 POLE ORANGE molex		DOCUMENT NO. SD-130019-005	
		4 PLACES ± --- ± ---		CHECKED BY: K. JOZWIK DATE: 2013/01/25					
		3 PLACES ± --- ± ---		APPROVED BY: JFMURPHY DATE: 2013/03/01					
2 PLACES ± --- ± .02		MATERIAL NO.		SEE CHART		SHEET NO. 1 OF 1			
1 PLACE ± 0.5 ± ---		ANGULAR ± 2 °		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION			
0 PLACE ± --- ± ---									