



SMT Power Inductors - DO5010H Series



- Irms ratings up to 15 A; saturation currents up to 30 A
- Heavy gauge wire for low DC resistance

Designer's Kit C355 contains 3 of each part

Core material Ferrite

Core and winding loss See www.coilcraft.com/coreloss

Terminations RoHS compliant tin-silver over copper. Other terminations available at additional cost.

Weight 3.2 – 4.0 g

Ambient temperature –40°C to +85°C with Irms current, +85°C to +125°C with derated current

Storage temperature Component: –40°C to +125°C.
Packaging: –40°C to +80°C

Resistance to soldering heat Max three 40 second reflows at +260°C, parts cooled to room temperature between cycles

Moisture Sensitivity Level (MSL) 1 (unlimited floor life at <30°C / 85% relative humidity)

Failures in Time (FIT) / Mean Time Between Failures (MTBF)
38 per billion hours / 26,315,789 hours, calculated per Telcordia SR-332

Packaging 250 per 13" reel Plastic tape: 32 mm wide, 0.38 mm thick, 24 mm pocket spacing, 7.8 mm pocket depth

PCB washing Only pure water or alcohol recommended

Part Number ¹	Inductance ² ±20% (µH)	DCR max (mOhm)	SRF typ ³ (MHz)	Isat ⁴ (A)	Irms ⁵ (A)
DO5010H-781ML	0.78	2.6	156	30	15
DO5010H-152ML	1.5	4.0	100	25	15
DO5010H-222ML	2.2	6.1	75	20	12
DO5010H-332ML	3.3	8.6	60	17	10
DO5010H-392ML	3.9	10	55	15	9.0
DO5010H-472ML	4.7	14	40	13	8.4
DO5010H-602ML	6.0	17	35	12	7.5
DO5010H-782ML	7.8	18	35	11	7.5
DO5010H-103ML	10	26	28	10	6.0
DO5010H-123ML	12	28	26	8.5	5.2
DO5010H-153ML	15	32	20	8.0	4.4
DO5010H-223ML	22	47	20	7.0	3.5
DO5010H-333ML	33	66	15	5.5	3.0
DO5010H-473ML	47	86	9	4.5	2.6
DO5010H-683ML	68	130	8	3.5	2.3
DO5010H-104ML	100	190	7	3.0	1.8
DO5010H-154ML	150	250	6	2.6	1.5
DO5010H-224ML	220	380	5	2.4	1.2
DO5010H-334ML	330	560	4	1.9	1.0
DO5010H-474ML	470	850	3	1.4	0.82
DO5010H-684ML	680	1100	2.5	1.2	0.72
DO5010H-105ML	1000	1800	2.0	1.0	0.56

1. When ordering, please specify **termination** and **packaging** codes:

DO5010H-105ML D

Termination: L = RoHS compliant tin-silver over copper.

Special order: T = RoHS tin-silver-copper (95.5/4/0.5) or
S = non-RoHS tin-lead (63/37).

Packaging: D = 13" machine-ready reel. EIA-481 embossed plastic tape.

B = Less than full reel. In tape, but not machine ready.
To have a leader and trailer added (\$25 charge), use code letter D instead.

- Inductance tested at 100 kHz, 0.1 Vrms using an Agilent/HP 4284A LCR meter or equivalent.
 - SRF measured using Agilent/HP 8753D network analyzer.
 - DC current at which the inductance drops 10% (typ) from its value without current.
 - Current that causes a 40°C temperature rise from 25°C ambient.
 - Electrical specifications at 25°C.
- Refer to Doc 362 "Soldering Surface Mount Components" before soldering.

Coilcraft®

Specifications subject to change without notice.
Please check our website for latest information.

Document 284-1 Revised 10/14/08

1102 Silver Lake Road Cary, Illinois 60013 Phone 847/639-6400 Fax 847/639-1469


E-mail info@coilcraft.com Web <http://www.coilcraft.com>




SMT Power Inductors - DO5010H Series

SPICE models ON OUR WEB SITE OR CD




Typical L vs Frequency



Typical L vs Current



Irms Derating



Part marking since Feb. 2005. Parts manufactured prior to that date may have color dots.
Visit www.coilcraft.com/colpowr.cfm for details.

Dimensions are in $\frac{\text{inches}}{\text{mm}}$

Coilcraft®

Specifications subject to change without notice.
Please check our website for latest information.

Document 284-2 Revised 10/14/08

1102 Silver Lake Road Cary, Illinois 60013 Phone 847/639-6400 Fax 847/639-1469

E-mail info@coilcraft.com Web <http://www.coilcraft.com>