





MATERIAL NUMBER	ENGINEERING NUMBER	MATERIAL NUMBER ON TAPE	ENGINEERING NUMBER ON TAPE	AWG	COLOR CODE	MWID	"ID" MIN	"L" MAX	"A" MIN	H ±.01/.3
I91640052	SBRA-8156N	N/A	N/A	22-18	RED	.13/3.3	.156/3.96	1.58/40.1	.235/5.97	N/A
I91640053	SBRA-8180N	N/A	N/A	22-18	RED	.13/3.3	.180/4.57	1.60/40.6	.235/5.97	N/A
I91640054	SBRB-8156N	I91640414	SBRB-8156NT	16-14	BLUE	.15/3.81	.156/3.96	1.60/40.6	.230/5.84	.39/9.9
I91640055	SBRB-8180N	N/A	N/A	16-14	BLUE	.15/3.81	.180/4.57	1.60/40.6	.230/5.84	N/A

ⓓ



PARTS ON TAPE

INSULATION: NYLON

FEMALE RECEPTACLE

FUNNEL FERRULE

MWID △3.

NIAC TUBING △2.

NOTES:

△1. TERMINAL
MATERIAL: COPPER
PLATING: TIN

△2. INSULATION
MATERIAL: HEAT SHRINKABLE
NIAC TUBING W/ HOT-MELT
ADHESIVE INNER LINER

△3. MWID= MAXIMUM WIRE INSULATION DIAMETER

CHANGED "A" DIM EC NO: ETC2006-0154 DRWN: ASAYDEH 2005/12/21 CHKD: JLOMASTR 2005/12/21 APPR: JPAWLICK 2005/12/21	QUALITY SYMBOLS	DESCRIPTION	GENERAL TOLERANCES (UNLESS SPECIFIED)		SCALE 1:1	DESIGN UNITS INCH	THIRD ANGLE PROJECTION		REVISE ON CAD ONLY							
					DIMENSION STYLE IN/MM		TITLE FULLY INSULATED AVIKRIMP PERMA-SEAL BULLET RECEPT .156/3.96-.180/4.57 DIA.									
			4 PLACES ± --- ± ---		DRAWN BY BENDERLE		DATE 2004/09/08		MOLEX MOLEX INCORPORATED							
			3 PLACES ± --- ± ---		CHECKED BY		DATE									
			2 PLACES ± .25 ± .01		R DEROSS		2004/09/08		MATERIAL NO. SEE CHART				DOCUMENT NO. SD-19164-035		SHEET NO. 1 OF 1	
			1 PLACE ± .5 ± .02		APPROVED BY		DATE									
			ANGULAR ± .5 °		R DEROSS		2004/09/08									
			DRAFT WHERE APPLICABLE													
			MUST REMAIN WITHIN DIMENSIONS													
					THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION				B							