




September 2015

# SMCJ5V0(C)A - SMCJ170(C)A 1500 Watt Transient Voltage Suppressors

## Features

- Glass-Passivated Junction
- 1500 W Peak Pulse Power Capability on 10/1000  $\mu$ s Waveform.
- Excellent Clamping Capability
- Low-Incremental Surge Resistance
- Fast Response Time: Typically Less than 1.0 ps from 0 V to BV Minimum for Unidirectional and 5.0 ns for Bidirectional
- Typical  $I_R$  Less than 1.0  $\mu$ A Above 10 V
- UL Certificate #E258596
- UL94V-0 Flammability Classification



SMC/DO-214AB

Band denotes cathode on unidirectional devices only. No band on bi-directional devices. Bi-directional types have CA suffix where electrical characteristics apply in both directions suitable for bi-directional applications.

## Absolute Maximum Ratings

Stresses exceeding the absolute maximum ratings may damage the device. The device may not function or be operable above the recommended operating conditions and stressing the parts to these levels is not recommended. In addition, extended exposure to stresses above the recommended operating conditions may affect device reliability. The absolute maximum ratings are stress ratings only. Values are at  $T_A = 25^\circ\text{C}$  unless otherwise noted.

| Symbol    | Parameter                                                                                          | Value      | Unit             |
|-----------|----------------------------------------------------------------------------------------------------|------------|------------------|
| $P_{PPM}$ | Peak Pulse Power Dissipation on 10/1000 $\mu$ s Waveform                                           | 1500       | W                |
| $I_{PPM}$ | Peak Pulse Current on 10/1000 $\mu$ s Waveform                                                     | See table  | A                |
| $I_{FSM}$ | Non-Repetitive Peak Forward Surge Current Superimposed on Rated Load (JEDEC Method) <sup>(1)</sup> | 200        | A                |
| $T_{STG}$ | Storage Temperature Range                                                                          | -55 to 150 | $^\circ\text{C}$ |
| $T_J$     | Operating Junction Temperature                                                                     | 150        | $^\circ\text{C}$ |

### Note:

1. Measured on 8.3 ms single half-sine wave or equivalent square wave: duty cycle = 4 pulses per minute maximum.

## Electrical Characteristics

Values are at  $T_A = 25^\circ\text{C}$  unless otherwise noted.

| Uni-Directional<br>Bi-Directional (C)<br>Device | Part<br>Marking <sup>(2)</sup> | Reverse<br>Stand-Off<br>Voltage<br>$V_{RWM}$ (V) | Breakdown<br>Voltage<br>$V_{BR}$ (V) |      | Test<br>Current<br>$I_T$ (mA) | Clamping<br>Voltage<br>at $I_{PPM}$<br>$V_C$ (V) | Peak Pulse<br>Current<br>$I_{PPM}$ (A) | Reverse<br>Leakage<br>at $V_{RWM}$<br>$I_R$ ( $\mu\text{A}$ ) <sup>(3)</sup> |
|-------------------------------------------------|--------------------------------|--------------------------------------------------|--------------------------------------|------|-------------------------------|--------------------------------------------------|----------------------------------------|------------------------------------------------------------------------------|
|                                                 |                                |                                                  | Min.                                 | Max. |                               |                                                  |                                        |                                                                              |
| SMCJ5V0(C)A                                     | GDE                            | 5.0                                              | 6.40                                 | 7.00 | 10                            | 9.2                                              | 163.0                                  | 1000                                                                         |
| SMCJ6V0(C)A                                     | GDG                            | 6.0                                              | 6.67                                 | 7.37 | 10                            | 10.3                                             | 145.6                                  | 1000                                                                         |
| SMCJ6V5(C)A                                     | GDK                            | 6.5                                              | 7.22                                 | 7.98 | 10                            | 11.2                                             | 133.9                                  | 500                                                                          |
| SMCJ7V0(C)A                                     | GDM                            | 7.0                                              | 7.78                                 | 8.60 | 10                            | 12.0                                             | 125.0                                  | 200                                                                          |
| SMCJ7V5(C)A                                     | GDP                            | 7.5                                              | 8.33                                 | 9.21 | 1                             | 12.9                                             | 116.3                                  | 100                                                                          |
| SMCJ8V0(C)A                                     | GDR                            | 8.0                                              | 8.89                                 | 9.83 | 1                             | 13.6                                             | 110.3                                  | 50                                                                           |
| SMCJ8V5(C)A                                     | GDT                            | 8.5                                              | 9.44                                 | 10.4 | 1                             | 14.4                                             | 104.2                                  | 20                                                                           |
| SMCJ9V0(C)A                                     | GDV                            | 9.0                                              | 10.0                                 | 11.1 | 1                             | 15.4                                             | 97.4                                   | 10                                                                           |
| SMCJ10(C)A                                      | GDX                            | 10                                               | 11.1                                 | 12.3 | 1                             | 17.0                                             | 88.2                                   | 5                                                                            |
| SMCJ11(C)A                                      | GDZ                            | 11                                               | 12.2                                 | 13.5 | 1                             | 18.2                                             | 82.4                                   | 5                                                                            |
| SMCJ12(C)A                                      | GEE                            | 12                                               | 13.3                                 | 14.7 | 1                             | 19.9                                             | 75.3                                   | 5                                                                            |
| SMCJ13(C)A                                      | GEG                            | 13                                               | 14.4                                 | 15.9 | 1                             | 21.5                                             | 69.8                                   | 5                                                                            |
| SMCJ14(C)A                                      | GEK                            | 14                                               | 15.6                                 | 17.2 | 1                             | 23.2                                             | 64.7                                   | 5                                                                            |
| SMCJ15(C)A                                      | GEM                            | 15                                               | 16.7                                 | 18.5 | 1                             | 24.4                                             | 61.5                                   | 5                                                                            |
| SMCJ16(C)A                                      | GEP                            | 16                                               | 17.8                                 | 19.7 | 1                             | 26.0                                             | 57.7                                   | 5                                                                            |
| SMCJ17(C)A                                      | GER                            | 17                                               | 18.9                                 | 20.9 | 1                             | 27.6                                             | 54.3                                   | 5                                                                            |
| SMCJ18(C)A                                      | GET                            | 18                                               | 20.0                                 | 22.1 | 1                             | 29.2                                             | 51.4                                   | 5                                                                            |
| SMCJ20(C)A                                      | GEV                            | 20                                               | 22.2                                 | 24.5 | 1                             | 32.4                                             | 46.3                                   | 5                                                                            |
| SMCJ22(C)A                                      | GEX                            | 22                                               | 24.4                                 | 26.9 | 1                             | 35.5                                             | 42.3                                   | 5                                                                            |
| SMCJ24(C)A                                      | GEZ                            | 24                                               | 26.7                                 | 29.5 | 1                             | 38.9                                             | 38.6                                   | 5                                                                            |
| SMCJ26(C)A                                      | GFE                            | 26                                               | 28.9                                 | 31.9 | 1                             | 42.1                                             | 35.6                                   | 5                                                                            |
| SMCJ28(C)A                                      | GFG                            | 28                                               | 31.1                                 | 34.4 | 1                             | 45.4                                             | 33.0                                   | 5                                                                            |
| SMCJ30(C)A                                      | GFK                            | 30                                               | 33.3                                 | 36.8 | 1                             | 48.4                                             | 31.0                                   | 5                                                                            |
| SMCJ33(C)A                                      | GFM                            | 33                                               | 36.7                                 | 40.6 | 1                             | 53.3                                             | 28.1                                   | 5                                                                            |
| SMCJ36(C)A                                      | GFP                            | 36                                               | 40.0                                 | 44.2 | 1                             | 58.1                                             | 25.8                                   | 5                                                                            |
| SMCJ40(C)A                                      | GFR                            | 40                                               | 44.4                                 | 49.1 | 1                             | 64.5                                             | 23.3                                   | 5                                                                            |
| SMCJ43(C)A                                      | GFT                            | 43                                               | 47.8                                 | 52.8 | 1                             | 69.4                                             | 21.6                                   | 5                                                                            |
| SMCJ45(C)A                                      | GFV                            | 45                                               | 50.0                                 | 55.3 | 1                             | 72.7                                             | 20.6                                   | 5                                                                            |
| SMCJ48(C)A                                      | GFX                            | 48                                               | 53.3                                 | 58.9 | 1                             | 77.4                                             | 19.4                                   | 5                                                                            |
| SMCJ51(C)A                                      | GFZ                            | 51                                               | 56.7                                 | 62.7 | 1                             | 82.4                                             | 18.2                                   | 5                                                                            |
| SMCJ54(C)A                                      | GGE                            | 54                                               | 60.0                                 | 66.3 | 1                             | 87.1                                             | 17.2                                   | 5                                                                            |
| SMCJ58(C)A                                      | GGG                            | 58                                               | 64.4                                 | 71.2 | 1                             | 93.6                                             | 16.0                                   | 5                                                                            |
| SMCJ60(C)A                                      | GGK                            | 60                                               | 66.7                                 | 73.7 | 1                             | 96.8                                             | 15.5                                   | 5                                                                            |
| SMCJ64(C)A                                      | GGM                            | 64                                               | 71.1                                 | 78.6 | 1                             | 103.0                                            | 14.6                                   | 5                                                                            |
| SMCJ70(C)A                                      | GGP                            | 70                                               | 77.8                                 | 86.0 | 1                             | 113.0                                            | 13.3                                   | 5                                                                            |
| SMCJ75(C)A                                      | GGR                            | 75                                               | 83.3                                 | 92.1 | 1                             | 121.0                                            | 12.4                                   | 5                                                                            |
| SMCJ78(C)A                                      | GGT                            | 78                                               | 86.7                                 | 95.8 | 1                             | 126.0                                            | 11.9                                   | 5                                                                            |

### Notes:

2. Color band denotes cathode on unidirectional devices only. No color band on bidirectional devices.
3. For bidirectional parts with  $V_{RWM} < 10\text{ V}$ , the  $I_R$  max limit is doubled.

**Electrical Characteristics** (Continued)Values are at  $T_A = 25^\circ\text{C}$  unless otherwise noted.

| Uni-Directional<br>Bi-Directional (C)<br>Device | Part<br>Marking <sup>(2)</sup> | Reverse<br>Stand-Off<br>Voltage<br>$V_{RWM}$ (V) | Breakdown<br>Voltage<br>$V_{BR}$ (V) |       | Test<br>Current<br>$I_T$ (mA) | Clamping<br>Voltage<br>at $I_{PPM}$<br>$V_C$ (V) | Peak Pulse<br>Current<br>$I_{PPM}$ (A) | Reverse<br>Leakage<br>at $V_{RWM}$<br>$I_R$ ( $\mu\text{A}$ ) <sup>(3)</sup> |
|-------------------------------------------------|--------------------------------|--------------------------------------------------|--------------------------------------|-------|-------------------------------|--------------------------------------------------|----------------------------------------|------------------------------------------------------------------------------|
|                                                 |                                |                                                  | Min.                                 | Max.  |                               |                                                  |                                        |                                                                              |
| SMCJ85(C)A                                      | GGV                            | 85                                               | 94.4                                 | 104.0 | 1                             | 137.0                                            | 10.9                                   | 5                                                                            |
| SMCJ90(C)A                                      | GGX                            | 90                                               | 100.0                                | 111.0 | 1                             | 146.0                                            | 10.3                                   | 5                                                                            |
| SMCJ100(C)A                                     | GGZ                            | 100                                              | 111.0                                | 123.0 | 1                             | 162.0                                            | 9.3                                    | 5                                                                            |
| SMCJ110(C)A                                     | GHE                            | 110                                              | 122.0                                | 135.0 | 1                             | 177.0                                            | 8.5                                    | 5                                                                            |
| SMCJ120(C)A                                     | GHG                            | 120                                              | 133.0                                | 147.0 | 1                             | 193.0                                            | 7.8                                    | 5                                                                            |
| SMCJ130(C)A                                     | GHK                            | 130                                              | 144.0                                | 159.0 | 1                             | 209.0                                            | 7.2                                    | 5                                                                            |
| SMCJ150(C)A                                     | GHM                            | 150                                              | 167.0                                | 185.0 | 1                             | 243.0                                            | 6.2                                    | 5                                                                            |
| SMCJ160(C)A                                     | GHP                            | 160                                              | 178.0                                | 197.0 | 1                             | 259.0                                            | 5.8                                    | 5                                                                            |
| SMCJ170(C)A                                     | GHR                            | 170                                              | 189.0                                | 209.0 | 1                             | 275.0                                            | 5.5                                    | 5                                                                            |

**Notes:**

2. Color band denotes cathode on unidirectional devices only. No color band on bidirectional devices.
3. For bidirectional parts with  $V_{RWM} < 10$  V, the  $I_R$  max limit is doubled.

## Typical Performance Characteristics




Figure 1. Peak Pulse Power Rating Curve




Figure 2. Pulse Derating Curve




Figure 3. Pulse Waveform




Figure 4. Junction Capacitance





Figure 5. Non-Repetitive Surge Current

## Physical Dimension





## TRADEMARKS

The following includes trademarks registered and unregistered trademarks and service marks, owned by Fairchild Semiconductor and/or its global subsidiaries, and is not intended to be an exhaustive list of all such trademarks.

AccuPower™  
AttitudeEngine™  
Awinda®  
AX-CAP®  
BitSiC™  
Build it Now™  
CorePLUS™  
CorePOWER™  
CROSSVOLT™  
CTL™  
Current Transfer Logic™  
DEUXPEED®  
Dual Cool™  
EcoSPARK®  
EfficientMax™  
ESBC™  
F®  
Fairchild®  
Fairchild Semiconductor®  
FACT Quiet Series™  
FACT®  
FastvCore™  
FETBench™  
FPS™

F-PFS™  
FRFET®  
Global Power Resource™  
GreenBridge™  
Green FPS™  
Green FPS™ e-Series™  
Gmax™  
GTO™  
IntelliMAX™  
ISOPLANAR™  
Making Small Speakers Sound Louder and Better™  
MegaBuck™  
MICROCOUPLER™  
MicroFET™  
MicroPak™  
MicroPak2™  
MillerDrive™  
MotionMax™  
MotionGrid™  
MTi®  
MTx®  
MVN®  
mWSaver®  
OptoHiT™  
OPTOLOGIC®

OPTOPLANAR®  
Power Supply WebDesigner™  
PowerTrench®  
PowerXS™  
Programmable Active Droop™  
QFET®  
QS™  
Quiet Series™  
RapidConfigure™  
Saving our world, 1mW/W/kW at a time™  
SignalWise™  
SmartMax™  
SMART START™  
Solutions for Your Success™  
SPM®  
STEALTH™  
SuperFET®  
SuperSOT™-3  
SuperSOT™-6  
SuperSOT™-8  
SupreMOS®  
SyncFET™  
Sync-Lock™

SYSTEM GENERAL®  
TinyBoost®  
TinyBuck®  
TinyCalc™  
TinyLogic®  
TINYOPTO™  
TinyPower™  
TinyPWM™  
TinyWire™  
TranSiC™  
TriFault Detect™  
TRUECURRENT®  
µSerDes™  
SerDes®  
UHC®  
Ultra FRFET™  
UniFET™  
VCX™  
VisualMax™  
VoltagePlus™  
XS™  
Xsens™  
仙童™

\* Trademarks of System General Corporation, used under license by Fairchild Semiconductor.

## DISCLAIMER

FAIRCHILD SEMICONDUCTOR RESERVES THE RIGHT TO MAKE CHANGES WITHOUT FURTHER NOTICE TO ANY PRODUCTS HEREIN TO IMPROVE RELIABILITY, FUNCTION, OR DESIGN. TO OBTAIN THE LATEST, MOST UP-TO-DATE DATASHEET AND PRODUCT INFORMATION, VISIT OUR WEBSITE AT [HTTP://WWW.FAIRCHILDSEMI.COM](http://www.fairchildsemi.com). FAIRCHILD DOES NOT ASSUME ANY LIABILITY ARISING OUT OF THE APPLICATION OR USE OF ANY PRODUCT OR CIRCUIT DESCRIBED HEREIN; NEITHER DOES IT CONVEY ANY LICENSE UNDER ITS PATENT RIGHTS, NOR THE RIGHTS OF OTHERS. THESE SPECIFICATIONS DO NOT EXPAND THE TERMS OF FAIRCHILD'S WORLDWIDE TERMS AND CONDITIONS, SPECIFICALLY THE WARRANTY THEREIN, WHICH COVERS THESE PRODUCTS.

## AUTHORIZED USE

Unless otherwise specified in this data sheet, this product is a standard commercial product and is not intended for use in applications that require extraordinary levels of quality and reliability. This product may not be used in the following applications, unless specifically approved in writing by a Fairchild officer: (1) automotive or other transportation, (2) military/aerospace, (3) any safety critical application – including life critical medical equipment – where the failure of the Fairchild product reasonably would be expected to result in personal injury, death or property damage. Customer's use of this product is subject to agreement of this Authorized Use policy. In the event of an unauthorized use of Fairchild's product, Fairchild accepts no liability in the event of product failure. In other respects, this product shall be subject to Fairchild's Worldwide Terms and Conditions of Sale, unless a separate agreement has been signed by both Parties.

## ANTI-COUNTERFEITING POLICY

Fairchild Semiconductor Corporation's Anti-Counterfeiting Policy. Fairchild's Anti-Counterfeiting Policy is also stated on our external website, [www.fairchildsemi.com](http://www.fairchildsemi.com), under Terms of Use

Counterfeiting of semiconductor parts is a growing problem in the industry. All manufacturers of semiconductor products are experiencing counterfeiting of their parts. Customers who inadvertently purchase counterfeit parts experience many problems such as loss of brand reputation, substandard performance, failed applications, and increased cost of production and manufacturing delays. Fairchild is taking strong measures to protect ourselves and our customers from the proliferation of counterfeit parts. Fairchild strongly encourages customers to purchase Fairchild parts either directly from Fairchild or from Authorized Fairchild Distributors who are listed by country on our web page cited above. Products customers buy either from Fairchild directly or from Authorized Fairchild Distributors are genuine parts, have full traceability, meet Fairchild's quality standards for handling and storage and provide access to Fairchild's full range of up-to-date technical and product information. Fairchild and our Authorized Distributors will stand behind all warranties and will appropriately address any warranty issues that may arise. Fairchild will not provide any warranty coverage or other assistance for parts bought from Unauthorized Sources. Fairchild is committed to combat this global problem and encourage our customers to do their part in stopping this practice by buying direct or from authorized distributors.

## PRODUCT STATUS DEFINITIONS

### Definition of Terms

| Datasheet Identification | Product Status        | Definition                                                                                                                                                                                          |
|--------------------------|-----------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Advance Information      | Formative / In Design | Datasheet contains the design specifications for product development. Specifications may change in any manner without notice.                                                                       |
| Preliminary              | First Production      | Datasheet contains preliminary data; supplementary data will be published at a later date. Fairchild Semiconductor reserves the right to make changes at any time without notice to improve design. |
| No Identification Needed | Full Production       | Datasheet contains final specifications. Fairchild Semiconductor reserves the right to make changes at any time without notice to improve the design.                                               |
| Obsolete                 | Not In Production     | Datasheet contains specifications on a product that is discontinued by Fairchild Semiconductor. The datasheet is for reference information only.                                                    |

Rev. 176

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Fairchild Semiconductor:](#)

[SMCJ58A](#)