




1. SEE CURRENT CATALOG FOR ADDITIONAL PART SUFFIXES TO INDICATE COLOR AND/OR PACKAGE QUANTITY.
2. THE FIBER-DUCT 2x2 AND FIBERRUNNER 2x2 3-SIDED BEND RADIUS CONTROL TRUMPET IS DESIGNED WITH A MINIMUM 2" (50.8) BEND RADIUS TO PROTECT FIBER OPTIC CABLES.
3. DIMENSIONS IN PARENTHESES ARE IN METRIC.



CAD_FILENAME/LAYERS

△
F

FTR2X2.pdf

PANDUIT

CORP TINLEY PARK, ILLINOIS

FIBER-DUCT 2x2 AND FIBERRUNNER 2x2
3-SIDED BEND RADIUS CONTROL
TRUMPET (FTR2X2)

CUSTOMER DRAWING

UNLESS OTHERWISE SPECIFIED,
DIMENSIONAL TOLERANCES ARE:

UNLESS OTHERWISE SPECIFIED,
ALL DIMENSIONS ARE GIVEN IN
INCHES, THIRD ANGLE PROJECTION.

$$\begin{array}{l} (.X) \pm \quad \quad \quad (.XXX) \pm \\ (.XX) \pm .03 \quad (.8) \quad \quad \quad \text{ANGLES} \pm \end{array}$$

DRAWN BY JHNU

DATE	1-19-01
------	---------

MAT'L:	
--------	--

ABS

SCALE	NONE
-------	------

DRAWING NO.
37617-88

DWG
A
SIZE

-	-----	---	---	H. REVISED PART WEIGHT	-----	--	--		
-	-----	---	---	G. REVISED GENERAL NOTES F. REVISED CAD FILENAME	-----	--	--		
3	7-21-06	DTP	RN	E. REVISED DRAWING TITLE D. REVISED AND REDRAWN	37617-88	RN	RN		
REV	DATE	BY	CHK	DESCRIPTION	ECN	- R	CUST	SUP	GMB