

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

50394-8054

Status:

Active

Overview:

Milli-Grid™ Connector System

Description:

Milli-Grid™ Crimp Terminal, Reel, Gold (Au) Flash, Lead free

Documents:

3D Model

Drawing (PDF)

Product Specification PS-51110-001 (PDF)

RoHS Certificate of Compliance (PDF)

Product Literature (PDF)

General

Product Family

Series

Application

Crimp Quality Equipment

Overview

Product Literature Order No

Product Name

UPC

Crimp Terminals

50394

Signal

Yes

Milli-Grid™ Connector System

987650-1991

Milli-Grid™

756054436530

Physical

Gender

Material - Metal

Material - Plating Mating

Material - Plating Termination

Net Weight

Packaging Type

Plating min - Mating

Plating min - Termination

Termination Interface: Style

Wire Insulation Diameter

Wire Size AWG

Wire Size mm²

Female

Phosphor Bronze

Gold

Nickel

0.023/g

Reel

0.051µm

2.032µm

Crimp or Compression

1.40mm max.

24, 26, 28, 30

N/A

Material Info


Reference - Drawing Numbers

Product Specification

Sales Drawing

PS-51110-001

SD-50394-8***



EU RoHS

ELV and RoHS

Compliant

REACH SVHC

Contains SVHC: No

Low-Halogen Status

Low-Halogen

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

50394Series

Use With

51110 Crimp Housing

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global	
Description	Product #
FineAdjust™ Applicator for 2.00mm Pitch Wire-to-Board Crimp Terminals 24-30 AWG	0639005200
T2 Terminator Die	0639105200
Hand Crimp Tool for Crimp Terminals	0638190100

This document was generated on 04/26/2013

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION