



OptiMOS[®]-P Small-Signal-Transistor
Features

- Dual P-Channel in SO8
- Enhancement mode
- Logic level
- 150°C operating temperature
- Qualified according JEDEC for target applications
- Halogen-free according to IEC61249-2-21
- Pb-free lead plating; RoHS compliant


SO 8


Type	Package	Marking	Lead free	Halogen free	Packing
BSO303P H	PG-DSO- 8	303P	Yes	Yes	dry

Maximum ratings, at $T_j=25\text{ °C}$, unless otherwise specified

Parameter	Symbol	Conditions	Value		Unit
			10 secs	steady state	
Continuous drain current ¹⁾	I_D	$T_C=25\text{ °C}$	-8,2	-7,0	A
		$T_C=70\text{ °C}$	-6,6	-5,8	
Pulsed drain current ²⁾	$I_{D,pulse}$	$T_C=25\text{ °C}$	-32,8		
Avalanche energy, single pulse	E_{AS}	$I_D=-8.2\text{ A}$, $R_{GS}=25\text{ }\Omega$	97		mJ
Gate source voltage	V_{GS}		± 20		V
Power dissipation	P_{tot}	$T_A=25\text{ °C}$	2		W
Operating and storage temperature	T_j , T_{stg}		-55 ... 150		°C
ESD class		JESD22-A114 HBM	1B (500V - 1kV)		
Soldering temperature			260 °C		
IEC climatic category; DIN IEC 68-1			55/150/56		

Parameter	Symbol	Conditions	Values			Unit
			min.	typ.	max.	

Thermal characteristics

Thermal resistance, junction - soldering point	R_{thJS}		-	-	50	K/W
SMD version, device on PCB:	R_{thJA}	minimal footprint, $t < 10s$			110	
		minimal footprint, steady state			150	
		6 cm ² cooling area ¹⁾ , $t < 10s$	-	-	62,5	
		6 cm ² cooling area ¹⁾ , steady state	-	-	80	

Electrical characteristics, at $T_j = 25^\circ C$, unless otherwise specified

Static characteristics

Drain-source breakdown voltage	$V_{(BR)DSS}$	$V_{GS} = 0 V, I_D = -250 \mu A$	-30	-	-	V
Gate threshold voltage	$V_{GS(th)}$	$V_{DS} = V_{GS}, I_D = -100 \mu A$	-1	-1,5	-2	
Zero gate voltage drain current	I_{DSS}	$V_{DS} = -30 V, V_{GS} = 0 V, T_j = 25^\circ C$	-	-0,1	-1	μA
		$V_{DS} = -30 V, V_{GS} = 0 V, T_j = 150^\circ C$	-	-10	-100	
Gate-source leakage current	I_{GSS}	$V_{GS} = -20 V, V_{DS} = 0 V$	-	-	-100	nA
Drain-source on-state resistance	$R_{DS(on)}$	$V_{GS} = -4.5 V, I_D = -6.6 A$	-	25	32	mW
		$V_{GS} = -10 V, I_D = -8.2 A$	-	17	21	
Transconductance	g_{fs}	$ V_{DS} > 2 I_D /R_{DS(on)max}, I_D = -6.6 A$	11	27	-	S

¹⁾ Device on 40 mm x 40 mm x 1.5 mm epoxy PCB FR4 with 6 cm² (one layer, 70 μm thick) copper area for drain connection. PCB is vertical without blown air: $t \leq 10$ sec.

²⁾ See figure3 for more detailed information

Parameter	Symbol	Conditions	Values			Unit
			min.	typ.	max.	

Dynamic characteristics

Input capacitance	C_{iss}	$V_{GS}=0\text{ V}, V_{DS}=-25\text{ V},$ $f=1\text{ MHz}$	-	1785	2678	pF
Output capacitance	C_{oss}		-	510	765	
Reverse transfer capacitance	C_{rss}		-	425	638	
Turn-on delay time	$t_{d(on)}$	$V_{DD}=-15\text{ V}, V_{GS}=-10\text{ V}, I_D=-1\text{ A},$ $R_G=6\ \Omega$	-	11	17	ns
Rise time	t_r		-	13	20	
Turn-off delay time	$t_{d(off)}$		-	55	83	
Fall time	t_f		-	39	59	

Gate Charge Characteristics³⁾


Gate to source charge	Q_{gs}	$V_{DD}=-24\text{ V}, I_D=-8.2\text{ A},$ $V_{GS}=0\text{ to }10\text{ V}$	-	-5	-6	nC
Gate to drain charge	Q_{gd}		-	-14	-20	
Gate charge total	Q_g		-	-36	-49	
Gate plateau voltage	$V_{plateau}$		-	-2,7	-	V

Reverse Diode

Diode continuous forward current	I_S	$T_C=25\text{ °C}$	-	-	-2,2	A
Diode direct current, pulsed	I_{SM}		-	-	-32,8	
Diode forward voltage	V_{SD}	$V_{GS}=0\text{ V}, I_F=-8.2\text{ A},$ $T_J=25\text{ °C}$	-	-0,9	-1,3	V
Reverse recovery time	t_{rr}	$V_R=-15\text{ V}, I_F= I_S ,$ $di_F/dt=100\text{ A}/\mu\text{s}$	-	24	36	ns
Reverse recovery charge	Q_{rr}		-	13	19	


1 Power dissipation

$$P_{\text{tot}} = f(T_A)$$



2 Drain current


$$I_D = f(T_A); |V_{GS}| \geq 10 \text{ V}$$



3 Safe operating area

$$I_D = f(V_{DS}); T_A = 25^\circ\text{C}^1; D = 0$$


parameter: t_p



4 Max. transient thermal impedance


$$Z_{\text{thJS}} = f(t_p)$$

parameter: $D = t_p/T$




5 Typ. output characteristics

 $I_D = f(V_{DS}); T_j = 25^\circ\text{C}$

parameter: V_{GS}



6 Typ. drain-source on resistance

 $R_{DS(on)} = f(I_D); T_j = 25^\circ\text{C}$


parameter: V_{GS}


7 Typ. transfer characteristics

 $I_D = f(V_{GS}); |V_{DS}| > 2|I_D|R_{DS(on)max}$


parameter: T_j


8 Typ. forward transconductance

 $g_{fs} = f(I_D); T_j = 25^\circ\text{C}$



9 Drain-source on-state resistance

$$R_{DS(on)} = f(T_j); I_D = -8.2 \text{ A}; V_{GS} = -10 \text{ V}$$




10 Typ. gate threshold voltage

$$V_{GS(th)} = f(T_j); V_{GS} = V_{DS}; I_D = -100 \text{ μA}$$



11 Typ. capacitances


$$C = f(V_{DS}); V_{GS} = 0 \text{ V}; f = 1 \text{ MHz}$$



12 Forward characteristics of reverse diode

$$I_F = f(V_{SD})$$


parameter: T_j



13 Avalanche characteristics

$$I_{AS}=f(t_{AV}); R_{GS}=25\ \Omega$$


parameter: $T_{j(\text{start})}$



14 Typ. gate charge


$$V_{GS}=f(Q_{gate}); I_D=-8.2\ \text{A pulsed}$$

parameter: V_{DD}




15 Drain-source breakdown voltage

$$V_{BR(DSS)}=f(T_j); I_D=-250\ \mu A$$




Package Outline

PG-DSO-8: Outline



1) DOES NOT INCLUDE MOLD FLASH OR PROTRUSIONS.

DIM	MILLIMETERS		INCHES	
	MIN	MAX	MIN	MAX
A	-	1.75	-	0.069
A1	0.10	-	0.004	-
A2	1.25	1.65	0.049	0.065
b	0.35	0.51	0.014	0.020
c	0.17	0.25	0.007	0.010
D	4.80	5.00	0.189	0.197
E	5.80	6.20	0.228	0.244
E1	3.80	4.00	0.150	0.157
e	1.27		0.050	
N	8		8	
L	0.39	0.89	0.015	0.035
h	0.23	0.50	0.009	0.020
Θ	0°	8°	0°	8°
Θ ₁	-	19°	-	19°
ccc	0.10		0.004	
ddd	0.25		0.010	
F1	5.59	5.79	0.220	0.228
F2	0.55	0.75	0.022	0.030
F3	1.21	1.41	0.048	0.056

DOCUMENT NO. Z8B00003333
SCALE 0 1.0 2mm
EUROPEAN PROJECTION 
ISSUE DATE 09.01.2008
REVISION 02

Published by
Infineon Technologies AG
81726 Munich, Germany
© 2009 Infineon Technologies AG
All Rights Reserved.

Legal Disclaimer

The information given in this document shall in no event be regarded as a guarantee of conditions or characteristics. With respect to any examples or hints given herein, any typical values stated herein and/or any information regarding the application of the device, Infineon Technologies hereby disclaims any and all warranties and liabilities of any kind, including without limitation, warranties of non-infringement of intellectual property rights of any third party.

Information

For further information on technology, delivery terms and conditions and prices, please contact the nearest Infineon Technologies Office (www.infineon.com).

Warnings

Due to technical requirements, components may contain dangerous substances. For information on the types in question, please contact the nearest Infineon Technologies Office.

Infineon Technologies components may be used in life-support devices or systems only with the express written approval of Infineon Technologies, if a failure of such components can reasonably be expected to cause the failure of that life-support device or system or to affect the safety or effectiveness of that device or system. Life support devices or systems are intended to be implanted in the human body or to support and/or maintain and sustain and/or protect human life. If they fail, it is reasonable to assume that the health of the user or other persons may be endangered.