

Address:
BLOCK 1, DEHUINA INDUSTRIAL DISTRICT,
MINGZHI RD LONGHUA, SHENZHEN,
GUANGDONG, CHINA 518131

TEL: (86) 755-8192552 8190943
FAX: (86) 755-8192557
E-mail: szwwiner@public.szptt.net.cn
HOME PAGE: www.globalsources.com/hornmic.co

CUSTOMER: Digi-Key Corporation

APPROVE SHEET

PRODUCT NAME	TYPE	DIMENSION	
Electret Condenser Microphone	EM8050U-51	Ø8.0×5.0(mm)	D.S.PCB

APPROVED :

李 華

DATE: 2000.11.25

CHECKED BY:

陳 為 波

DATE: 2000.11.25

ISSUED BY:

陳 為 波

DATE:



APPROVED BY

DATE:

Address:
BLOCK 1, DEHUINA INDUSTRIAL DISTRICT,
MINGZHI RD LONGHUA, SHENZHEN,
GUANGDONG, CHINA 518131


TEL: (86) 755-8192552 8190943
FAX: (86) 755-8192557
E-mail: szwwiner @ public.szptt.net.cn
HOME PAGE: www.globalsources.com/hornmic.co

SPECIFICATION

Item	Symbol	Test conditions	Min	Standard	Max	Unit
Sensitivity	S	f=1KHz. Pin=1pa	-54	-51	-47	dB 0dB=1V/pa
Directivity		Unidirectional				
Impedance	Zout				680	Ω
Current consumption	I	f=1KHz. Pin=1pa			500	uA
Sensitivity reduction	ΔS	f=1KHz. Pin=1pa. Vs=1.5→1V			-3	dB
S/N ratio	S/N(A)	f=1KHz. Pin=1pa. A=curve	58			dB

Measurement Circuit (Test Condition Vs=1.5V RL=680 Ω)

Ta=20°C R.H=65%)




Address:
BLOCK 1, DEHUNA INDUSTRIAL DISTRICT,
MINGZHI RD LONGHUA, SHENZHEN,
GUANGDONG, CHINA 518131

TEL: (86) 755-8192552 8190943
FAX: (86) 755-8192557
E-mail: szwwiner@public.szptt.net.cn
HOME PAGE: www.globalsources.com/hornmic.co

Dimensional Drawing

unit: mm



PART	MIN	TYPE	MAX	REMARK
A	Ø7.9	Ø8	Ø8.1	
B	4.8	5	5.2	
C	0.2	-	0.7	
D	Ø0.6	-	Ø0.8	

Typical Frequency Response Curve

