





REV.	DATE	DESCRIPTION
NC	07/22/02	INITIAL RELEASE
A	07/20/05	UPDATE DRAWING FORMAT



CRIMP NOTES:

1. CRIMPED FERRULE
HEX CRIMP SIZE .429"
2. CRIMPED CONTACT PIN
HEX CRIMP SIZE .100"

8				UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY.	APPROVALS	DATE	Amphenol Connex TNC CRIMP JACK (FOR RG-8, 213/U CABLE) PART NO. 122482
7				UNLESS OTHERWISE SPECIFIED, TOLERANCES FOR MILLIMETERS ARE:	DRAWN	G.R.S.	
6				0.5 - 8mm ± 0.20mm	CHECKED		
5				8 - 30mm ± 0.40mm	ISSUED		
4				30 - 120mm ± 0.50mm	SHEET	1 OF 1	
3	FERRULE	COPPER	NICKEL	UNLESS OTHERWISE SPECIFIED, TOLERANCES FOR INCHES ARE:			
2	CONTACT PIN	PHOS. BRONZE	GOLD	.020 - .315 = ± 0.007"			
1	INSULATOR	TEFLON	NATURAL	.315 - 1.180 = ± 0.015"			
	BODY	BRASS	NICKEL	1.180 - 4.724 = ± 0.020"			
	DESCRIPTION	MATERIAL	FINISH	QTY	DO NOT SCALE DRAWING	CAD FILE	DWG. NO.
						C:/122/122482.DWG	122482.DWG
							REV. A
							SIZE A
							SCALE NA