



✓ Active

TE CONNECTIVITY (TE)

MQS BU-GEH,ASSY 6P

AMP | MQS

1355082-2

TE Internal Number: 1355082-2

EU RoHS Compliant

EU ELV Compliant

Connector Style Housing for female terminals

Mating Tab Width .63 mm [.025 in]

Connector System Wire-to-Board, Wire-to-Device, Wire-to-Wire

Number of Positions 6

Centerline (Pitch) 2.85 mm [.112 in]

PRODUCT DRAWING
English

3D PDF

DOCUMENTATION

Product Drawings

MICRO QUADLOK SOCKET-HSG., 6POSN. + RETAINER (KIT)

PDF

English

CAD Files

3D PDF

PDF

3D

Customer View Model

2D_DXF.ZIP

English

Customer View Model

3D_IGS.ZIP

English

Customer View Model

3D_STP.ZIP

English

FEATURES



Please review product documents or [contact us](#) for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

Product Type Features

Connector Style Housing for female terminals

Connector System Wire-to-Board, Wire-to-Device, Wire-to-Wire

Sealable No

Hybrid Connector No

Primary Locking Feature On the terminal

Strain Relief No

Configuration Features

Number of Positions 6

Number of Rows 1

Electrical Characteristics

Nominal Voltage Architecture (V) 12

Operating Voltage (VDC) 12

Body Features

Color Brown

Cable Exit Angle Other

Body Material PBT GF

Contact Features

Mating Tab Width .63 mm [.025 in]

Mechanical Attachment

Mounting Feature No

Terminal Position Assurance Yes

Polarized Yes

Housing Features

Centerline (Pitch) 2.85 mm [.112 in]

Dimensions

Width 19 mm [.748 in]
Height 14.75 mm [.581 in]
Length 24.4 mm [.961 in]

Usage Conditions

Operating Temperature Range -40 – 80 °C [-40 – 176 °F]

Operation/Application

Circuit Application Signal

Industry Standards

Degree of Protection Other
UL Flammability Rating UL 94-HB

Packaging Features

Packaging Method Kit

Other

Connector Position Assurance Capable No
Serviceable Yes

PRODUCT COMPLIANCE



Statement of Compliance

[Statement of Compliance](#)

PDF