




	1	2	3	4	5	6	7																																																																																				
A								A																																																																																			
B								B																																																																																			
C								C																																																																																			
D	Notes: - E243711 (UL) SVT 3x18AWG(0.824mm²) VW-1 60°C 300V CSA 228191 SVT 3x18AWG(0.824mm²) FT2 60°C 300V -LF- - Jacket color: Black - E-Green; L-Black; N-White							D																																																																																			
E	 CONDUCTOR CONSTRUCTION(N/mm): 41/0.16AS PVC INSULATION AVERAGE THICKNESS: 0.38mm ID: 2.10±0.1mm F III PVC JACKET AVERAGE THICKNESS: 0.76mm OD: 6.50±0.15mm							E																																																																																			
F	Electrical: 100% open and short testing - Insulation Resistance: 100MΩ Min. - Voltage: 500V DC/1min 							F																																																																																			
G	<table><tr><td>Scale</td><td>Free</td><td></td><td></td><td></td><td></td><td>Date</td><td>Name</td><td rowspan="2">Title Power cord Right angle to Open, 3 Meters, SVT</td></tr><tr><td>TOLERANCE</td><td></td><td></td><td></td><td></td><td></td><td>Drawn</td><td>23.04.14</td></tr><tr><td>X.</td><td>±0.3</td><td></td><td></td><td></td><td></td><td>Approved</td><td>23.04.14</td><td rowspan="2">ASSMANN WSW-No. A-PC1504-030021-1</td></tr><tr><td>X.X</td><td>±X</td><td></td><td></td><td></td><td></td><td></td><td></td></tr><tr><td>X.XX</td><td>±X</td><td></td><td></td><td></td><td></td><td></td><td></td><td rowspan="2">Drawing-No.</td></tr><tr><td>DIM</td><td>TOL</td><td></td><td></td><td></td><td></td><td></td><td></td></tr><tr><td>X.°</td><td>±X°</td><td></td><td></td><td></td><td></td><td></td><td></td><td rowspan="2">rev00</td></tr><tr><td>X.X°</td><td>±X°</td><td></td><td></td><td></td><td></td><td></td><td></td></tr><tr><td>Angle</td><td>TOL</td><td>Id.</td><td>Modification</td><td>Date</td><td>Name</td><td colspan="2" rowspan="3"> ASSMANN WSW components 1840 W. Drake Drive, Suite 101 • Tempe, AZ 85283 Toll Free: 1-877-277-6266 • Email: info@assmann.us </td><td rowspan="2">Sheet 1/1</td></tr><tr><td></td><td></td><td></td><td></td><td></td><td></td></tr></table>							Scale	Free					Date	Name	Title Power cord Right angle to Open, 3 Meters, SVT	TOLERANCE						Drawn	23.04.14	X.	±0.3					Approved	23.04.14	ASSMANN WSW-No. A-PC1504-030021-1	X.X	±X							X.XX	±X							Drawing-No.	DIM	TOL							X.°	±X°							rev00	X.X°	±X°							Angle	TOL	Id.	Modification	Date	Name	ASSMANN WSW components 1840 W. Drake Drive, Suite 101 • Tempe, AZ 85283 Toll Free: 1-877-277-6266 • Email: info@assmann.us		Sheet 1/1							G
Scale	Free					Date	Name	Title Power cord Right angle to Open, 3 Meters, SVT																																																																																			
TOLERANCE						Drawn	23.04.14																																																																																				
X.	±0.3					Approved	23.04.14	ASSMANN WSW-No. A-PC1504-030021-1																																																																																			
X.X	±X																																																																																										
X.XX	±X							Drawing-No.																																																																																			
DIM	TOL																																																																																										
X.°	±X°							rev00																																																																																			
X.X°	±X°																																																																																										
Angle	TOL	Id.	Modification	Date	Name	ASSMANN WSW components 1840 W. Drake Drive, Suite 101 • Tempe, AZ 85283 Toll Free: 1-877-277-6266 • Email: info@assmann.us		Sheet 1/1																																																																																			
H	Unit: mm RoHS Compliant							H																																																																																			
	1	2	3	4	5	6	7																																																																																				