






13	12	11	10	9	8	7	6	5	4	3	2	1
PART NUMBER	ENGINEERING NO.	LENGTH										
1300140067	2R8004A20F060	6' 0" +2.19 - 0 [1.8M +55.6 - 0]										
1300140061	2R8004A20A120	12' 0" +3.50 - 0 [3.7M +88.9 - 0]										



REF. KNOCK-OUT HOLE



- NOTES:
- 1. MATERIAL: SEE TABLE
 - 2. FINISHES: SEE TABLE
 - 3. CABLE ASSEMBLIES ARE BAGGED SEPERATELY IN POLY BAGS WITH BARCODE LABEL ATTACHED TO OUTSIDE OF BAG
 - 4. WRAP LABEL IS MARKED WITH P/N, DATE CODE VOLTAGE & AMPERAGE
 - 5. MATES WITH: MINI CHANGE, C-SIZE 8 POLE CORDSET
 - 6. ELECTRICAL SPECIFICATIONS:
VOLTAGE RATING: 600V
CURRENT RATING: 7 AMPS
 - 7. ASSEMBLY IS RoHS COMPLIANT

1	ORANGE
2	BLUE
3	WHITE/BLACK
4	BLACK
5	WHITE
6	RED
7	GREEN/YELLOW-GND
8	RED/BLACK

WIRING DIAGRAM

7	1	LABEL	PLASTIC FILM	BLACK/YELLOW
6	1	POTTING	EPOXY	
5	7	WIRE, 16 AWG (UL 1015)	PVC INSULATED	SEE WIRE DIAGRAM
4	8	SOCKET SLEEVE	ST.STEEL	
3	8	CONTACT SOCKET	BRASS	GOLD PLATED
2	1	INSERT	PVC	YELLOW
1	1	RECEPTACLE SHELL	ZINC ALLOY	E-COAT, BLACK
ITEM	QTY.	DESCRIPTION	MATERIAL	FINISH

RELEASED	EC NO: WNA2009-0813	2009/06/09	DRWN:BRUPERT	2009/06/09	CHKD:BRUPERT	2009/06/10	APPR:JF MURPHY	2009/06/10
REV	A	DESCRIPTION	QUALITY SYMBOLS					
			▽=0					
			▽=0					

GENERAL TOLERANCES (UNLESS SPECIFIED)			
	mm	INCH	
4 PLACES	± ---	± ---	
3 PLACES	± ---	± ---	
2 PLACES	± ---	± .01	
1 PLACE	± 0.3	± ---	
ANGULAR ±1/2°			
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			

DRAWN BY	DATE
BRUPERT	2009/04/06
CHECKED BY	DATE
B.WOODMAN	2009/04/06
APPROVED BY	DATE
J.MURPHY	2009/04/06
MATERIAL NO.	
SEE CHART	
SIZE	C

SCALE	DESIGN UNITS	THIRD ANGLE PROJECTION	
1:1	INCH		
TITLE			
MINI-CHANGE CORD ASSY FEMALE, B-SIZE 8 POLE			
MOLEX INCORPORATED			
DOCUMENT NO.			SHEET NO.
SD-130014-007			1 OF 1
THIS INFORMATION THAT IS PROPRIETARY TO MOLEX SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION			