

	1	2	3	4	5	6	7																																																																																																																																																																					
A	③ 300ft(91.44m) red line AWM 2651 28AWG E350147 105°C 300V VW-1							A																																																																																																																																																																				
B								B																																																																																																																																																																				
C	0,85±0,1 1,27±0,07 A B							C																																																																																																																																																																				
D	<table><tr><th rowspan="2">Cores</th><th colspan="2">Size of conductor</th><th rowspan="2">A①</th><th rowspan="2">B①</th><th rowspan="2">Cores</th><th colspan="2">Size of conductor</th><th rowspan="2">A①</th><th rowspan="2">B①</th></tr><tr><th>AWG</th><th>Composition</th><th>AWG</th><th>Composition</th></tr><tr><td>02</td><td>28</td><td>7/0.127</td><td>1.27±0.15</td><td>2.54±0.15</td><td>18</td><td>28</td><td>7/0.127</td><td>21.59±0.30</td><td>22.86±0.30</td></tr><tr><td>03</td><td>28</td><td>7/0.127</td><td>2.54±0.15</td><td>3.81±0.15</td><td>20</td><td>28</td><td>7/0.127</td><td>24.13±0.30</td><td>25.40±0.30</td></tr><tr><td>04</td><td>28</td><td>7/0.127</td><td>3.81±0.20</td><td>5.08±0.20</td><td>② 24</td><td>28</td><td>7/0.127</td><td>29.21±0.30</td><td>30.48±0.30</td></tr><tr><td>05</td><td>28</td><td>7/0.127</td><td>5.08±0.20</td><td>6.35±0.20</td><td>25</td><td>28</td><td>7/0.127</td><td>30.48±0.30</td><td>31.75±0.30</td></tr><tr><td>06</td><td>28</td><td>7/0.127</td><td>6.35±0.20</td><td>7.62±0.20</td><td>26</td><td>28</td><td>7/0.127</td><td>31.75±0.30</td><td>33.02±0.30</td></tr><tr><td>07</td><td>28</td><td>7/0.127</td><td>7.62±0.20</td><td>8.89±0.20</td><td>30</td><td>28</td><td>7/0.127</td><td>36.83±0.35</td><td>38.10±0.35</td></tr><tr><td>08</td><td>28</td><td>7/0.127</td><td>8.89±0.20</td><td>10.16±0.20</td><td>34</td><td>28</td><td>7/0.127</td><td>41.91±0.35</td><td>43.18±0.35</td></tr><tr><td>09</td><td>28</td><td>7/0.127</td><td>10.16±0.25</td><td>11.43±0.25</td><td>37</td><td>28</td><td>7/0.127</td><td>45.72±0.35</td><td>46.99±0.35</td></tr><tr><td>10</td><td>28</td><td>7/0.127</td><td>11.43±0.25</td><td>12.70±0.25</td><td>40</td><td>28</td><td>7/0.127</td><td>49.53±0.35</td><td>50.80±0.35</td></tr><tr><td>11</td><td>28</td><td>7/0.127</td><td>12.70±0.25</td><td>13.97±0.25</td><td>50</td><td>28</td><td>7/0.127</td><td>62.23±0.35</td><td>63.50±0.35</td></tr><tr><td>12</td><td>28</td><td>7/0.127</td><td>13.97±0.25</td><td>15.24±0.25</td><td>60</td><td>28</td><td>7/0.127</td><td>74.93±0.40</td><td>76.20±0.40</td></tr><tr><td>13</td><td>28</td><td>7/0.127</td><td>15.24±0.25</td><td>16.51±0.25</td><td>64</td><td>28</td><td>7/0.127</td><td>80.01±0.40</td><td>81.28±0.40</td></tr><tr><td>14</td><td>28</td><td>7/0.127</td><td>16.51±0.25</td><td>17.78±0.25</td><td></td><td></td><td></td><td></td><td></td></tr><tr><td>15</td><td>28</td><td>7/0.127</td><td>17.78±0.25</td><td>19.05±0.25</td><td></td><td></td><td></td><td></td><td></td></tr><tr><td>16</td><td>28</td><td>7/0.127</td><td>19.05±0.25</td><td>20.32±0.25</td><td></td><td></td><td></td><td></td><td></td></tr></table>							Cores	Size of conductor		A①	B①	Cores	Size of conductor		A①	B①	AWG	Composition	AWG	Composition	02	28	7/0.127	1.27±0.15	2.54±0.15	18	28	7/0.127	21.59±0.30	22.86±0.30	03	28	7/0.127	2.54±0.15	3.81±0.15	20	28	7/0.127	24.13±0.30	25.40±0.30	04	28	7/0.127	3.81±0.20	5.08±0.20	② 24	28	7/0.127	29.21±0.30	30.48±0.30	05	28	7/0.127	5.08±0.20	6.35±0.20	25	28	7/0.127	30.48±0.30	31.75±0.30	06	28	7/0.127	6.35±0.20	7.62±0.20	26	28	7/0.127	31.75±0.30	33.02±0.30	07	28	7/0.127	7.62±0.20	8.89±0.20	30	28	7/0.127	36.83±0.35	38.10±0.35	08	28	7/0.127	8.89±0.20	10.16±0.20	34	28	7/0.127	41.91±0.35	43.18±0.35	09	28	7/0.127	10.16±0.25	11.43±0.25	37	28	7/0.127	45.72±0.35	46.99±0.35	10	28	7/0.127	11.43±0.25	12.70±0.25	40	28	7/0.127	49.53±0.35	50.80±0.35	11	28	7/0.127	12.70±0.25	13.97±0.25	50	28	7/0.127	62.23±0.35	63.50±0.35	12	28	7/0.127	13.97±0.25	15.24±0.25	60	28	7/0.127	74.93±0.40	76.20±0.40	13	28	7/0.127	15.24±0.25	16.51±0.25	64	28	7/0.127	80.01±0.40	81.28±0.40	14	28	7/0.127	16.51±0.25	17.78±0.25						15	28	7/0.127	17.78±0.25	19.05±0.25						16	28	7/0.127	19.05±0.25	20.32±0.25						D
Cores	Size of conductor		A①	B①	Cores	Size of conductor			A①	B①																																																																																																																																																																		
	AWG	Composition				AWG	Composition																																																																																																																																																																					
02	28	7/0.127	1.27±0.15	2.54±0.15	18	28	7/0.127	21.59±0.30	22.86±0.30																																																																																																																																																																			
03	28	7/0.127	2.54±0.15	3.81±0.15	20	28	7/0.127	24.13±0.30	25.40±0.30																																																																																																																																																																			
04	28	7/0.127	3.81±0.20	5.08±0.20	② 24	28	7/0.127	29.21±0.30	30.48±0.30																																																																																																																																																																			
05	28	7/0.127	5.08±0.20	6.35±0.20	25	28	7/0.127	30.48±0.30	31.75±0.30																																																																																																																																																																			
06	28	7/0.127	6.35±0.20	7.62±0.20	26	28	7/0.127	31.75±0.30	33.02±0.30																																																																																																																																																																			
07	28	7/0.127	7.62±0.20	8.89±0.20	30	28	7/0.127	36.83±0.35	38.10±0.35																																																																																																																																																																			
08	28	7/0.127	8.89±0.20	10.16±0.20	34	28	7/0.127	41.91±0.35	43.18±0.35																																																																																																																																																																			
09	28	7/0.127	10.16±0.25	11.43±0.25	37	28	7/0.127	45.72±0.35	46.99±0.35																																																																																																																																																																			
10	28	7/0.127	11.43±0.25	12.70±0.25	40	28	7/0.127	49.53±0.35	50.80±0.35																																																																																																																																																																			
11	28	7/0.127	12.70±0.25	13.97±0.25	50	28	7/0.127	62.23±0.35	63.50±0.35																																																																																																																																																																			
12	28	7/0.127	13.97±0.25	15.24±0.25	60	28	7/0.127	74.93±0.40	76.20±0.40																																																																																																																																																																			
13	28	7/0.127	15.24±0.25	16.51±0.25	64	28	7/0.127	80.01±0.40	81.28±0.40																																																																																																																																																																			
14	28	7/0.127	16.51±0.25	17.78±0.25																																																																																																																																																																								
15	28	7/0.127	17.78±0.25	19.05±0.25																																																																																																																																																																								
16	28	7/0.127	19.05±0.25	20.32±0.25																																																																																																																																																																								
E								E																																																																																																																																																																				
F								F																																																																																																																																																																				
G	RoHS compliant Unit: mm		Scale	Free				Date	Name	Description. Flat Cable Pitch 1.27mm	G																																																																																																																																																																	
TOLERANCE						Drawn	24.04.2015	Amy																																																																																																																																																																				
				③	Add the length dimension	20.04.2022	Peter	Approved	20.04.2022	Peter		ASSMANN WSW-No. AWG28-xx/G/300																																																																																																																																																																
				②	Update notes & tolerance	23.06.2020	Luca				Drawing-No.																																																																																																																																																																	
H					DIM	TOL	①	Update the tolerance	04.11.2015	Amy	ASS 7306 CA		rev03	H																																																																																																																																																														
					④	Drawn	24.04.2015	Amy	Customer-No.		Sheet 1 / 1																																																																																																																																																																	
		Angle	TOL	Id.	Modification		Date	Name																																																																																																																																																																				
	1	2	3	4	5	6	7																																																																																																																																																																					