

Features:

- Precision tolerances to $\pm 0.01\%$
- TCR down to $\pm 2 \text{ ppm/}^\circ\text{C}$
- Wide R-value range
- Lower values may be available
- Consult factory for tighter tolerances
- Qualified to AEC-Q200
- RoHS compliant and halogen-free




Electrical Specifications										
Type / Code	Power Rating (Watts) @ 70°C	Maximum Wor King Voltage ⁽¹⁾	Maximum Overload Voltage	Resistance Temperature Coefficient	Ohmic Range (Ω) and Tolerance					
					0.01%	0.05%	0.1%	0.25%	0.5%	1%
RNCF0201	0.032 W	15 V	30 V	±25 ppm/°C	-		49.9 - 4.99 K			
				±50 ppm/°C			49.9 - 33 K			
RNCF0402	0.063 W	25 V	50 V	±2 ppm/°C	49.9 - 4.99 K			-		
				±5 ppm/°C	49.9 - 20 K					
				±10 ppm/°C	49.9 - 20 K		49.9 - 100 K			
				±15 ppm/°C			49.9 - 100 K			
				±25 ppm/°C	-	49.9 - 12 K	4 - 511 K	4 - 511 K		
				±50 ppm/°C						
	0.1 W	50 V	100 V	±2 ppm/°C	49.9 - 4.99 K			-		
				±5 ppm/°C	49.9 - 20 K					
				±10 ppm/°C	49.9 - 12 K		49.9 - 100 K			
				±15 ppm/°C						
				±25 ppm/°C	-	49.9 - 12 K	4.7 - 255 K			
				±50 ppm/°C						
RNCF0603	0.063 W	50 V	100 V	2 ppm/°C	24.9 - 15 K			-		
				±5 ppm/°C	29.9 - 60 K					
				±10 ppm/°C	24.9 - 100 K	4.7 - 332 K	4.7 - 511 K			
				±15 ppm/°C						
				±25 ppm/°C	-	4.7 - 332 K	1 - 1 M			
				±50 ppm/°C						
	0.1 W	75 V	150 V	±2 ppm/°C	24.9 - 15 K			-		
				±5 ppm/°C	24.9 - 60 K					
				±10 ppm/°C	24.9 - 100 K	4.7 - 332 K	4.7 - 511 K			
				±15 ppm/°C						
				±25 ppm/°C			1 - 1 M			
				±50 ppm/°C						
0.166 W	100 V	150 V	±25 ppm/°C	-	10 - 332 K					
			±50 ppm/°C							
RNCF0805	0.1 W	100 V	200 V	± 2 ppm/°C	24.9 - 30 K			-		
				±5 ppm/°C	24.9 - 150 K					
				±10 ppm/°C	24.9 - 200 K	4.7 - 1 M				
				±15 ppm/°C						
				±25 ppm/°C	-	4.7 - 1 M	1 - 2 M			
				±50 ppm/°C						
	0.125 W	150 V	300 V	±2 ppm/°C	24.9 - 30 K			-		
				±5 ppm/°C	24.9 - 150 K					
				±10 ppm/°C	24.9 - 200 K	4.7 - 511 K	4.7 - 1 M			
				±15 ppm/°C						4.7 - 1 M
				±25 ppm/°C	24.9 - 200 K	4.7 - 511 K	1 - 1 M			
				±50 ppm/°C						
	0.25 W	150 V	300 V	±25 ppm/°C	-	10 - 499 K				
				±50 ppm/°C						

Electrical Specifications (cont.)											
Type / Code	Power Rating (Watts) @ 70°C	Maximum Wor King Voltage ⁽¹⁾	Maximum Overload Voltage	Resistance Temperature Coefficient	Ohmic Range (Ω) and Tolerance						
					0.01%	0.05%	0.1%	0.25%	0.5%	1%	
RNCF1206	0.125 W	150 V	300 V	± 2 ppm/°C	24.9 - 49.9 K			-			
				±5 ppm/°C	24.9 - 300 K						
				±10 ppm/°C	24.9 - 499 K	4.7 - 1.5 M					
				±15 ppm/°C							
				±25 ppm/°C	-	4.7 - 1 M	1 - 2.5 M				
				±50 ppm/°C							
	0.25 W	200 V	400 V	±2 ppm/°C	24.9 - 49.9 K			-			
				±5 ppm/°C	24.9 - 300 K						
				±10 ppm/°C	24.9 - 499 K	4.7 - 1 M					
				±15 ppm/°C							
				±25 ppm/°C	24.9 - 499 K	1 - 1 M					
				±50 ppm/°C							
	0.33 W	200 V	400 V	±25 ppm/°C	-	10 - 1 M					
				±50 ppm/°C							
RNCF1210	0.25 W	150 V	300 V	± 2 ppm/°C	24.9 - 49.9 K			-			
				±5 ppm/°C	24.9 - 300 K						
				±10 ppm/°C	24.9 - 499 K	4.7 - 1 M					
				±15 ppm/°C							
				±25 ppm/°C	-	4.7 - 1 M	1 - 2.5 M				
				±50 ppm/°C							
	0.33 W	200 V	400 V	±2 ppm/°C	24.9 - 49.9 K			-			
				±5 ppm/°C	24.9 - 300 K						
				±10 ppm/°C	24.9 - 499 K	4.7 - 1 M					
				±15 ppm/°C							
				±25 ppm/°C	24.9 - 499 K	1 - 1 M					
				±50 ppm/°C							
	RNCF2010	0.25 W	150 V	300 V	±2 ppm/°C	24.9 - 100 K			-		
					±5 ppm/°C	24.9 - 300 K					
± 10 ppm/°C					24.9 - 499 K	4.7 - 1 M					
± 15 ppm/°C											
±25 ppm/°C					-	4.7 - 1 M	1 - 3 M				
±50 ppm/°C											
0.33 W		200 V	400 V	±2 ppm/°C	24.9 - 49.9 K			-			
				±5 ppm/°C	24.9 - 300 K						
				±10 ppm/°C	24.9 - 499 K	4.7 - 1 M					
				±15 ppm/°C							
±25 ppm/°C	4.7 - 1 M										
±50 ppm/°C					1-- 1 M						
RNCF2512	0.5 W	150 V	300 V	±2 ppm/°C	24.9 - 100 K			-			
				±5 ppm/°C	24.9 - 300 K						
				±10 ppm/°C	24.9 - 499 K	4.7 - 1 M					
				±15 ppm/°C							
				±25 ppm/°C	-	4.7 - 1 M	1 - 3 M				
				±50 ppm/°C							
	0.75 W	200 V	400 V	±10 ppm/°C	24.9 - 2 K	4.7 - 2 K		1 - 2 K			
				±15 ppm/°C							
				±25 ppm/°C							
				±50 ppm/°C							
1 W	200 V	400 V	±25 ppm/°C	-		4.7 - 100	1 - 100				
			±50 ppm/°C								

(1) Lesser of $\sqrt{P \cdot R}$ or maximum working voltage.

(2) For those value / tolerance / TCR combinations that have multiple power ratings available, the default will be the highest power rating for that case size. If a lower power rating is desired, please contact factory.

Mechanical Specifications



Type / Code	Weight (g) (1000 pc.)	L Body Length	W Body Width	H Body Height	a Top Termination	b Bottom Termination	Unit
RNCF0201	0.14	0.023 ± 0.002 0.58 ± 0.05	0.011 ± 0.002 0.29 ± 0.05	0.009 ± 0.002 0.23 ± 0.05	0.005 ± 0.002 0.12 ± 0.05	0.006 ± 0.002 0.15 ± 0.05	inches mm
RNCF0402	0.54	0.039 ± 0.002 1.00 ± 0.05	0.020 ± 0.002 0.50 ± 0.05	0.012 ± 0.002 0.30 ± 0.05	0.008 ± 0.004 0.20 ± 0.10	0.008 ± 0.004 0.20 ± 0.10	inches mm
RNCF0603	1.83	0.061 ± 0.004 1.55 ± 0.10	0.031 ± 0.004 0.80 ± 0.10	0.018 ± 0.004 0.45 ± 0.10	0.012 ± 0.008 0.30 ± 0.20	0.012 ± 0.008 0.30 ± 0.20	inches mm
RNCF0805	4.71	0.079 ± 0.006 2.00 ± 0.15	0.049 ± 0.006 1.25 ± 0.15	0.022 ± 0.004 0.55 ± 0.10	0.012 ± 0.008 0.30 ± 0.20	0.016 ± 0.008 0.40 ± 0.20	inches mm
RNCF1206	9.02	0.120 ± 0.006 3.05 ± 0.15	0.061 ± 0.006 1.55 ± 0.15	0.022 ± 0.004 0.55 ± 0.10	0.017 ± 0.008 0.42 ± 0.20	0.014 ± 0.010 0.35 ± 0.25	inches mm
RNCF1210	10	0.122 ± 0.006 3.10 ± 0.15	0.094 ± 0.006 2.40 ± 0.15	0.022 ± 0.004 0.55 ± 0.10	0.016 ± 0.008 0.40 ± 0.20	0.022 ± 0.010 0.55 ± 0.25	inches mm
RNCF2010	23.61	0.193 ± 0.006 4.90 ± 0.15	0.094 ± 0.006 2.40 ± 0.15	0.022 ± 0.004 0.55 ± 0.10	0.024 ± 0.012 0.60 ± 0.30	0.020 ± 0.010 0.50 ± 0.25	inches mm
RNCF2512	38.6	0.248 ± 0.006 6.30 ± 0.15	0.122 ± 0.006 3.10 ± 0.15	0.022 ± 0.004 0.55 ± 0.10	0.024 ± 0.012 0.60 ± 0.30	0.020 ± 0.010 0.50 ± 0.25	inches mm


Performance Characteristics

Test	Test Method	Test Specification		Test Condition
		Tol. ≤ 0.05%	Tol. > 0.05%	
Temperature coefficient of Resistance (T.C.R.)	MIL-STD-202 Method 304	As specified.		+25 / -55 / +25 / +125 / +25 °C
Short Time Overload	JIS-C-5201-1 4.13	Δ R ± 0.05%	Δ R ± 0.2%	RCWV * 2.5 or Max. overload voltage whichever is lower for 5 seconds
		Δ R ± 0.2% for high power rating		
Insulation Resistance	MIL-STD-202 Method 302	> 9999 M Ω		Apply 100 V _{DC} for 1 minute
Endurance	MIL-STD-202 Method 108A	Δ R ± 0.05%	Δ R ± 0.2%	70 ± 2 °C, RCWV for 1000 hours with 1.5 hours "ON" and 0.5 hour "OFF"
		Δ R ± 0.5% for high power rating		
		0201 ≤ 7 k Ω: Δ R ± 0.2% 0201 > 7 k Ω: Δ R ± 0.5%		
Damp Heat with Load	MIL-STD-202 Method 103B	Δ R ± 0.05%	Δ R ± 0.3%	40 ± 2 °C, 90 ~ 95% R.H. RCWV for 1000 hours with 1.5 hours "ON" and 0.5 hour "OFF"
		Δ R ± 0.5% for high power rating		
Bending Strength	JIS-C-5201-1 4.33	Δ R ± 0.05%	Δ R ± 0.1%	Bending amplitude for 10 seconds. 2010 and 2512 sizes: 2 mm Other sizes: 3 mm
Solderability	MIL-STD-202 Method 208H	95% min. coverage		245 ± 5 °C for 3 seconds
Resistance to Soldering Heat	MIL-STD-202 Method 210E	Δ R ± 0.05%	Δ R ± 0.1%	260 ± 5 °C for 10 seconds
Dielectric Withstand Voltage	MIL-STD-202 Method 301	by type		Max. overload voltage for 1 minute
Low Temperature Operation	JIS-C-5201-1 4.36	Δ R ± 0.05%	Δ R ± 0.2%	1 hour, - 65 °C, followed by 45 minutes of RCWV
		Δ R ± 0.5% for high power rating		
High Temperature Exposure	MIL-STD-202 Method 108	Δ R ± 0.5%		+155 °C for 1000 hours


RCWV (Rated Continuous Working Voltage) = $\sqrt{P \cdot R}$ or Max. Operating Voltage, whichever is lower.

Storage Temperature: 60 ~ 82 °F. Humidity < 80% R.H.


Power Derating Curve:



Soldering Condition:




IR Reflow Soldering



Wave Soldering (Flow Soldering)

- (1) Time of IR reflow soldering at maximum temperature point 260 °C: 10 seconds
- (2) Time of wave soldering at maximum temperature point 260 °C: 10 seconds
- (3) Time of soldering iron at maximum temperature point 410 °C: 5 seconds

Reel Specifications




Type / Code	A	B	C	W	T	Unit
RNCF0201	7.008 ± 0.039 178.00 ± 1.00	2.362 ± 0.039 60.00 ± 1.00	0.531 ± 0.028 13.50 ± 0.70	0.374 ± 0.039 9.50 ± 1.00	0.453 ± 0.039 11.50 ± 1.00	inches mm
RNCF0402	7.008 ± 0.039 178.00 ± 1.00	2.362 ± 0.039 60.00 ± 1.00	0.531 ± 0.028 13.50 ± 0.70	0.374 ± 0.039 9.50 ± 1.00	0.453 ± 0.039 11.50 ± 1.00	inches mm
RNCF0603	7.008 ± 0.039 178.00 ± 1.00	2.362 ± 0.039 60.00 ± 1.00	0.531 ± 0.028 13.50 ± 0.70	0.374 ± 0.039 9.50 ± 1.00	0.453 ± 0.039 11.50 ± 1.00	inches mm

Reel Specifications (cont.)

Type / Code	A	B	C	W	T	Unit
RNCF0805	7.008 ± 0.039 178.00 ± 1.00	2.362 ± 0.039 60.00 ± 1.00	0.531 ± 0.028 13.50 ± 0.70	0.374 ± 0.039 9.50 ± 1.00	0.453 ± 0.039 11.50 ± 1.00	inches mm
RNCF1206	7.008 ± 0.039 178.00 ± 1.00	2.362 ± 0.039 60.00 ± 1.00	0.531 ± 0.028 13.50 ± 0.70	0.374 ± 0.039 9.50 ± 1.00	0.453 ± 0.039 11.50 ± 1.00	inches mm
RNCF1210	7.008 ± 0.039 178.00 ± 1.00	2.362 ± 0.039 60.00 ± 1.00	0.531 ± 0.028 13.50 ± 0.70	0.374 ± 0.039 9.50 ± 1.00	0.453 ± 0.039 11.50 ± 1.00	inches mm
RNCF2010	7.008 ± 0.039 178.00 ± 1.00	2.362 ± 0.039 60.00 ± 1.00	0.531 ± 0.028 13.50 ± 0.70	0.531 ± 0.039 13.50 ± 1.00	0.610 ± 0.039 15.50 ± 1.00	inches mm
RNCF2512	7.008 ± 0.039 178.00 ± 1.00	2.362 ± 0.039 60.00 ± 1.00	0.531 ± 0.028 13.50 ± 0.70	0.531 ± 0.039 13.50 ± 1.00	0.610 ± 0.039 15.50 ± 1.00	inches mm


Packaging Specifications – Paper Tape




Type / Code	A	B	W	E	F	Unit
RNCF0201	0.016 ± 0.002 0.40 ± 0.05	0.028 ± 0.002 0.70 ± 0.05	0.315 ± 0.004 8.00 ± 0.10	0.069 ± 0.002 1.75 ± 0.05	0.138 ± 0.002 3.50 ± 0.05	inches mm
RNCF0402	0.028 ± 0.002 0.70 ± 0.05	0.046 ± 0.002 1.16 ± 0.05	0.315 ± 0.004 8.00 ± 0.10	0.069 ± 0.002 1.75 ± 0.05	0.138 ± 0.002 3.50 ± 0.05	inches mm
RNCF0603	0.043 ± 0.002 1.10 ± 0.05	0.075 ± 0.002 1.90 ± 0.05	0.315 ± 0.004 8.00 ± 0.10	0.069 ± 0.002 1.75 ± 0.05	0.138 ± 0.002 3.50 ± 0.05	inches mm
RNCF0805	0.063 ± 0.002 1.60 ± 0.05	0.093 ± 0.002 2.37 ± 0.05	0.315 ± 0.004 8.00 ± 0.10	0.069 ± 0.020 1.75 ± 0.50	0.138 ± 0.002 3.50 ± 0.05	inches mm
RNCF1206	0.079 ± 0.002 2.00 ± 0.05	0.140 ± 0.002 3.55 ± 0.05	0.315 ± 0.004 8.00 ± 0.10	0.069 ± 0.002 1.75 ± 0.05	0.138 ± 0.002 3.50 ± 0.05	inches mm
RNCF1210	0.108 ± 0.002 2.75 ± 0.05	0.134 ± 0.002 3.40 ± 0.05	0.315 ± 0.004 8.00 ± 0.10	0.069 ± 0.002 1.75 ± 0.05	0.138 ± 0.002 3.50 ± 0.05	inches mm
Type / Code	P0	P1	P2	D0	T	Unit
RNCF0201	0.157 ± 0.004 4.00 ± 0.10	0.079 ± 0.002 2.00 ± 0.05	0.079 ± 0.002 2.00 ± 0.05	0.061 ± 0.001 1.55 ± 0.03	0.017 ± 0.001 0.42 ± 0.02	inches mm
RNCF0402	0.157 ± 0.004 4.00 ± 0.10	0.079 ± 0.002 2.00 ± 0.05	0.079 ± 0.002 2.00 ± 0.05	0.061 ± 0.002 1.55 ± 0.05	0.016 ± 0.001 0.40 ± 0.03	inches mm
RNCF0603	0.157 ± 0.004 4.00 ± 0.10	0.157 ± 0.004 4.00 ± 0.10	0.079 ± 0.002 2.00 ± 0.05	0.061 ± 0.002 1.55 ± 0.05	0.024 ± 0.001 0.60 ± 0.03	inches mm
RNCF0805	0.157 ± 0.004 4.00 ± 0.10	0.157 ± 0.004 4.00 ± 0.10	0.079 ± 0.002 2.00 ± 0.05	0.061 ± 0.002 1.55 ± 0.05	0.030 ± 0.002 0.75 ± 0.05	inches mm
RNCF1206	0.157 ± 0.004 4.00 ± 0.10	0.157 ± 0.004 4.00 ± 0.10	0.079 ± 0.002 2.00 ± 0.05	0.061 ± 0.002 1.55 ± 0.05	0.030 ± 0.002 0.75 ± 0.05	inches mm
RNCF1210	0.157 ± 0.002 4.00 ± 0.05	0.157 ± 0.004 4.00 ± 0.10	0.079 ± 0.002 2.00 ± 0.05	0.063 ± 0.004 1.60 ± 0.10	0.030 ± 0.002 0.75 ± 0.05	inches mm

Peel Force of Top Cover Tape

The peel speed shall be about 300 mm / min $\pm$ 5%
The peel force of top cover tape shall be between 8 gf to 60 gf




Packaging Specifications – Embossed Plastic Tape




Type / Code	A	B	W	E	F	Unit
RNCF2010	0.112 $\pm$ 0.004 2.85 $\pm$ 0.10	0.215 $\pm$ 0.004 5.45 $\pm$ 0.10	0.472 $\pm$ 0.004 12.00 $\pm$ 0.10	0.069 $\pm$ 0.004 1.75 $\pm$ 0.10	0.217 $\pm$ 0.002 5.50 $\pm$ 0.05	inches mm
RNCF2512	0.134 $\pm$ 0.004 3.40 $\pm$ 0.10	0.262 $\pm$ 0.004 6.65 $\pm$ 0.10	0.472 $\pm$ 0.004 12.00 $\pm$ 0.10	0.069 $\pm$ 0.004 1.75 $\pm$ 0.10	0.217 $\pm$ 0.002 5.50 $\pm$ 0.05	inches mm
Type / Code	P0	P1	P2	D0	T	Unit
RNCF2010	0.157 $\pm$ 0.002 4.00 $\pm$ 0.05	0.157 $\pm$ 0.004 4.00 $\pm$ 0.10	0.079 $\pm$ 0.002 2.00 $\pm$ 0.05	0.059 $\pm$ 0.004 1.50 $\pm$ 0.10	0.039 $\pm$ 0.008 1.00 $\pm$ 0.20	inches mm
RNCF2512	0.157 $\pm$ 0.002 4.00 $\pm$ 0.05	0.157 $\pm$ 0.004 4.00 $\pm$ 0.10	0.079 $\pm$ 0.002 2.00 $\pm$ 0.05	0.059 $\pm$ 0.004 1.50 $\pm$ 0.10	0.039 $\pm$ 0.008 1.00 $\pm$ 0.20	inches mm

Peel Force of Top Cover Tape

The peel speed shall be about 300 mm / min $\pm$ 5%
The peel force of top cover tape shall be between 20 gf to 80 gf



Recommended Pad Layout



Type / Code	A	B	C	Unit
RNCF0201	0.010 0.25	0.012 0.30	0.016 ± 0.008 0.40 ± 0.20	inches mm
RNCF0402	0.020 0.50	0.020 0.50	0.024 ± 0.008 0.60 ± 0.20	inches mm
RNCF0603	0.031 0.80	0.039 1.00	0.035 ± 0.008 0.90 ± 0.20	inches mm
RNCF0805	0.039 1.00	0.039 1.00	0.053 ± 0.008 1.35 ± 0.20	inches mm
RNCF1206	0.079 2.00	0.045 1.15	0.067 ± 0.008 1.70 ± 0.20	inches mm
RNCF1210	0.079 2.00	0.045 1.15	0.098 ± 0.008 2.50 ± 0.20	inches mm
RNCF2010	0.142 3.60	0.055 1.40	0.098 ± 0.008 2.50 ± 0.20	inches mm
RNCF2512	0.193 4.90	0.063 1.60	0.122 ± 0.008 3.10 ± 0.20	inches mm

RoHS Compliance

Stackpole Electronics has joined the worldwide effort to reduce the amount of lead in electronic components and to meet the various regulatory requirements now prevalent, such as the European Union's directive regarding "Restrictions on Hazardous Substances" (RoHS 3). As part of this ongoing program, we periodically update this document with the status regarding the availability of our compliant components. All our standard part numbers are compliant to EU Directive 2011/65/EU of the European Parliament as amended by Directive (EU) 2015/863/EU as regards the list of restricted substances.

RoHS Compliance Status

Standard Product Series	Description	Package / Termination Type	Standard Series RoHS Compliant	Lead-Free Termination Composition	Lead-Free Mfg. Effective Date (Std Product Series)	Lead-Free Effective Date Code (YY/WW)
RNCF	Precision Thin Film Surface Mount Chip Resistor	SMD	YES	100% Matte Sn over Ni	May-04	04/18

“Conflict Metals” Commitment

We at Stackpole Electronics, Inc. are joined with our industry in opposing the use of metals mined in the “conflict region” of the eastern Democratic Republic of the Congo (DRC) in our products. Recognizing that the supply chain for metals used in the electronics industry is very complex, we work closely with our own suppliers to verify to the extent possible that the materials and products we supply do not contain metals sourced from this conflict region. As such, we are in compliance with the requirements of Dodd-Frank Act regarding Conflict Minerals.

Compliance to “REACH”

We certify that all passive components supplied by Stackpole Electronics, Inc. are SVHC (Substances of Very High Concern) free and compliant with the requirements of EU Directive 1907/2006/EC, “The Registration, Evaluation, Authorization and Restriction of Chemicals”, otherwise referred to as REACH. Contact us for complete list of REACH Substance Candidate List.

Environmental Policy

It is the policy of Stackpole Electronics, Inc. (SEI) to protect the environment in all localities in which we operate. We continually strive to improve our effect on the environment. We observe all applicable laws and regulations regarding the protection of our environment and all requests related to the environment to which we have agreed. We are committed to the prevention of all forms of pollution.

How to Order

1	2	3	4	5	6	7	8	9	10	11	12	13	14	15
R	N	C	F	0	8	0	5	D	T	E	4	K	7	5

Product Series		Size	Tolerance			Packaging				TCR		Resistance Value ⁽²⁾ Four characters with the multiplier used as the decimal holder. 24.9 ohm = 24R9 10 Kohm = 10K0 1 Mohm = 1M00		
Code	Description	Code	Code	Tol	Value ⁽¹⁾	Code	Description	Size	Quantity	Code	ppm			
RNCF	Precision Thin Film Chip Resistors	0201	T	0.01%	E192, E96, E24	T	7" Reel Paper Tape	0201, 0402	10000	W	2			
		0402	A	0.05%				0603, 0805	5000	Y	5			
		0603	B	0.1%				1206, 1210		T	10			
		0805	C	0.25%			7" Reel Plastic Tape		2010, 2512	4000	S	15		
		1206	D	0.5%	E96, E24						E	25		
		1210	F	1%							C	50		
		2010	K	7" Reel	All Sizes	1000	D	100						
2512														

(1) E192 values are not marked, and may be subject to 20 K pieces MOQ

(2) Values below 10 ohm and above 1 Mohm may be subject to 20 K pieces MOQ