

# DP2 SERIES

## High-performance Digital Pressure Sensor



**Complete functionality!  
Selection from a wide  
lineup**

\* Passed the UL 991 Environment Test

\* UL 61010C-1 compatible, Passed the UL 991 Environment Test based on SEMI S2-0200.  
[Category applicable for semiconductor manufacturing: TWW2, Process Equipment]  
[Applicable standards: UL 61010C-1]  
[Additional test / evaluation standards as per intended use: UL991, SEMI S2-0200]



### High accuracy • high resolution • high speed

It achieves a 2.5 ms, or less, response time at a high resolution of 1/1,000. It enables highly accurate sensing with its excellent repeatability and temperature characteristics.

#### Response time

2.5 ms or less

#### Repeatability

Within  $\pm 0.2\%$  F.S.  $\pm 1$  digit

#### Temperature characteristics

Within  $\pm 1\%$  F.S.

### Clearly visible LED display with 3 1/2 digits

Bright red LED 7-segment display having 3 1/2 digits, 10 mm 0.394 in high. The displayed figures are remarkably noticeable not only in a dark area, but also in a well-lit place.

Incorporates minus sign indication




### Setting with easy key operation

Initialization and threshold value settings are easily done by key operation while seeing the values on the display.




### Four output modes enable versatile pressure level control

#### 1 Hysteresis mode




The common hysteresis of the comparative outputs can be set, as desired, with the set values.

#### 2 Window comparator mode




The comparative outputs can be turned ON or OFF by a pressure which is within the pressure range set by Set Value 1 and Set Value 2.

#### 3 Dual output mode



The outputs can be put to different use, such as, detection of different kinds of objects, control function, alarm function etc.

#### 4 Automatic sensitivity setting mode




Using actual objects, if the pressure values for OK objects and NG objects are input, then the sensor is automatically set to the optimum pressure value (mid-value).

### Selection from six pressure units

The pressure unit can be selected from six different systems to suit your requirement.

(The selectable pressure units differ with the sensor type. When the pressure unit is changed, the measured pressure value and the set values are automatically converted.)




Note: 'MPa' in case of DP2-22□, DP2-42□ and DP2-62□.

## APPLICATIONS


### Confirmation of chip component suction

The light weight type does not disturb the movement of the suction head, even if it is mounted close to the head.




### Verifying placement of frame

High pressure is attained when the frame is exactly seated. Hence, the pressure change when the frame is exactly placed is detected.




### Controlling clamping force

The clamping force can be changed to suit the workpiece by controlling the supplied air pressure.




### Inspecting orientation of glass sheet

The orientation of the glass sheet can be recognized by detecting the change in vacuum due to presence / absence of indentation.




### Detecting tap breakage

Two opposed nozzles are supplied air at different pressures. If the tap breaks, the pressure at the lower pressure side nozzle is affected by the air of the higher pressure side nozzle. This change in pressure is detected.



### Controlling edge of winding film

With bifurcated nozzles placed on both sides of the film, the position of the winding film is recognized as right-shifted (high pressure), OK (middle pressure), or left-shifted (low pressure).



## Analog voltage output incorporated as a standard

Since a linear analog voltage output (1 to 5 V) is incorporated, the sensor is ideally suited for real time monitoring or for remote control in combination with an analog controller (ultra-compact digital panel controller **CA2** series, or digital panel controller **CA** series).

### Peak hold / bottom hold display

The peak value or the bottom value of the varying pressure can be displayed. This function is convenient for finding the pressure variation range or for determining a reference for pressure settings.

### Analog bar display

Pressure changes can also be displayed in an analog fashion using LED bars. Hence, sudden pressure changes can be recognized at a glance. (LED bars indicate the pressure level in steps of 10 % F.S., regardless of the pressure unit.)

#### Analog bar display




#### Digital display



## A Wide Variety of Models


Models are selectable according to mounting style, environmental resistance, and manner of use.

### Standard type / DP2-2



Mounting on a panel


### Flat type / DP2-4



Direct mounting on a wall

### Light weight type / DP2-80


Total weight 70 g approx.




The sensor can be mounted on the suction head of a chip mounter.

Asian type

### IP67 type / DP2-6



Water and dust proof



The **DP2** series covers world-wide usage with the Asian type, the North American type and the European type. Each type provides the customary pressure unit, suitable transistor output, and pressure port.

|                | Pressure unit                         |                                                                             | Output                 | Pressure port                     |
|----------------|---------------------------------------|-----------------------------------------------------------------------------|------------------------|-----------------------------------|
|                | The international system of unit (SI) |                                                                             |                        |                                   |
| Asian          | Pa                                    | kgf/cm <sup>2</sup> (Positive pressure type)<br>mmHg (Vacuum pressure type) | NPN and analog voltage | Rc (PT) 1/8 or M5 female thread   |
| North American |                                       | psi (Positive pressure type)<br>inHg (Vacuum pressure type)                 | NPN and analog voltage | NPT 1/8 or NPTF 1/8 female thread |
| European       |                                       | bar                                                                         | PNP and analog voltage | G (PF) 1/8 female thread          |

## ORDER GUIDE

| Type     |                   |                |                | Appearance                                                                          | Rated pressure range | Model No.        | Pressure port             | Comparative output            |
|----------|-------------------|----------------|----------------|-------------------------------------------------------------------------------------|----------------------|------------------|---------------------------|-------------------------------|
| Standard | Vacuum pressure   | — 101 kPa type | Asian          |    | 0 to — 101.3 kPa     | <b>DP2-20</b>    | Rc (PT) 1/8 female thread | NPN open-collector transistor |
|          |                   |                | North American |                                                                                     |                      | <b>DP2-20F</b>   | NPTF 1/8 female thread    | PNP open-collector transistor |
|          |                   |                |                |                                                                                     |                      | <b>DP2-20F-P</b> |                           |                               |
|          |                   | 100 kPa type   | Asian          |                                                                                     | 0 to 100.0 kPa       | <b>DP2-21</b>    | Rc (PT) 1/8 female thread | NPN open-collector transistor |
|          |                   |                | North American |                                                                                     |                      | <b>DP2-21F</b>   | NPTF 1/8 female thread    | PNP open-collector transistor |
|          |                   |                |                |                                                                                     |                      | <b>DP2-21F-P</b> |                           |                               |
|          | Positive pressure | 1 MPa type     | Asian          |    | 0 to 1.000 MPa       | <b>DP2-22</b>    | Rc (PT) 1/8 female thread | NPN open-collector transistor |
|          |                   |                | North American |                                                                                     |                      | <b>DP2-22F</b>   | NPTF 1/8 female thread    | PNP open-collector transistor |
|          |                   |                |                |                                                                                     |                      | <b>DP2-22F-P</b> |                           |                               |
|          |                   | — 101 kPa type | Asian          |   | 0 to — 101.3 kPa     | <b>DP2-80</b>    | M5 female thread          | NPN open-collector transistor |
|          |                   |                | North American |                                                                                     |                      | <b>DP2-40N</b>   | NPT 1/8 female thread     |                               |
|          |                   |                | European       |                                                                                     |                      | <b>DP2-40E</b>   | G (PF) 1/8 female thread  | PNP open-collector transistor |
|          | Positive pressure | 100 kPa type   | Asian          |                                                                                     | 0 to 100.0 kPa       | <b>DP2-41</b>    | Rc (PT) 1/8 female thread | NPN open-collector transistor |
|          |                   |                | North American |                                                                                     |                      | <b>DP2-41N</b>   | NPT 1/8 female thread     |                               |
|          |                   |                | European       |                                                                                     |                      | <b>DP2-41E</b>   | G (PF) 1/8 female thread  | PNP open-collector transistor |
|          |                   | 1 MPa type     | Asian          |                                                                                     | 0 to 1.000 MPa       | <b>DP2-42</b>    | Rc (PT) 1/8 female thread | NPN open-collector transistor |
|          |                   |                | North American |                                                                                     |                      | <b>DP2-42N</b>   | NPT 1/8 female thread     |                               |
|          |                   |                | European       |                                                                                     |                      | <b>DP2-42E</b>   | G (PF) 1/8 female thread  | PNP open-collector transistor |
| IP67     | Vacuum pressure   | — 101 kPa type | Asian          |  | 0 to — 101.3 kPa     | <b>DP2-60</b>    | Rc (PT) 1/8 female thread | NPN open-collector transistor |
|          |                   |                | North American |                                                                                     |                      | <b>DP2-60N</b>   | NPT 1/8 female thread     |                               |
|          |                   |                | European       |                                                                                     |                      | <b>DP2-60E</b>   | G (PF) 1/8 female thread  | PNP open-collector transistor |
|          | Positive pressure | 100 kPa type   | Asian          |                                                                                     | 0 to 100.0 kPa       | <b>DP2-61</b>    | Rc (PT) 1/8 female thread | NPN open-collector transistor |
|          |                   |                | North American |                                                                                     |                      | <b>DP2-61N</b>   | NPT 1/8 female thread     |                               |
|          |                   |                | European       |                                                                                     |                      | <b>DP2-61E</b>   | G (PF) 1/8 female thread  | PNP open-collector transistor |
|          |                   | 1 MPa type     | Asian          |                                                                                     | 0 to 1.000 MPa       | <b>DP2-62</b>    | Rc (PT) 1/8 female thread | NPN open-collector transistor |
|          |                   |                | North American |                                                                                     |                      | <b>DP2-62N</b>   | NPT 1/8 female thread     |                               |
|          |                   |                | European       |                                                                                     |                      | <b>DP2-62E</b>   | G (PF) 1/8 female thread  | PNP open-collector transistor |

## ORDER GUIDE


### 5 m 16.404 ft cable length type

5 m 16.404 ft cable length type is also available. (Standard: 2 m 6.562 ft)

| Type     |                   |                 | Standard  | 5 m 16.404 ft cable length type                                |
|----------|-------------------|-----------------|-----------|----------------------------------------------------------------|
| Standard | Vacuum pressure   | — 101 kPa type  | DP2-20    | DP2-20-C5                                                      |
|          |                   |                 | DP2-20F   | _____                                                          |
|          |                   |                 | DP2-20F-P | _____                                                          |
|          | Positive pressure | 100 kPa type    | DP2-21    | DP2-21-C5                                                      |
|          |                   |                 | DP2-21F   | _____                                                          |
|          |                   |                 | DP2-21F-P | _____                                                          |
|          |                   | 1 MPa type      | DP2-22    | DP2-22-C5                                                      |
|          |                   |                 | DP2-22F   | _____                                                          |
|          |                   |                 | DP2-22F-P | _____                                                          |
| Flat     | Light weight      | Vacuum pressure | DP2-80    | DP2-80-C5                                                      |
|          |                   |                 | DP2-40N   | _____                                                          |
|          |                   |                 | DP2-40E   | _____                                                          |
|          | Positive pressure | 100 kPa type    | DP2-41    | DP2-41-C5                                                      |
|          |                   |                 | DP2-41N   | _____                                                          |
|          |                   |                 | DP2-41E   | _____                                                          |
|          |                   | 1 MPa type      | DP2-42    | DP2-42-C5                                                      |
|          |                   |                 | DP2-42N   | _____                                                          |
|          |                   |                 | DP2-42E   | _____                                                          |
| IP67     | Vacuum pressure   | — 101 kPa type  | DP2-60    | The IP67 type is the standard type with a 5 m 16.404 ft cable. |
|          |                   |                 | DP2-60N   |                                                                |
|          |                   |                 | DP2-60E   |                                                                |
|          | Positive pressure | 100 kPa type    | DP2-61    |                                                                |
|          |                   |                 | DP2-61N   |                                                                |
|          |                   |                 | DP2-61E   |                                                                |
|          |                   | 1 MPa type      | DP2-62    |                                                                |
|          |                   |                 | DP2-62N   |                                                                |
|          |                   |                 | DP2-62E   |                                                                |

### Accessories

- **DPX-01** [Pressure port attachment (Standard type only)]
- **DPX-02** [Hexagon-socket-head plug for pressure port (Standard type only)]




## OPTIONS

| Designation                                    | Model No.       | Description                                                                                                                            |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                  |
|------------------------------------------------|-----------------|----------------------------------------------------------------------------------------------------------------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Sensor mounting bracket<br>(For standard type) | <b>MS-DPX</b>   | Mounting bracket for standard type<br>[Two M4 (length 6 mm 0.236 in) pan head screws and two spring washers are attached.]             |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                  |
|                                                | <b>MS-DPX-4</b> | Back angled mounting bracket for standard type<br>[Two M4 (length 6 mm 0.236 in) pan head screws and two spring washers are attached.] |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                  |
| Straight bush                                  | <b>DPX-03</b>   | Changes the pressure port from female thread [Rc (PT) 1/8] to male thread [R (PT) 1/8]                                                 |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                  |
| Panel mounting bracket<br>(For standard type)  | <b>MS-DPX-2</b> | It can be used for mounting on a panel<br>(1 to 3.2 mm 0.039 to 0.126 in thick).                                                       |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                  |
| Front protection cover<br>(For standard type)  | <b>DPX-04</b>   | It protects the sensor's adjustment panel.<br>(It can be fitted when the panel mounting bracket is used.)                              |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                  |
| Digital panel controller<br>(Note)             | <b>CA2-T2</b>   | NPN open-collector transistor                                                                                                          | This is a very small controller which allows two independent threshold level settings.<br>• Supply voltage: 24 V DC $\pm 10\%$<br>• No. of inputs: 1 No. (sensor input)<br>• Input range: 1 to 5 V DC<br>• Main functions:<br>Threshold level setting function, zero-adjust function, scale setting function, hysteresis setting function, start / hold function, auto-reference function, power supply ON-delay function, etc.                                                                                  |
|                                                | <b>CA-R2</b>    | Relay contact                                                                                                                          | This is a multi-functional controller having mathematical functions, hold function, etc.<br>• Supply voltage: 100 to 240 V AC $\pm 10\%$<br>• No. of inputs: 2 Nos. (sensor inputs)<br>• Input range: 1 to 5 V DC<br>• Power supply for sensor: 12 V DC, 150 mA<br>• Main functions:<br>Mathematical functions, process number selection function, hold function, scaling function, auto-reference function, power supply ON-delay function, measurement start delay function, hysteresis setting function, etc. |
|                                                | <b>CA-T2</b>    | NPN open-collector transistor                                                                                                          |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                  |
|                                                | <b>CA-B2</b>    | NPN open-collector transistor<br>With BCD output                                                                                       |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                  |


### Sensor mounting bracket

• MS-DPX

• MS-DPX-4




Two M4 (length 6 mm 0.236 in) pan head screws and two spring washers are attached.



Two M4 (length 6 mm 0.236 in) pan head screws and two spring washers are attached.

### Straight bush


• DPX-03



### Panel mounting bracket, Front protection cover

• MS-DPX-2

• DPX-04



### Digital panel controller


• CA2 series



• CA series



## SPECIFICATIONS


| Item                                                                    | Model No.                  | Type                  | Vacuum pressure                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                              |              |         |         | Positive pressure                                                                                             |         |         |                                                                                                              |         |         |
|-------------------------------------------------------------------------|----------------------------|-----------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--------------|---------|---------|---------------------------------------------------------------------------------------------------------------|---------|---------|--------------------------------------------------------------------------------------------------------------|---------|---------|
|                                                                         |                            |                       | — 101kPa type                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                |              |         |         | 100kPa type                                                                                                   |         |         | 1MPa type                                                                                                    |         |         |
|                                                                         |                            |                       | Standard                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                     | Light weight | Flat    | IP67    | Standard                                                                                                      | Flat    | IP67    | Standard                                                                                                     | Flat    | IP67    |
|                                                                         |                            |                       | Asian                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                        | DP2-20       | DP2-80  | ———     | DP2-60                                                                                                        | DP2-21  | DP2-41  | DP2-61                                                                                                       | DP2-22  | DP2-42  |
|                                                                         |                            | North American (Note) | DP2-20F(-P)                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                  | ———          | DP2-40N | DP2-60N | DP2-21F(-P)                                                                                                   | DP2-41N | DP2-61N | DP2-22F(-P)                                                                                                  | DP2-42N | DP2-62N |
|                                                                         |                            | European              | ———                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                          | ———          | DP2-40E | DP2-60E | ———                                                                                                           | DP2-41E | DP2-61E | ———                                                                                                          | DP2-42E | DP2-62E |
| Type of pressure                                                        |                            |                       | Gauge pressure                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                               |              |         |         |                                                                                                               |         |         |                                                                                                              |         |         |
| Rated pressure range                                                    |                            |                       | 0 to — 101.3 kPa                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                             |              |         |         | 0 to 100.0 kPa                                                                                                |         |         | 0 to 1.000 MPa                                                                                               |         |         |
| Set pressure range                                                      |                            |                       | 5.1 to — 101.3 kPa<br>{ 0.052 to — 1.033 kgf/cm <sup>2</sup> , 0.051 to — 1.013 bar<br>0.74 to — 14.70 psi, 38 to — 760 mmHg<br>1.5 to — 29.9 inHg }                                                                                                                                                                                                                                                                                                                                                                                                                                         |              |         |         | { — 5.0 to 100.0 kPa<br>— 0.051 to 1.020 kgf/cm <sup>2</sup><br>— 0.050 to 1.000 bar<br>— 0.72 to 14.50 psi } |         |         | { — 0.050 to 1.000 MPa<br>— 0.51 to 10.20 kgf/cm <sup>2</sup><br>— 0.50 to 10.00 bar<br>— 7.2 to 145.0 psi } |         |         |
| Pressure withstandability                                               |                            |                       | 490 kPa                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                      |              |         |         |                                                                                                               |         |         | 1.47 MPa                                                                                                     |         |         |
| Applicable fluid                                                        |                            |                       | Non-corrosive gas                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                            |              |         |         |                                                                                                               |         |         |                                                                                                              |         |         |
| Selectable units                                                        |                            |                       | kPa, kgf/cm <sup>2</sup> , bar, psi, mmHg, inHg                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                              |              |         |         | kPa, kgf/cm <sup>2</sup> , bar, psi                                                                           |         |         | MPa, kgf/cm <sup>2</sup> , bar, psi                                                                          |         |         |
| Supply voltage                                                          |                            |                       | 12 to 24 V DC $\pm\frac{10}{15}\%$ Ripple P-P 10 % or less                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                   |              |         |         |                                                                                                               |         |         |                                                                                                              |         |         |
| Current consumption                                                     |                            |                       | 50 mA or less                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                |              |         |         |                                                                                                               |         |         |                                                                                                              |         |         |
| Comparative outputs<br>(Comparative Output 1)<br>(Comparative Output 2) |                            |                       | <Asian, North American (Standard NPN output, flat and IP67 types)><br>NPN open-collector transistor<br>• Maximum sink current: 100 mA<br>• Applied voltage: 30 V DC or less (between comparative output and 0 V)<br>• Residual voltage: 1 V or less (at 100 mA sink current)<br>0.4 V or less (at 16 mA sink current)<br><North American (Standard PNP output type), European><br>PNP open-collector transistor<br>• Maximum source current: 100 mA<br>• Applied voltage: 30 V DC or less (between comparative output and + V)<br>• Residual voltage: 2 V or less (at 100 mA source current) |              |         |         |                                                                                                               |         |         |                                                                                                              |         |         |
|                                                                         | Utilization category       |                       | DC-12 or DC-13                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                               |              |         |         |                                                                                                               |         |         |                                                                                                              |         |         |
|                                                                         | Output modes               |                       | Equipped with 4 types of modes: hysteresis mode, window comparator mode, dual output mode, automatic sensitivity setting mode (selectable by key operation)                                                                                                                                                                                                                                                                                                                                                                                                                                  |              |         |         |                                                                                                               |         |         |                                                                                                              |         |         |
|                                                                         | Hysteresis                 |                       | 1 digit (however, variable in hysteresis mode and 2 digits when using psi unit)                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                              |              |         |         |                                                                                                               |         |         |                                                                                                              |         |         |
|                                                                         | Repeatability              |                       | Within $\pm 0.2\%$ F.S. $\pm 1$ digit                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                        |              |         |         |                                                                                                               |         |         |                                                                                                              |         |         |
|                                                                         | Response time              |                       | 2.5 ms or less                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                               |              |         |         |                                                                                                               |         |         |                                                                                                              |         |         |
|                                                                         | Short-circuit protection   |                       | Incorporated                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                 |              |         |         |                                                                                                               |         |         |                                                                                                              |         |         |
| Analog voltage output                                                   |                            |                       | Output voltage: 1 to 5 V (over rated pressure range)<br>Zero-point: within 1 V $\pm 5\%$ F.S.<br>Span: within 4 V $\pm 5\%$ F.S.<br>Linearity: within $\pm 1\%$ F.S.<br>Output impedance: 1 k $\Omega$ approx.<br>                                                                                                                                                                                                                                                                                      |              |         |         |                                                                                                               |         |         |                                                                                                              |         |         |
| Display                                                                 |                            |                       | 3½ digit red LED display (Sampling rate: 4 times/sec. approx.)                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                               |              |         |         |                                                                                                               |         |         |                                                                                                              |         |         |
|                                                                         | Displayable pressure range |                       | 5.1 to — 101.3 kPa<br>{ 0.052 to — 1.033 kgf/cm <sup>2</sup> , 0.051 to — 1.013 bar<br>0.74 to — 14.70 psi, 38 to — 760 mmHg<br>1.5 to — 29.9 inHg }                                                                                                                                                                                                                                                                                                                                                                                                                                         |              |         |         | { — 5.0 to 100.0 kPa<br>— 0.051 to 1.020 kgf/cm <sup>2</sup><br>— 0.050 to 1.000 bar<br>— 0.72 to 14.50 psi } |         |         | { — 0.050 to 1.000 MPa<br>— 0.51 to 10.20 kgf/cm <sup>2</sup><br>— 0.50 to 10.00 bar<br>— 7.2 to 145.0 psi } |         |         |
| Analog bar display                                                      |                            |                       | LED bar display in steps of 10 % F.S. approx.                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                |              |         |         |                                                                                                               |         |         |                                                                                                              |         |         |
| Operation indicators                                                    | Comparative Output 1       |                       | Orange LED (lights up when Comparative Output 1 is ON)                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                       |              |         |         |                                                                                                               |         |         |                                                                                                              |         |         |
|                                                                         | Comparative Output 2       |                       | Green LED (lights up when Comparative Output 2 is ON)                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                        |              |         |         |                                                                                                               |         |         |                                                                                                              |         |         |
| Environmental resistance                                                | Pollution degree           |                       | 3 (Industrial environment)                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                   |              |         |         |                                                                                                               |         |         |                                                                                                              |         |         |
|                                                                         | Protection                 |                       | Standard, Flat and Light weight types: IP40 (IEC), IP67 type: IP67 (IEC)                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                     |              |         |         |                                                                                                               |         |         |                                                                                                              |         |         |
|                                                                         | Ambient temperature        |                       | — 10 to + 50 °C + 14 to + 122 °F (No dew condensation or icing allowed), Storage: — 10 to + 60 °C + 14 to + 140 °F                                                                                                                                                                                                                                                                                                                                                                                                                                                                           |              |         |         |                                                                                                               |         |         |                                                                                                              |         |         |
|                                                                         | Ambient humidity           |                       | 35 to 85 % RH, Storage: 35 to 85 % RH                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                        |              |         |         |                                                                                                               |         |         |                                                                                                              |         |         |
|                                                                         | EMC                        |                       | EN 50081-2, EN 50082-2, EN 61000-6-2                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                         |              |         |         |                                                                                                               |         |         |                                                                                                              |         |         |
|                                                                         | Voltage withstandability   |                       | 1,000 V AC for one min. between all supply terminals connected together and enclosure                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                        |              |         |         |                                                                                                               |         |         |                                                                                                              |         |         |
|                                                                         | Insulation resistance      |                       | 50 M $\Omega$ , or more, with 500 V DC megger between all supply terminals connected together and enclosure                                                                                                                                                                                                                                                                                                                                                                                                                                                                                  |              |         |         |                                                                                                               |         |         |                                                                                                              |         |         |
|                                                                         | Vibration resistance       |                       | 10 to 150 Hz frequency, 0.75 mm 0.030 in amplitude in X, Y and Z directions for two hours each                                                                                                                                                                                                                                                                                                                                                                                                                                                                                               |              |         |         |                                                                                                               |         |         |                                                                                                              |         |         |
|                                                                         | Shock resistance           |                       | 100 m/s <sup>2</sup> acceleration (10 G approx.) in X, Y and Z directions for three times each                                                                                                                                                                                                                                                                                                                                                                                                                                                                                               |              |         |         |                                                                                                               |         |         |                                                                                                              |         |         |
| Temperature characteristics                                             |                            |                       | Over ambient temperature range — 10 to + 50 °C + 14 to + 122 °F : within $\pm 1\%$ F.S. of detected pressure at + 20 °C + 68 °F                                                                                                                                                                                                                                                                                                                                                                                                                                                              |              |         |         |                                                                                                               |         |         |                                                                                                              |         |         |
| Pressure port                                                           | Asian                      |                       | Standard, Flat and IP67 types: Rc (PT) ⅛ female thread, Light weight type: M5 female thread                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                  |              |         |         |                                                                                                               |         |         |                                                                                                              |         |         |
|                                                                         | North American             |                       | Standard type: NPTF ⅛ female thread, Flat and IP67 types: NPT ⅛ female thread                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                |              |         |         |                                                                                                               |         |         |                                                                                                              |         |         |
|                                                                         | European                   |                       | Flat and IP67 types: G (PF) ⅛ female thread                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                  |              |         |         |                                                                                                               |         |         |                                                                                                              |         |         |
| Material                                                                |                            |                       | Front case: ABS, Rear case: PPS (glass fiber reinforced), Display surface: Acrylic<br>Pressure port attachment: Die-cast zinc alloy [Light weight type: POM (glass fiber reinforced), pressure port is brass (nickel plated)]<br>Front cover (IP67 type only): Polycarbonate                                                                                                                                                                                                                                                                                                                 |              |         |         |                                                                                                               |         |         |                                                                                                              |         |         |
| Cable                                                                   |                            |                       | 0.15 mm <sup>2</sup> 5-core oil resistant cabtyre cable, 2 m 6.562 ft long (IP67 type: 5 m 16.404 ft long)                                                                                                                                                                                                                                                                                                                                                                                                                                                                                   |              |         |         |                                                                                                               |         |         |                                                                                                              |         |         |
| Cable extension                                                         |                            |                       | Extension up to total 100 m 328.084 ft (less than 10 m 32.808 ft when conforming to CE marking) is possible with 0.3 mm <sup>2</sup> , or more, cable.                                                                                                                                                                                                                                                                                                                                                                                                                                       |              |         |         |                                                                                                               |         |         |                                                                                                              |         |         |
| Weight                                                                  |                            |                       | Standard type: 95 g approx., Flat type: 120 g approx., IP67 type: 370 g approx., Light weight type: 70 g approx.                                                                                                                                                                                                                                                                                                                                                                                                                                                                             |              |         |         |                                                                                                               |         |         |                                                                                                              |         |         |
| Accessories                                                             |                            |                       | Hexagon-socket-head plug for pressure port: 1 pc. (Standard type only), Pressure unit label: 1 pc.                                                                                                                                                                                                                                                                                                                                                                                                                                                                                           |              |         |         |                                                                                                               |         |         |                                                                                                              |         |         |

Note: Model Nos. of North American standard type having the suffix 'P' are PNP output type.

## I/O CIRCUIT AND WIRING DIAGRAMS

### NPN output type


#### I/O circuit diagram



- Notes: 1) When using the analog voltage output, take care to connect external device of proper input impedance. Also, when a cable extension is used, voltage drop due to cable resistance should be taken into account.
- 2) The analog voltage output does not incorporate a short-circuit protection circuit. Do not connect it directly to a power supply or a capacitive load.


Symbols ... D: Reverse supply polarity protection diode  
Z<sub>D1</sub>, Z<sub>D2</sub>, Z<sub>D3</sub>: Surge absorption zener diode  
Tr<sub>1</sub>, Tr<sub>2</sub>: NPN output transistor

#### Wiring diagram



### PNP output type


#### I/O circuit diagram



- Notes: 1) When using the analog voltage output, take care to connect external device of proper input impedance. Also, when a cable extension is used, voltage drop due to cable resistance should be taken into account.
- 2) The analog voltage output does not incorporate a short-circuit protection circuit. Do not connect it directly to a power supply or a capacitive load.

Symbols ... D: Reverse supply polarity protection diode  
Z<sub>D1</sub>, Z<sub>D2</sub>, Z<sub>D3</sub>: Surge absorption zener diode  
Tr<sub>1</sub>, Tr<sub>2</sub>: PNP output transistor

#### Wiring diagram



## PRECAUTIONS FOR PROPER USE

### All models




- This product is not a safety sensor. Its use is not intended or designed to protect life and prevent body injury or property damage from dangerous parts of machinery. It is a normal pressure detection sensor.
- The DP2 series is designed for use with non-corrosive gas. It cannot be used with liquid or corrosive gas.

### Operation

- If setting is impossible even with pressing the MODE key, verify whether the key-protect function is enabled. Please note that pressing down on the MODE key for an extended moment will enable the key-protect function as soon as the key is released.
- If using the window comparator mode, set the pressure value so that there is a difference of 3 digits, or more, between Set Value 1 (P-1) and Set Value 2 (P-2). No output will be possible with a 0 to 2 digit difference.

### Functional description



|   | Description                                       | Function                                                                                                                                                                                                                                                                                                                                                                                                                                                                      |
|---|---------------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| ① | 3 1/2 digit LED display (Red)                     | Displays measured pressure, settings, error messages and key-protect status.                                                                                                                                                                                                                                                                                                                                                                                                  |
| ② | Comparative Output 1 operation indicator (Orange) | Lights up when Comparative Output 1 is ON.                                                                                                                                                                                                                                                                                                                                                                                                                                    |
| ③ | Comparative Output 2 operation indicator (Green)  | Lights up when Comparative Output 2 is ON.                                                                                                                                                                                                                                                                                                                                                                                                                                    |
| ④ | Increment key (▲)                                 | <ul style="list-style-type: none"> <li>• In the initial setting mode, pressing the key changes the settable digit.</li> <li>• In the Set Value 1, 2 modes, pressing the key changes the set value to the high pressure side in case of positive pressure type sensor and to the high vacuum side in case of vacuum pressure type sensor.</li> <li>• In the sensing mode, if the key is pressed continuously for 4 sec. or more, the display shows peak hold value.</li> </ul> |
| ⑤ | Decrement key (▼)                                 | <ul style="list-style-type: none"> <li>• In the initial setting mode, pressing the key changes the set conditions.</li> <li>• In the Set Value 1, 2 modes, pressing the key changes the set value to the low pressure side in case of positive pressure type sensor and to the low vacuum side in case of vacuum pressure type sensor.</li> <li>• In the sensing mode, if the key is pressed continuously for 4 sec. or more, the display shows bottom hold value.</li> </ul> |
| ⑥ | Mode selection key (MODE)                         | <ul style="list-style-type: none"> <li>• Each press of the key changes the selected mode to sensing mode, Set Value 1 (P-1) set mode and Set Value 2 (P-2) set mode.</li> <li>• In the sensing mode, if the key is pressed continuously for about 3 sec., key-protect can be set / released.</li> <li>• In the sensing mode, if the mode selection key is pressed while pressing the increment key (▲), the initial setting mode is obtained.</li> </ul>                      |

In the sensing mode, if both the keys are pressed simultaneously, zero-point adjustment is done.

### Error messages

- When an error occurs, take the following corrective action.

| Error message | Cause                                                   | Corrective action                                                                                                               |
|---------------|---------------------------------------------------------|---------------------------------------------------------------------------------------------------------------------------------|
|               | Overcurrent due to short-circuit.                       | Switch off the power supply and check the load.                                                                                 |
|               | Pressure is being applied during zero-point adjustment. | Applied pressure at the pressure port should be brought to atmospheric pressure and zero-point adjustment should be done again. |
|               | Positive pressure type                                  | Applied pressure exceeds the upper limit of displayable pressure range.                                                         |
|               | Vacuum pressure type                                    | Applied pressure exceeds the lower limit of displayable pressure range.                                                         |
|               | Positive pressure type                                  | Applied pressure exceeds the lower limit of displayable pressure range.                                                         |
|               | Vacuum pressure type                                    | Applied pressure exceeds the upper limit of displayable pressure range.                                                         |

Applied pressure should be brought within the rated pressure range.

### Wiring

The analog voltage output does not incorporate a short-circuit protection circuit. Do not directly connect a power supply or a capacitive load.

- Make sure that the power supply is off while wiring.
- Verify that the supply voltage variation is within the rating.
- If power is supplied from a commercial switching regulator, ensure that the frame ground (F.G.) terminal of the power supply is connected to an actual ground.
- In case noise generating equipment (switching regulator, inverter motor, etc.) is used in the vicinity of this sensor, connect the frame ground (F.G.) terminal of the equipment to an actual ground.
- Do not run the wires together with high-voltage lines or power lines or put them in the same raceway. This can cause malfunction due to induction.

### Conditions in use for CE conformity

- The DP2 series is a CE conformity product complying with EMC Directive. The harmonized standard with regard to immunity that applies to this product is EN 61000-6-2 (Note) and the following condition must be met to conform to that standard.

#### Condition

- The sensor should be connected less than 10 m 32.808 ft from the power supply.

Note: The EN 50082-2 that previously applied to the products for conforming to EMC Directive was replaced by EN 61000-6-2 starting April 1st, 2002.


## PRECAUTIONS FOR PROPER USE

### All models

#### Setting

- If key-protect has been set, make sure to release key-protect before operating the keys.  
(Please refer to 'Key-protect function' for the procedure.)
- Set Value 1 (P-1) and Set Value 2 (P-2) can be made common for all the output modes.
- The setting of Set Value 2 (P-2) with respect to Set Value 1 (P-1) can only be towards the high pressure side in case of the positive pressure type sensor and only towards the high vacuum side in case of the vacuum pressure type sensor.
- Set Value 3 (P-3) is automatically set to the mid-value of Set Value 1 (P-1) and Set Value 2 (P-2).  
(When setting the pressure value for the automatic sensitivity mode)
- The conditions which are set are stored in an EEPROM. Kindly note that the EEPROM has a life span and its guaranteed life is 100,000 write operation cycles.

#### Setting procedure



#### ① Zero-point adjustment


- The displayed pressure when the pressure port is left open is adjusted to zero.




- The sensor will automatically enter the sensing mode when power is supplied.
- Let the pressure port be at atmospheric pressure (i.e., no applied pressure condition), and press, simultaneously, the increment and decrement keys continuously.
- 0.00 is displayed and, when the fingers are released, zero-point adjustment is completed and the sensor returns to the sensing mode.

#### ② Initial setting

- Pressure 'Unit', 'Display' and 'Output mode' of the comparative outputs are set.




- In the sensing mode, press MODE key while pressing ▲ key.
  - Initial setting is displayed.
  - If sensor is being used for the first time, PHd is displayed.
- The settable digit blinks.
- The settable digit changes when ▲ key is pressed and the setting is changed when ▼ key is pressed.



#### ③ Pressure value setting

**For the case when output mode is set to either hysteresis mode ( H ), window comparator mode ( L ) or dual output mode ( d ).**

- 'Set Value 1 (P-1)' and Set Value 2 (P-2)' of the comparative outputs are set.



- Press MODE key in the sensing mode to set to Set Value 1 (P-1) set mode.
- Enter Set Value 1 (P-1) using ▲ key and ▼ key.
- Then, press MODE key to set to Set Value 2 (P-2) set mode.
- Enter Set Value 2 (P-2) using ▲ key and ▼ key.
- Then, press MODE key to set to sensing mode.

**For the case when output mode is set to automatic sensitivity setting mode ( R ).**

- 'Set Value 1 (P-1)', 'Set Value 2 (P-2)' and 'Set Value 3 (P-3)' of the comparative outputs are set.



- Press MODE key in the sensing mode to set to Set Value 1 (P-1) set mode.
- Within the required permissible pressure range, having created a pressure state which is nearest to the atmospheric pressure, press ▼ key to enter Set Value 1 (P-1).
- Then, press MODE key to set to Set Value 2 (P-2) set mode.
- Within the required permissible pressure range, having created a pressure state which is nearest to the high pressure end (for a positive pressure type sensor) or the high vacuum end (for a vacuum pressure type sensor), press ▲ key to enter Set Value 2 (P-2).
- Then, press MODE key to set to Set Value 3 (P-3) set mode.
- Check Set Value 3 (P-3) which has been set automatically. When Set Value 3 (P-3) is to be changed, enter Set Value 3 (P-3) using ▲ key and ▼ key.
- After checking and setting, press MODE key to set to sensing mode.

- The automatically set Set Value 3 (P-3) can be manually changed to a value between Set Value 1 (P-1) and Set Value 2 (P-2).
- If using the window comparator mode, set the pressure value so that there is a difference of 3 digits, or more, between Set Value 1 (P-1) and Set Value 2 (P-2). No output will be possible with a 0 to 2 digit difference.

## PRECAUTIONS FOR PROPER USE

### All models

#### Conversion of pressure units

- In the DP2 series, the conversion to different units is automatically done on changing the setting of the pressure unit. However, this conversion can also be obtained by multiplying the values by the coefficients given in the table on the right.

#### Conversion procedure

- For example, if 2 kPa is to be expressed in kgf/cm<sup>2</sup>,  
since  $1 \text{ kPa} = 1.01972 \times 10^{-2} \text{ kgf/cm}^2$ ,  
2 kPa becomes  
 $2 \times 1.01972 \times 10^{-2} \div 0.020 \text{ kgf/cm}^2$ .

Conversion table for pressure units

|                       | kPa                      | MPa                      | kgf/cm <sup>2</sup>      | bar                      | psi                      | mmHg (Torr)           | inHg                    | atm                      |
|-----------------------|--------------------------|--------------------------|--------------------------|--------------------------|--------------------------|-----------------------|-------------------------|--------------------------|
| 1 kPa                 | 1                        | $1 \times 10^{-3}$       | $1.01972 \times 10^{-2}$ | $1 \times 10^{-2}$       | $1.45038 \times 10^{-1}$ | 7.50062               | 0.2953                  | $9.86923 \times 10^{-3}$ |
| 1 MPa                 | $1 \times 10^3$          | 1                        | $1.01972 \times 10$      | $1 \times 10$            | $1.45038 \times 10^2$    | $7.50062 \times 10^3$ | $0.2953 \times 10^3$    | 9.86923                  |
| 1 kgf/cm <sup>2</sup> | $9.80665 \times 10$      | $9.80665 \times 10^{-2}$ | 1                        | $9.80665 \times 10^{-1}$ | $1.42234 \times 10$      | $7.35559 \times 10^2$ | $2.8959 \times 10$      | $9.67841 \times 10^{-1}$ |
| 1 bar                 | $1 \times 10^2$          | $1 \times 10^{-1}$       | 1.01972                  | 1                        | $1.45038 \times 10$      | $7.50062 \times 10^2$ | $2.953 \times 10$       | $9.86923 \times 10^{-1}$ |
| 1 psi                 | 6.89473                  | $6.89473 \times 10^{-3}$ | $7.03065 \times 10^{-2}$ | $6.89473 \times 10^{-2}$ | 1                        | $5.17147 \times 10$   | 2.036                   | $6.80457 \times 10^{-2}$ |
| 1 mmHg (1 Torr)       | $1.33322 \times 10^{-1}$ | $1.33322 \times 10^{-4}$ | $1.35951 \times 10^{-3}$ | $1.33322 \times 10^{-3}$ | $1.93368 \times 10^{-2}$ | 1                     | $3.9370 \times 10^{-2}$ | $1.31579 \times 10^{-3}$ |
| 1 inHg                | 3.3864                   | $3.3864 \times 10^{-3}$  | $3.4531 \times 10^{-2}$  | $3.3864 \times 10^{-2}$  | 0.4912                   | $2.5400 \times 10$    | 1                       | $3.342 \times 10^{-2}$   |
| 1 atm                 | $1.01325 \times 10^2$    | $1.01325 \times 10^{-1}$ | 1.03323                  | 1.01325                  | $1.46960 \times 10$      | $7.60000 \times 10^2$ | $2.9921 \times 10$      | 1                        |

#### Key-protect function

- Key-protect is a function which prevents any unintentional change in the conditions which have been entered in each setting mode by making the sensor not to respond to the key operations.

#### Setting of key-protect



- In the sensing mode, press **MODE** key continuously for about 3 sec. and release it immediately when **On** is displayed.  
(• Key-protect is set and the sensor returns to the sensing mode.)

#### Release of key-protect



- In the sensing mode, press **MODE** key continuously for about 3 sec. and release it immediately when **OFF** is displayed.  
(• Key-protect is released and the sensor returns to the sensing mode.)

#### Others

- Use within the rated pressure range.
- Do not apply pressure exceeding the pressure with-standability value. The diaphragm will get damaged and correct operation shall not be maintained.
- Do not use during the initial transient time (0.5 sec.) after the power supply is switched on.
- Avoid use of standard type, flat type and light weight type of sensors in places where steam and dust is excessive.
- Take care that the sensor does not come in direct contact with water, oil, grease, or organic solvents, such as, thinner, etc.
- Do not insert wires, etc., into the pressure port. The diaphragm will get damaged and correct operation shall not be maintained.
- Do not operate the keys with pointed or sharp objects.

# DP2


## PRECAUTIONS FOR PROPER USE

### Standard type

#### Setting of pressure lead direction

- The pressure lead direction can be changed by dismantling the pressure port attachment and changing the mounting direction. The tightening torque of the hexagon-socket-head bolt (length: 9 mm 0.354 in or less) should be 0.29 N·m or less.

Note: Make sure to close any unused pressure port with the hexagon-socket-head plug supplied as accessory.




#### Piping

- When connecting a hexagon-socket-head plug or coupling to the pressure port, hold the hexagonal part of the pressure port with a 12 mm 0.472 in spanner and make sure that the tightening torque is 9.8 N·m or less. Also, in order to prevent any leakage, wind a sealing tape on the coupling when connecting. However, sealing tape is not required for North American type (DP2-□F□) using NPTF 1/8 coupling. (Sealing tape is required if NPT 1/8 coupling is used.)



#### Mounting


- When mounting the sensor with the sensor mounting bracket, etc., the tightening torque should be 1.2 N·m or less.



### Flat type Light weight type


#### Setting of pressure lead direction

- The pressure lead direction can be changed by dismantling the pressure port attachment and changing the mounting direction. The tightening torque of the hexagon-socket-head bolt (length: 9 mm 0.354 in or less) should be 0.29 N·m or less.



#### Piping

- When connecting a coupling to the pressure port, hold the pressure port attachment with a 16 mm 0.630 in (light weight type: 10 mm 0.394 in) spanner and make sure that the tightening torque is 9.8 N·m or less (light weight type: 1.47 N·m or less). Also, in order to prevent any leakage, wind a sealing tape on the coupling when connecting.



## PRECAUTIONS FOR PROPER USE


### IP67 type

#### Piping for pressure measurement inlet port

- When connecting a coupling to the pressure measurement inlet port, hold the pressure port attachment with a spanner and make sure that the tightening torque is 9.8 N·m or less. Also, in order to prevent any leakage, wind a sealing tape on the coupling when connecting.


#### Piping for atmospheric pressure inlet port

- If there is a possibility of water entering into the sensor enclosure through the atmospheric pressure inlet port, connect a tube to the atmospheric pressure inlet port through a M5 coupling and extend the other end of the tube to a safe place. In this case, ensure that this end of the tube does not get clogged.



#### Fitting of front cover


- Insert the bosses on the front cover into the guide holes at the bottom of the pressure port attachment, and push in the direction of the arrow to fit the hook. When removing the front cover, release the hook first.



# DP2


## DIMENSIONS (Unit: mm in)

### DP2-20 DP2-21 DP2-22 Standard type




Note: NPTF 1/8 female thread for North American type.

### DP2-80 Light weight type




### DP2-40 DP2-41 DP2-42 Flat type



Note: NPT 1/8 female thread for North American type, and G (PF) 1/8 female thread for European type.

## DIMENSIONS (Unit: mm in)

DP2-60 DP2-61  
DP2-62 IP67 type




Note: NPT 1/8 for North American type, and G (PF) 1/8 for European type.

## MS-DPX


Sensor mounting bracket for standard type (Optional)

### Assembly dimensions



Material: Cold rolled carbon steel (SPCC)  
(Uni-chrome plated)

Two M4 (length 6 mm 0.236 in) pan head screws  
and two spring washers are attached.




# DP2

## DIMENSIONS (Unit: mm in)

### MS-DPX-4


Back angled mounting bracket for standard type (Optional)

#### Assembly dimensions



Material: Cold rolled carbon steel (SPCC)  
(Uni-chrome plated)


Two M4 (length 6 mm 0.236 in) pan head screws  
and two spring washers are attached.



### MS-DPX-2 DPX-04

Panel mounting bracket, front protection cover for standard type (Optional)

#### Assembly dimensions




□ portion shows the front protection cover.

Material: Polycarbonate (Front protection cover)

Nylon 6, Stainless steel (SUS304)(Panel mounting bracket)

#### Panel cut-out dimensions



Note: The panel thickness should be 1 to 3.2 mm 0.039 to 0.126 in.