


ALL RIGHTS RESERVED. NO PORTION OF THIS PUBLICATION, WHETHER IN WHOLE OR IN PART CAN BE REPRODUCED WITHOUT THE EXPRESS WRITTEN CONSENT OF SPC TECHNOLOGY.

REVISIONS					DOC. NO. SPC-F005 * Effective: 12/21/98 * DCP No. 680			
DCP #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD	DATE
	A	RELEASED	JAP	11/28/91				
1116	B	Bulk items added; Was CBS-TO-****	JWM	4/3/01	JC	4/3/01	JC	4/3/01

NOTES:

1. MAXIMUM CURRENT: SAME AS WIRE
2. TEMPERATURE RANGE: 175 °C/347 °F MAX.
3. STRIP AWAY THE END 3/4 INCHES OF WIRE INSULATION
4. TERMINAL MATERIAL: ETP COPPER
5. TERMINAL PLATING: TIN
6. UL LISTED AND CSA CERTIFIED FOR USE ON STRANDED COPPER (AWG) WIRE ONLY



SPC Type No.	Wire Size (AWG)	Stud Size	Pkg QTY	W	C	L	E	U	ØT
SPC3658	12 ~ 10	6 (.138)	1000						
SPC3897	12 ~ 10	8 (.164)	1000	.32	.29	.73	.54	.04	.135
SPC3898	12 ~ 10	10 (.190)	1000						
CBS-TO-1406	16 ~ 14	6 (.138)	1000						
SPC3656	16 ~ 14	6 (.138)	1000						
CBS-TO-1408	16 ~ 14	8 (.164)	1000	.30					.09
SPC3657	16 ~ 14	8 (.164)	1000						
SPC3896	16 ~ 14	10 (.190)	1000						
CBS-TO-1804	22 ~ 18	4 (.112)	1000		.25	.65	.50	.03	
SPC3653	22 ~ 18	4 (.112)	1000						
CBS-TO-1806	22 ~ 18	6 (.138)	1000	.25					.07
SPC3654	22 ~ 18	6 (.138)	1000						
CBS-TO-1808	22 ~ 18	8 (.164)	1000	.30					
SPC3655	22 ~ 18	8 (.164)	1000	.30					

LISTED



E38918



LR22190M6

OSHA
Acceptable

SPC-F005.DWG

DISCLAIMER:
ALL STATEMENTS AND TECHNICAL INFORMATION CONTAINED HEREIN ARE BASED UPON INFORMATION AND/OR TESTS WE BELIEVE TO BE ACCURATE AND RELIABLE. SINCE CONDITIONS OF USE ARE BEYOND OUR CONTROL, WE CANNOT GUARANTEE THE SUITABILITY OF OUR PRODUCTS FOR THE INTENDED USE AND ASSUME ALL RISK AND LIABILITY WHATSOEVER IN CONNECTION THEREWITH.



SPC TECHNOLOGY

UNLESS OTHERWISE

SPECIFIED,
DIMENSIONS ARE
FOR REFERENCE
PURPOSES ONLY.

DRAWN BY:	DATE:
JC	3/7/91
CHECKED BY:	DATE:
JC	12/27/91
APPROVED BY:	DATE:
JL	11/27/91

DRAWING TITLE:

Non-Insulated Block Fork Terminals

SIZE	DWG. NO.	ELECTRONIC FILE	REV
A	TA-317	TA-317.dwg	B
SCALE:	NTS	U.O.M.: INCHES [mm]	SHEET: 1 OF 1