




REVISONS		DATE	BY	APP'D
CE	16			
F	LNR			
T	REV PER EC 0A40-0096-03	20MAR03	DUF	TD

1. DIMENSIONS IN [] ARE IN INCHES
E MAXIMUM CONNECTOR LOSS IS EQUAL TO 0.50 dB
PLUS CABLE ATTENUATION.



VIEW A-A
NOT TO SCALE

FIBER PATH	
LEFT CONNECTOR	RIGHT CONNECTOR
A	B
B	A



VIEW B-B
NOT TO SCALE

THIS DRAWING IS A CONTROLLED DOCUMENT.			
DESIGNER: KRAYBILL	DATE: 07/98	AMP	AMP Incorporated Harrisburg, PA 17105-3608
APPROVED: J. SWARTZBAUGH	DATE: 07/98	NAME:	CABLE ASSY, FIBER OPTIC, 62.5/125µm, TWIN Z/P RISER, MT-RJ TO MT-RJ, OPTIMATE
DRAWN: J. SWARTZBAUGH	DATE: 07/98	SIZE:	A2
CHECKED: J. SWARTZBAUGH	DATE: 07/98	DRAWING NO:	00779
DATE: 07/98	DATE: 07/98	SCALE:	1" = 2'
DATE: 07/98	DATE: 07/98	SHEET:	1 OF 2
DATE: 07/98	DATE: 07/98	REV:	T
DATE: 07/98	DATE: 07/98	RESTRICTED TO:	
DATE: 07/98	DATE: 07/98	WEIGHT:	
DATE: 07/98	DATE: 07/98	CUSTOMER DRAWING:	

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION. 19
 © COPYRIGHT 19 BY AMP INCORPORATED. ALL RIGHTS RESERVED.

LOG	EXT	REVISIONS						
CE	16	P	LYR	DESCRIPTION	DATE	OWN	APVD	
			T	REV PER EC 0A40-0096-03	20MAR03	DLF	TD	

0.50		0.31±0.05	[12.0±2.0]	9-1278032-9
0.51		7.62±0.08	[300±3.0]	9-1278032-8
0.50		0.61±0.05	[24.0±2.0]	9-1278032-7
0.50		0.50±0.05	[19.7±2.0]	9-1278032-6
0.50		1.50±0.05	[59.1±2.0]	9-1278032-5
0.50		2.50±0.05	[98.4±2.0]	9-1278032-4
1.25	500.00±5.00	19.658.03±196.9		9-1278032-3
0.60	200.00±2.00	7874.01±78.74		9-1278032-2
0.85	100.00±1.00	3937.01±39.37		9-1278032-1
0.62	80.00±0.80	3149.61±31.50		8-1278032-0
0.61	76.00±0.76	2692.13±29.92		7-1278032-6
0.61	75.00±0.75	2952.76±29.53		7-1278032-5
0.60	68.00±0.68	2677.17±26.77		6-1278032-8
0.60	66.00±0.66	2598.43±25.98		6-1278032-6
0.59		81.0±0.6	[2402±24]	6-1278032-1
0.58		55.00±0.55	[2165.35±121.85]	5-1278032-5
0.58		50.00±0.50	[1968.50±19.69]	5-1278032-0
0.57		45.00±0.45	[1771.65±17.72]	4-1278032-5
0.56		40.00±0.40	[1574.80±15.75]	4-1278032-0
0.55		31.0±0.3	[1220.0±12.0]	3-1278032-1
0.55		30.00±0.30	[1181.10±11.81]	3-1278032-0
0.54		24.00±0.30	[944.88±11.81]	2-1278032-4
0.53		20±.3	[787±12.0]	2-1278032-0
0.52		15.0±0.15	[590.6±6]	1-1278032-5
0.52		13.0±.0.15	[511.8±6.0]	1-1278032-3
0.52		12.0±0.15	[472.4±6.0]	1-1278032-2
0.52		10.0±0.15	[393.7±6]	1-1278032-0
0.51		8.0±0.15	[315.0±6.0]	1278032-8
0.51		7.0±0.08	[275.6±3]	1278032-7
0.51		6.0±0.08	[236.2±3]	1278032-6
0.51		5.0±0.08	[196.9±3]	1278032-5
0.51		4.0±0.08	[157.5±3.0]	1278032-4
0.50		3.0±0.05	[118.1±2.0]	1278032-3
0.50		2.0±0.05	[78.7±2.0]	1278032-2
0.50		1.0±0.05	[39.4±2.0]	1278032-1

[illegible]