






PRODUCT NR.
85922-XYZ
85922-XYZLF

| PLATING CONTACT AREA: | | | | | |
|-----------------------|-------------------|--|--|--|--|
| DASH NR: | PERFORMANCE LEVEL | | | | |
| -1YY/1YYLF | TELCORDIA CO | | | | |
| -2YY/2YYLF | CUSTOMER SPECIAL | | | | |
| -3YY/3YYLF | CUSTOMER SPECIAL | | | | |



RECOMMENDED HOLE PATTERN,
COMPONENT SIDE.

| DASH NR | CONFIGURATION | | | | | PCB THICKN. | DIM A | DIM B | DIM C | DIM D |
|---------|---------------|---|---|---|---|-------------|-------|-------|-------|-------|
| | ROW # | 6 | 5 | 4 | 3 | | | | | |
| -X01 | D | + | + | + | + | + | 2.4 | 14.14 | 3.50 | 0.54 |
| | C | + | + | + | + | + | | | | |
| | B | + | + | + | + | + | | | | |
| | A | + | + | + | + | + | | | | |
| -X02 | D | + | + | + | + | + | 3.2 | 13.60 | 4.04 | 0.00 |
| | C | + | + | + | + | + | | | | |
| | B | + | + | + | + | + | | | | |
| | A | + | + | + | + | + | | | | |
| -X03 | D | + | + | + | + | + | 2.4 | 13.60 | 3.24 | 0.00 |
| | C | + | + | + | + | + | | | | |
| | B | + | + | + | + | + | | | | |
| | A | + | + | + | + | + | | | | |
| -X04 | D | + | + | + | + | + | 1.6 | 13.60 | 2.39 | 0.00 |
| | C | + | + | + | + | + | | | | |
| | B | + | + | + | + | + | | | | |
| | A | + | + | + | + | + | | | | |
| -X05 | D | + | + | + | + | + | 1.6 | 14.14 | 2.70 | 0.54 |
| | C | + | + | + | + | + | | | | |
| | B | + | + | + | + | + | | | | |
| | A | + | + | + | + | + | | | | |
| -X06 | D | + | + | + | + | + | 1.6 | 14.64 | 3.00 | 0.54 |
| | C | + | + | + | + | + | | | | |
| | B | + | + | + | + | + | | | | |
| | A | + | + | + | + | + | | | | |
| -X07 | D | + | + | + | + | + | 1.6 | 15.14 | 2.50 | 0.54 |
| | C | + | + | + | + | + | | | | |
| | B | + | + | + | + | + | | | | |
| | A | + | + | + | + | + | | | | |
| -X20 | D | + | + | + | + | - | 2.4 | 14.14 | 3.50 | 0.54 |
| | C | + | + | + | + | - | | | | |
| -X20LF | B | + | + | + | + | - | | | | |
| | A | + | + | + | + | + | | | | |

"-" POSITION NOT LOADED
"+" POSITION LOADED

NOTES:

1. BODY MATL: LIQUID CRYSTAL POLYMER 30% GLASS FLAME RETARDANT ACC. UL 94-VO
2. TERMINAL MATERIAL: PHOSPHOR BRONZE.
3. PLATING SOLDERTAILS 2-8 μ m SnPb 90-97 OR 2-8 μ m PURE FOR LF.
4. LOAD IN THIS DIRECTION (E.G. THROUGH CODING) 30 NEWTON MAXIMUM PER CONNECTOR.
5. LOAD IN THIS DIRECTION 15 NEWTON MAXIMUM PER CONNECTOR.
6. TO ENSURE PROPER ALIGNMENT OF MULTIPLE MODULES ON A BOARD THE USE OF A FIXTURE IS RECOMMENDED.
7. PRODUCT MARKING: PARTNUMBER & BATCH I.D.
8. THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AS DESCRIBED IN GS-22-008.
9. THE HOUSING WILL WITHSTAND EXPOSURE TO 260 DEGREE PEAK TEMPERATURE FOR 10 SECONDS IN A WAVE SOLDER APPLICATION.

| matl. code | tolerances unless otherwise specified | CUSTOMER COPY | FCI | electronics |
|------------|---------------------------------------|---------------|---------------|--------------------|
| Ltr | tech no | dr. date | projection | www.tcdconnect.com |
| H | 0000-0170 | 00005/22/02 | linear | |
| J | 0000-0171 | 00007/10/02 | | |
| X | 0000-0000 | 00005/26/02 | employees | |
| | dr. | M. MEIER | 960313 | |
| E | 0000-0172 | 00004/22/02 | | |
| F | 0000-0173 | 00006/04/02 | dr. P. SCHALK | 960313 |
| G | 0000-0071 | 00004/11/02 | scale | |
| | dr. | P. SCHALK | 960313 | |
| | sheet | 5:1 | A1 | 85922 |
| | revision | | | sheet 1 of 1 |
| | index | | | |
| | sheet | | | |
| | | | | |