



LOC	DIST	REVISIONS					
AD	47	P	LTR	DESCRIPTION	DATE	DWN	APVD
			D2	REVISED PER ECO-12-007590	19JUL12	KH	MH




- ① HOUSING: LIQUID CRYSTAL POLYMER, COLOR BLACK.
CONTACTS: HIGH RELIABILITY COPPER ALLOY.
GROUND BUSSES: BRASS, UNS C26000
- ② CONTACTS & GROUND BUSES: NICKEL UNDERPLATE ALL OVER,
MATING SURFACE PLATED TO MEET LEVEL 2 PERFORMANCE
REQUIREMENTS OF TE PRODUCT SPECIFICATION 108-1422,
SOLDER TAILS PLATED TIN-LEAD.
- ③ DATE CODE MARKED IN AREA INDICATED ON SIDE OPPOSITE
POSITION #1.
- ④ ONE GROUND BUS WITH 5 TAILS PER EACH MODULE.
- ⑤ TOLERANCE NON-ACCUMULATIVE.
- ⑥ FOR STANDARD APPLICATIONS, ORIENTATION HOLE TO BE
 $\phi.094 \pm .002 [2.39 \pm 0.05]$.
FOR SLIP-FIT APPLICATIONS, ORIENTATION HOLE TO BE
 $\phi.079 \pm .001 [2.00 \pm 0.03]$.
- ⑦ CONNECTORS PACKAGED ON 13 INCH DIA REELS PER EIA 481.
- ⑧ NOT RELEASED FOR PRODUCTION.




Ⓐ	NO	4.724[120]	3.000[76.2]	6	3.450[87.63]	3.898[99.01]	4.000[101.6]	266	1-767127-4
Ⓐ	NO	4.094[104]	2.500[63.5]	5	2.950[74.93]	3.398[86.31]	3.500[88.9]	228	1-767127-3
	NO	4.094[104]	2.000[50.8]	4	2.450[62.23]	2.898[73.61]	3.000[76.2]	190	1-767127-2
	NO	3.465[88]	1.500[38.1]	3	1.950[49.53]	2.398[60.91]	2.500[63.5]	152	1-767127-1
Ⓐ	NO	2.835[72]	1.000[25.4]	2	1.450[36.83]	1.898[48.21]	2.000[50.8]	114	1-767127-0
Ⓐ	NO	2.205[56]	.500[12.7]	1	.950[24.13]	1.398[35.51]	1.500[38.1]	76	767127-9
Ⓐ	NO	1.732[44]	.000[0]	0	.450[11.43]	.898[22.81]	1.000[25.4]	38	767127-8
Ⓐ	YES	4.724[120]	3.000[76.2]	6	3.450[87.63]	3.898[99.01]	4.000[101.6]	266	767127-7
Ⓐ	YES	4.094[104]	2.500[63.5]	5	2.950[74.93]	3.398[86.31]	3.500[88.9]	228	767127-6
	YES	4.094[104]	2.000[50.8]	4	2.450[62.23]	2.898[73.61]	3.000[76.2]	190	767127-5
	YES	3.465[88]	1.500[38.1]	3	1.950[49.53]	2.398[60.91]	2.500[63.5]	152	767127-4
Ⓐ	YES	2.835[72]	1.000[25.4]	2	1.450[36.83]	1.898[48.21]	2.000[50.8]	114	767127-3
Ⓐ	YES	2.205[56]	.500[12.7]	1	.950[24.13]	1.398[35.51]	1.500[38.1]	76	767127-2
Ⓐ	YES	1.732[44]	.000[0]	0	.450[11.43]	.898[22.81]	1.000[25.4]	38	767127-1
	VACUUM COVER INCLUDED	F	E	D	C	B	A	NO OF POS	PART NUMBER

SEE SHEET 2 FOR RECOMMENDED PC BOARD LAYOUT
AND PACKAGING DETAIL


THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J. GERACE	7-9-99	 TE Connectivity	
		CHK S. STRICKLER	7-9-99		
DIMENSIONS:		APVD A. MONK		NAME	
INCHES		PRODUCT SPEC		PLUG ASSEMBLY, .495[12.57] VERTICAL, .025[0.64]CL, GULL WING LEADS, POCKET TAPE PACKAGED, MICTOR	



PACKAGING DETAIL $\triangle 7$
SCALE 2:1
DIMENSIONS ARE FOR REFERENCE



RECOMMENDED PC BOARD LAYOUT
(VIEWED FROM CONNECTOR SIDE)

THIS DRAWING IS A CONTROLLED DOCUMENT.				DWN J. GERACE	7-9-99	 TE Connectivity																									
				CHK S. STRICKLER	7-9-99																										
DIMENSIONS: INCHES 		TOLERANCES UNLESS OTHERWISE SPECIFIED: <table><tr><td>0. PLC</td><td>±</td><td>-</td></tr><tr><td>1. PLC</td><td>±</td><td>-</td></tr><tr><td>2. PLC</td><td>±</td><td>-</td></tr><tr><td>3. PLC</td><td>±</td><td>.005[0.13]</td></tr><tr><td>4. PLC</td><td>±</td><td>-</td></tr><tr><td>ANGLES</td><td>±</td><td>-</td></tr><tr><td>FINISH</td><td>-</td><td>-</td></tr></table>			0. PLC	±	-	1. PLC	±	-	2. PLC	±	-	3. PLC	±	.005[0.13]	4. PLC	±	-	ANGLES	±	-	FINISH	-	-	APPROV A. MONK	7-9-99	NAME PLUG ASSEMBLY, .495[12.57] VERTICAL, .025[0.64]CL, GULL WING LEADS, POCKET TAPE PACKAGED, MICTOR			
					0. PLC	±	-																								
					1. PLC	±	-																								
					2. PLC	±	-																								
					3. PLC	±	.005[0.13]																								
4. PLC	±	-																													
ANGLES	±	-																													
FINISH	-	-																													
PRODUCT SPEC 108-1422																															
APPLICATION SPEC 114-11004																															
SIZE A1	CAGE CODE 00779	DRAWING NO C=767127																													
RESTRICTED TO -																															
MATERIAL -		WEIGHT -			CUSTOMER DRAWING																										
					SCALE 8:1		SHEET 2 OF 2		REV D2																						