



# 1075MP

## 75 Watts, 50 Volts, Class C

### Avionics 1025 - 1150 MHz

#### GENERAL DESCRIPTION

The 1075MP is a COMMON BASE bipolar transistor. It is designed for pulsed systems in the frequency band 1025-1150 MHz. The device has gold thin-film metallization for proven highest MTTF. The transistor includes input prematch for broadband capability. Low thermal resistance package reduces junction temperature, extends life.

#### ABSOLUTE MAXIMUM RATINGS

Maximum Power Dissipation @ 25°C<sup>2</sup> 250 Watts Pk


#### Maximum Voltage and Current

BVces	Collector to Emitter Voltage	65 Volts
BVebo	Emitter to Base Voltage	3.5 Volts
Ic	Collector Current	6.5 Amps Pk

#### Maximum Temperatures

Storage Temperature	- 65 to + 150°C
Operating Junction Temperature	+ 200°C

#### CASE OUTLINE 55FW-1



#### ELECTRICAL CHARACTERISTICS @ 25°C


SYMBOL	CHARACTERISTICS	TEST CONDITIONS	MIN	TYP	MAX	UNITS
P <sub>OUT</sub>	Power Out	F= 1025-1150 MHz V <sub>cc</sub> = 50 Volts PW = 10 $\mu$ sec, DF = 1%	75			W
P <sub>IN</sub>	Power Input				13	W
P <sub>G</sub>	Power Gain		7.6	8.5		dB
$\eta$ <sub>C</sub>	Efficiency			40		%
VSWR <sup>1</sup>	Load Mismatch Tolerance	F = 1090 MHz			20:1	

#### FUNCTIONAL CHARACTERISTICS @ 25°C


BVebo	Emitter to Base Breakdown	I <sub>e</sub> = 5 mA	3.5			V
BVces	Collector to Emitter Breakdown	I <sub>c</sub> = 15mA	65			V
H <sub>fe</sub>	DC Current Gain	V <sub>ce</sub> = 5V, I <sub>c</sub> = 100 mA	20			
C <sub>ob</sub>	Output Capacitance	V <sub>cb</sub> = 50 V, f = 1 MHz		12		pF
$\theta$ <sub>jc</sub> <sup>1</sup>	Thermal Resistance				0.6	°C/W

Note 1: At rated pulse conditions

Rev A: Dec 2009




Microsemi reserves the right to change, without notice, the specifications and information contained herein. Visit our web site at [www.microsemi.com](http://www.microsemi.com) or contact our factory direct.



**STYLE 1:**  
**PIN1 = COLLECTOR**  
**2 = BASE (2X)**  
**3 = Emitter**

**STYLE 2:**  
**PIN1 = COLLECTOR**  
**2 = Emitter (2X)**  
**3 = BASE**



DIM	MILLIMETER	$\pm$ TOL	INCHES	$\pm$ TOL
A	5.08	.13	.200	.005
B	7.11 DIA	.13	.280 DIA	.005
C	0.13	.02	.005	.001
D	1.40	.13	.055	.005
E	26.92	.64	1.060	.025
F	45°	5°	45°	5°
G	3.94	REF	.155	REF
H	2.54	.13	.100	.005

DWG NO.

55FW



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Microsemi:](#)

[1075MP](#)