

B




Tactile Switches


B




PTS645S Model

**PTS645V Model**


S STRAIGHT




PCB LAYOUT




STRAIGHT WITH ESD PIN




PCB LAYOUT





V VERTICAL



PCB LAYOUT



SMT



Dimensions are shown: mm (inches)
Specifications and dimensions subject to change

PTS645 Series 6 mm Tact Switches

ACTUATION FORCE




OPTION CODE	FORCE
L	130 grams
M	160 grams
H	200 grams
K	260 grams

ACTUATOR HEIGHT




OPTION CODE	DIMENSION H	TERMINATION	SCHEMATIC	
			Without EMC pin	With EMC pin
43	4,3 (.169)	Thru-hole and SMT		
50	5,0 (.197)	Thru-hole and SMT		
70	7,0 (.275)	Thru-hole and SMT		
95	9,5 (.374)	Thru-hole and SMT		
31	3,15 (.124)	Vertical		
39	3,85 (.151)	Vertical		
58	5,85 (.230)	Vertical		
83	8,35 (.329)	Vertical		


43




50




70




95




31





39



58



83



First Angle
Projection

PTS645 Series
6 mm Tact Switches

TAPE & REEL

Tactile Switches

B

