

9097250 TOSHIBA (DISCRETE/OPTO)

56C 07646 DT-33-11

SILICON NPN TRIPLE DIFFUSED TYPE

2SC3180


POWER AMPLIFIER APPLICATIONS.

FEATURES:

- . Complementary to 2SA1263
- . Recommend for 40W High Fidelity Audio Frequency Amplifier Output Stage.

MAXIMUM RATINGS (Ta=25°C)

CHARACTERISTIC	SYMBOL	RATING	UNIT
Collector-Base Voltage	V_{CBO}	80	V
Collector-Emitter Voltage	V_{CEO}	80	V
Emitter-Base Voltage	V_{EBO}	5	V
Collector Current	I_C	6	A
Base Current	I_B	0.6	A
Collector Power Dissipation ($T_c=25^{\circ}\text{C}$)	P_C	60	W
Junction Temperature	T_j	150	$^{\circ}\text{C}$
Storage Temperature Range	T_{stg}	-55 ~ 150	$^{\circ}\text{C}$



Weight : 4.6g

ELECTRICAL CHARACTERISTICS ($T_a=25^{\circ}\text{C}$)

CHARACTERISTIC	SYMBOL	TEST CONDITION	MIN.	TYP.	MAX.	UNIT
Collector Cut-off Current	I_{CBO}	$V_{CB}=80V, I_E=0$	-	-	5.0	μA
Emitter Cut-off Current	I_{EBO}	$V_{EB}=5V, I_C=0$	-	-	5.0	μA
Collector-Emitter Breakdown Voltage	$V_{(BR)CEO}$	$I_C=50mA, I_B=0$	80	-	-	V
DC Current Gain	$h_{FE(1)}$ (Note)	$V_{CE}=5V, I_C=1A$	55	-	160	
	$h_{FE(2)}$	$V_{CE}=5V, I_C=3A$	35	75	-	
Collector Emitter Saturation Voltage	$V_{CE(sat)}$	$I_C=5A, I_B=0.5A$	-	0.45	2.0	V
Base-Emitter Voltage	V_{BE}	$V_{CE}=5V, I_C=3A$	-	0.92	1.5	V
Transition Frequency	f_T	$V_{CE}=5V, I_C=1A$	-	30	-	MHz
Collector Output Capacitance	C_{ob}	$V_{CB}=10V, I_E=0, f=1MHz$	-	105	-	pF







Note : $h_{FE(1)}$ Classification, R : 55~110 O : 80~160

||||| TOSHIBA CORPORATION

9097250 TOSHIBA (DISCRETE/OPTO)

56C J7547

DT-33-11

2SC3180

TOSHIBA CORPORATION