


0.5mm Pitch Board to Board Connector

DF17 Series



■Features

1. DF17 series are the connector which has been developed mainly for the mobile phone.

Connector Problems Involving in Mobile phone
Example:



The following problems can be solved;

"Connector Damage Caused when Mobile phone is Dropped"

"Electrical Discontinuity in Printed Circuit Board is Fixed (Fastened by screws)"

Especially, in regard to the resistance to the drop shock, Hirose has developed a new connector structure utilizing its unique technology, and greatly enhanced the resistance to the drop shock.

In broad variation development, the connector can be utilized in wide fields of LCD equipment, miniature information terminal equipment and so on, in addition to mobile phones.



2. Performance Enhancement

The receptacle is designed in a BOX structure and has also enhanced shock-proof, pinch-proof and scoop-proof performance.

In addition, the receptacle contact has employed the high scoop-proof bellows type.

3. With Metal Fitting available




In order to grade up the strength against the mechanical stress, the metal fitting specification is also available.

4. Broad Variations in Contact Number

The connectors are lined up per 10 contacts between 20 and 80 contacts to take countermeasures for multi-signalization.

5. Stacking Height 4 to 8mm

The stacking height can be selected (per millimeter) between 4mm and 8mm in combination of the receptacle with the header.



● : Available
▲ : Under plan

Header \ Receptacle		DF17#(□)-*DS-0.5V	
		3.0	4.0
DF17#(□)-*DP-0.5V	2.0	5mm	6mm
	2.5	5.5mm	6.5mm
	4.0	7mm	8mm

Receptacle \ Header		DF17(3.0H)-*DS-0.5V
DF17(1.0H)-*DP-0.5V	4mm	

Note : The stacking height doesn't include the solder paste thickness.

■ Applications

Mobile phones, LCD, miniature equipment and so on

DF17 Series 0.5mm Pitch Board to Board Connector

Product Specifications

Rating	Current rating Voltage rating	0.3A 50V AC	Operating Temperature Range Operating Humidity Range	-35 to 85℃ (Note 1) 40 to 80%	Storage Temperature Range Storage Humidity Range	-10 to 60℃(Note 2) 40 to 70%
--------	----------------------------------	----------------	---	----------------------------------	---	---------------------------------

Item	Specification	Condition
1. Insulation Resistance	500M ohms min.	100V DC
2. Withstanding voltage	No flashover or insulation breakdown.	150V AC/1 minute
3. Contact Resistance	60m ohms max.	100mA
4. Vibration	No electrical discontinuity of 1μs or more	Frequency: 10 to 55 Hz, single amplitude of 0.75 mm, 2 hours in each of the 3 directions.
5. Humidity (Steady state)	Contact resistance: 60m ohms max. Insulation resistance: 250M ohms min.	96 hours at temperature of 40℃ and humidity of 90% to 95%
6. Temperature Cycle	Contact resistance: 60m ohms max. Insulation resistance: 500M ohms min.	(-55℃: 30 minutes 5 to 35℃: 10 minutes 85℃: 30 minutes 5 to 35℃: 10 minutes) 5 cycles
7. Durability (Mating/un-mating)	Contact resistance: 60m ohms	50 cycles
8. Resistance to Soldering heat	No deformation of components affecting performance.	Reflow: At the recommended temperature profile Manual soldering: 350℃ for 3 seconds

Note 1: Includes temperature rise caused by current flow.
 Note 2: The term "storage" refers to products stored for long period of time prior to mounting and use. Operating Temperature Range and Humidity range covers non conducting condition of installed connectors in storage, shipment or during transportation.
 Note 3: Information contained in this catalog represents general requirements for this Series. Contact us for the drawings and specifications for a specific part number shown.

Material

Product	Part	Material	Finish	Remarks
Receptacle	Insulator	Polyamide	White	UL94V-0
	Contact	Phosphor copper	Gold plated (Note 1)	———
	Metal Fitting	Phosphor copper	Tin-lead plated	———
Header	Insulator	Polyamide	White	UL94V-0
	Contact	Phosphor copper	Gold plated (Note 2)	———
	Metal Fitting	Phosphor copper	Tin-lead plated	———

Note1: DF17(0.3)-*DS-0.5V : Contact area: gold plating/lead area: flash gold plated
 DF17(4.0)-*DS-0.5V : Contact area: gold plating/lead area: tin plated
 DF17(4.0)-*DP-0.5V : Contact area: gold plating/lead area: tin plated
 Note2: The header gold plated product:Contact area: gold plating/lead area: tin plated
 DF17(1.0H)-*DS-0.5V only: Contact area: gold plating/lead area: flash gold plated


Ordering Information

Receptacle/Header

DF17 # (**) - * DS - 0.5 V (**)
 ① ② ③ ④ ⑤ ⑥ ⑦ ⑧

① Series Name: DF17	④ Number of Contacts 20,26,30,40,50,60,70,80 contacts									
② Type	⑤ Connector Type DS: Receptacle DP: Header									
<table><tr><td></td><td>Fitting</td><td>Boss</td></tr><tr><td>DF17</td><td>○</td><td>○</td></tr><tr><td>DF17B</td><td>○</td><td>×</td></tr></table>		Fitting	Boss	DF17	○	○	DF17B	○	×	⑥ Contact Pitch: 0.5mm
	Fitting	Boss								
DF17	○	○								
DF17B	○	×								
	⑦ Contact Type V: Straight SMT									
③ Product height The stacking height can be determined by adding the figures in parentheses to receptacle and header.	⑧ Packaging Type (57):Gold plated,embossed tape packaging									

■ Receptacle With metal fitting



● Stacking Height: 4mm

Part Number	CL No.	Number of Contacts	A	B	C	D	E	F	G	H	RoHS
DF17(3.0H)-26DS-0.5V(57)	683-0253-2-57	26	11.5	8.3	7.0	6.0	8.5	11.3	3.0	3.0	YES
DF17(3.0H)-30DS-0.5V(57)	683-0268-0-57	30	12.5	9.3	8.0	7.0	9.5	12.3			
DF17(3.0H)-60DS-0.5V(57)	683-0361-5-57	60	20.0	16.8	15.5	14.5	17.0	19.8			
DF17(3.0H)-70DS-0.5V(57)	683-0393-1-57	70	22.5	19.3	18.0	17.0	19.5	22.3			
DF17(3.0H)-80DS-0.5V(57)	683-0369-7-57	80	25.0	21.8	20.5	19.5	22.0	24.8			

● Stacking Height: 5mm, 7mm

Part Number	CL No.	Number of Contacts	A	B	C	D	E	F	G	H	RoHS
DF17(3.0)- 20DS-0.5V(57)	683-0002-2-57	20	10.0	6.8	5.5	4.5	7.0	9.8	3.5	3.0	YES
DF17(3.0)- 26DS-0.5V(57)	683-0241-3-57	26	11.5	8.3	7.0	6.0	8.5	11.3			
DF17(3.0)- 30DS-0.5V(57)	683-0003-5-57	30	12.5	9.3	8.0	7.0	9.5	12.3			
DF17(3.0)- 40DS-0.5V(57)	683-0004-8-57	40	15.0	11.8	10.5	9.5	12.0	14.8			
DF17(3.0)- 50DS-0.5V(57)	683-0005-0-57	50	17.5	14.3	13.0	12.0	14.5	17.3			
DF17(3.0)- 60DS-0.5V(57)	683-0006-3-57	60	20.0	16.8	15.5	14.5	17.0	19.8			
DF17(3.0)- 70DS-0.5V(57)	683-0007-6-57	70	22.5	19.3	18.0	17.0	19.5	22.3			
DF17(3.0)- 80DS-0.5V(57)	683-0008-9-57	80	25.0	21.8	20.5	19.5	22.0	24.8			

● Stacking Height: 6mm, 8mm


Part Number	CL No.	Number of Contacts	A	B	C	D	E	F	G	H	RoHS
DF17(4.0)-20DS-0.5V(57)	683-0042-7-57	20	10.0	6.8	5.5	4.5	7.0	9.8	4.5	4.0	YES
DF17(4.0)-30DS-0.5V(57)	683-0043-0-57	30	12.5	9.3	8.0	7.0	9.5	12.3			
DF17(4.0)-40DS-0.5V(57)	683-0044-2-57	40	15.0	11.8	10.5	9.5	12.0	14.8			
DF17(4.0)-50DS-0.5V(57)	683-0045-5-57	50	17.5	14.3	13.0	12.0	14.5	17.3			
DF17(4.0)-60DS-0.5V(57)	683-0046-8-57	60	20.0	16.8	15.5	14.5	17.0	19.8			
DF17(4.0)-70DS-0.5V(57)	683-0047-0-57	70	22.5	19.3	18.0	17.0	19.5	22.3			
DF17(4.0)-80DS-0.5V(57)	683-0048-3-57	80	25.0	21.8	20.5	19.5	22.0	24.8			

Note 1. In regard to this product, the embossed tape packaging is the standard packaging. (1000 pcs./ reel.)

Note 2. If the without boss specification is required, please contact HRS sales department.

DF17 Series 0.5mm Pitch Board to Board Connector

Header With metal fitting



● Stacking Height: 4mm

Part Number	CL No.	Number of Contacts	A	B	C	D	E	F	G	H	RoHS
DF17(1.0H)-26DP-0.5V(57)	683-0257-3-57	26	11.5	8.2	7.1	6.0	8.5	11.3	3.3	1.0	YES
DF17(1.0H)-30DP-0.5V(57)	683-0272-7-57	30	12.5	9.2	8.1	7.0	9.5	12.3			
DF17(1.0H)-60DP-0.5V(57)	683-0365-6-57	60	20.0	16.7	15.6	14.5	17.0	19.8			
DF17(1.0H)-70DP-0.5V(57)	683-0397-2-57	70	22.5	19.2	18.1	17.0	19.5	22.3			
DF17(1.0H)-80DP-0.5V(57)	683-0373-4-57	80	25.0	21.7	20.6	19.5	22.0	24.8			

● Stacking Height: 5mm, 6mm

Part Number	CL No.	Number of Contacts	A	B	C	D	E	F	G	H	RoHS
DF17(2.0)- 20DP-0.5V(57)	683-0082-1-57	20	10.0	6.7	5.6	4.5	7.0	9.8	4.3	2.0	YES
DF17(2.0)- 30DP-0.5V(57)	683-0083-4-57	30	12.5	9.2	8.1	7.0	9.5	12.3			
DF17(2.0)- 40DP-0.5V(57)	683-0084-7-57	40	15.0	11.7	10.6	9.5	12.0	14.8			
DF17(2.0)- 50DP-0.5V(57)	683-0085-0-57	50	17.5	14.2	13.1	12.0	14.5	17.3			
DF17(2.0)- 60DP-0.5V(57)	683-0086-2-57	60	20.0	16.7	15.6	14.5	17.0	19.8			
DF17(2.0)- 70DP-0.5V(57)	683-0087-5-57	70	22.5	19.2	18.1	17.0	19.5	22.3			
DF17(2.0)- 80DP-0.5V(57)	683-0088-8-57	80	25.0	21.7	20.6	19.5	22.0	24.8			

● Stacking Height: 7mm, 8mm

Part Number	CL No.	Number of Contacts	A	B	C	D	E	F	G	H	RoHS
DF17(4.0)-20DP-0.5V(57)	683-0122-4-57	20	10.0	6.7	5.6	4.5	7.0	9.8	6.3	4.0	YES
DF17(4.0)-30DP-0.5V(57)	683-0123-7-57	30	12.5	9.2	8.1	7.0	9.5	12.3			
DF17(4.0)-40DP-0.5V(57)	683-0124-0-57	40	15.0	11.7	10.6	9.5	12.0	14.8			
DF17(4.0)-50DP-0.5V(57)	683-0125-2-57	50	17.5	14.2	13.1	12.0	14.5	17.3			
DF17(4.0)-60DP-0.5V(57)	683-0126-5-57	60	20.0	16.7	15.6	14.5	17.0	19.8			
DF17(4.0)-70DP-0.5V(57)	683-0127-8-57	70	22.5	19.2	18.1	17.0	19.5	22.3			
DF17(4.0)-80DP-0.5V(57)	683-0128-0-57	80	25.0	21.7	20.6	19.5	22.0	24.8			

● Stacking Height: 5.5mm, 6.5mm


Part Number	CL No.	Number of Contacts	A	B	C	D	E	F	G	H	RoHS
DF17(2.5)-26DP-0.5V(57)	683-0245-4-57	26	11.5	8.2	7.1	6.0	8.5	11.3	4.8	2.5	YES
DF17(2.5)-80DP-0.5V(57)	683-0168-5-57	80	25.0	21.7	20.6	19.5	22.0	24.8			

Note 1. In regard to this product, the embossed tape packaging is the standard packaging. (1000 pcs./reel.)

Note 2. If the without boss specification is required, please contact HRS sales department.

■ PCB mounting pattern

- Receptacle
- Header



Number of Contacts	D	E	J	K
20	4.5	7.0	10.4	7.6
26	6.0	8.5	11.9	9.1
30	7.0	9.5	12.9	10.1
40	9.5	12.0	15.4	12.6
50	12.0	14.5	17.9	15.1
60	14.5	17.0	20.4	17.6
70	17.0	19.5	22.9	20.1
80	19.5	22.0	25.4	22.6


S	
Receptacle	4.3
Header	4

* The recommended solder paste thickness is 150μm.

- Note 1.  If the pattern is included in the shaded area, and not treated with resist, it could touch the connector contact.
- Note 2. If the boss isn't included, the boss hole shown in the above figure isn't required.

■ Receptacle

Connector	L	M	N	P	Q	R
DF17#(3.0)-26DS-0.5V	11.5	-	24	3.3	25.5	330
DF17#(3.0)-30DS-0.5V	11.5	-	24	3.3	25.5	330
DF17#(3.0)-60DS-0.5V	14.2	28.4	32	3.3	33.5	330
DF17#(3.0)-70DS-0.5V	20.2	40.4	44	3.3	45.5	330
DF17#(3.0)-80DS-0.5V	20.2	40.4	44	3.3	45.5	330



Technical drawing of a metal plate with a central slot and a central component. The drawing includes dimensions for the plate and the component, and cross-sections X-X and Y-Y.

Dimensions:

- Top horizontal dimensions: 12 ± 0.1 , 2 ± 0.1 , 4 ± 0.1
- Right vertical dimensions: 1.75 ± 0.1 , $L \pm 0.1$, $M \pm 0.1$, $N \pm 0.3$
- Bottom horizontal dimensions: 0.2 ± 0.05 , 0.3 ± 0.1 , $P \pm 0.15$
- Left vertical dimensions: $R1.5$ (top), $R0.75$ (bottom)
- Left horizontal dimensions: $+0.1$ (top), $+0.15$ (bottom)
- Bottom horizontal dimensions: $+0.15$ (top), 0 (bottom)

Section X-X: A cross-section of the central component, showing a rectangular shape with a central slot. The dimensions are 1.75 ± 0.1 , $L \pm 0.1$, $M \pm 0.1$, and $N \pm 0.3$.


Section Y-Y: A cross-section of the metal plate, showing a rectangular shape with a central slot. The dimensions are 0.3 ± 0.1 and $P \pm 0.15$.

Unreeling direction: Indicated by an arrow pointing to the right.

Connector	L	M	N	P	Q	R
DF17(1.0H)-26DP-0.5V	11.5	-	24	3.6	25.5	330
DF17(1.0H)-30DP-0.5V	11.5	-	24	3.6	25.5	330
DF17(1.0H)-60DP-0.5V	14.2	28.4	32	3.6	33.5	330
DF17(1.0H)-70DP-0.5V	20.2	40.4	44	3.6	45.5	330
DF17(1.0H)-80DP-0.5V	20.2	40.4	44	3.6	45.5	330

DF17 Series 0.5mm Pitch Board to Board Connector

■ Precautions

1. Recommended Temperature Profile (SMT)	 Note1: Up to 2 cycles of Reflow soldering are possible under the same conditions, provided that there is a return to normal temperature between the first and second cycle. Note2: The temperature profile indicates the board surface temperature at the point of contacts with the connector terminals.
2. Recommended Manual Soldering Condition (SMT)	Soldering iron temperature: $350 \pm 3^\circ\text{C}$ Soldering time: Within 2 seconds
3. Recommended Screen Thickness (SMT)	0.15mm
4. Board Warp(SMT)	Max 0.02mm in the connector center area, based on the both connector edges
5. Cleaning Condition	Refer to the "Nylon Connector Use Hand book".
6. Cautions	■ The header is designed in a structure where contacts are exposed. Touching it with bare hands would cause contact failure or electrostatic element damage. ■ Where no board is mounted, the insertion or extraction will cause damage or contact deformation. ■ Avoid retaining the board with the connector only, and fix the board by any other means than the connector. ■ Excessive scoop insertion or extraction may result in damage. ■ In the manual soldering process, don't carry out the flux coating which will cause a flux blister on the connector. ■ The color phase of this product may be slightly different from that of the formed product according to the manufacturing lot. However, the difference doesn't affect the performance.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Hirose Electric:

[DF17A\(3.0\)-70DS-0.5V\(57\)](#) [DF17A\(3.0\)-100DS-0.5V\(57\)](#) [DF17B\(3.0\)-100DS-0.5V\(57\)](#) [DF17C\(3.0\)-20DS-0.5V\(57\)](#)
[DF17C\(3.0\)-30DS-0.5V\(57\)](#) [DF17C\(3.0\)-40DS-0.5V\(57\)](#) [DF17C\(3.0\)-50DS-0.5V\(57\)](#) [DF17C\(3.0\)-60DS-0.5V\(57\)](#)
[DF17C\(3.0\)-70DS-0.5V\(57\)](#) [DF17C\(3.0\)-100DS-0.5V\(57\)](#) [DF17C\(4.0\)-20DS-0.5V\(57\)](#) [DF17C\(4.0\)-30DS-0.5V\(57\)](#)
[DF17C\(4.0\)-40DS-0.5V\(57\)](#) [DF17C\(4.0\)-50DS-0.5V\(57\)](#) [DF17C\(4.0\)-60DS-0.5V\(57\)](#) [DF17C\(4.0\)-70DS-0.5V\(57\)](#)
[DF17A\(2.0\)-100DP-0.5V\(57\)](#) [DF17B\(2.0\)-100DP-0.5V\(57\)](#) [DF17C\(2.0\)-20DP-0.5V\(57\)](#) [DF17C\(2.0\)-30DP-0.5V\(57\)](#)
[DF17C\(2.0\)-50DP-0.5V\(57\)](#) [DF17C\(2.0\)-60DP-0.5V\(57\)](#) [DF17C\(2.0\)-100DP-0.5V\(57\)](#) [DF17\(4.0\)-40DP-0.5V\(67\)](#)
[DF17C\(4.0\)-20DP-0.5V\(57\)](#) [DF17C\(4.0\)-30DP-0.5V\(57\)](#) [DF17C\(4.0\)-50DP-0.5V\(57\)](#) [DF17C\(4.0\)-60DP-0.5V\(57\)](#)
[DF17C\(4.0\)-70DP-0.5V\(57\)](#) [DF17C\(4.0\)-80DP-0.5V\(57\)](#) [DF17A\(2.5\)-80DP-0.5V\(57\)](#) [DF17C\(2.5\)-80DP-0.5V\(57\)](#)
[DF17A\(3.0\)-26DS-0.5V\(57\)](#) [DF17C\(3.0\)-26DS-0.5V\(57\)](#) [DF17A\(2.5\)-26DP-0.5V\(57\)](#) [DF17C\(2.5\)-26DP-0.5V\(57\)](#)
[DF17D\(2.5\)-26DP-0.5V\(57\)](#) [DF17E\(2.5\)-26DP-0.5V\(57\)](#) [DF17F\(2.5\)-26DP-0.5V\(57\)](#) [DF17G\(2.5\)-26DP-0.5V\(57\)](#)
[DF17A\(3.0H\)-26DS-0.5V\(57\)](#) [DF17C\(3.0H\)-26DS-0.5V\(57\)](#) [DF17A\(1.0H\)-26DP-0.5V\(57\)](#) [DF17C\(1.0H\)-26DP-0.5V\(57\)](#)
[DF17D\(1.0H\)-26DP-0.5V\(57\)](#) [DF17F\(1.0H\)-26DP-0.5V\(57\)](#) [DF17J\(3.0\)-20DS-0.5V\(57\)](#) [DF17J\(4.0\)-20DP-0.5V\(57\)](#)
[DF17C\(3.0H\)-30DS-0.5V\(57\)](#) [DF17C\(1.0H\)-30DP-0.5V\(57\)](#) [DF17D\(2.0\)-100DP-0.5V\(57\)](#) [DF17F\(2.0\)-100DP-0.5V\(57\)](#)
[DF17D\(4.0\)-40DP-0.5V\(57\)](#) [DF17A\(3.0H\)-60DS-0.5V\(57\)](#) [DF17C\(3.0H\)-60DS-0.5V\(57\)](#) [DF17A\(1.0H\)-60DP-0.5V\(57\)](#)
[DF17C\(1.0H\)-60DP-0.5V\(57\)](#) [DF17A\(3.0H\)-80DS-0.5V\(57\)](#) [DF17C\(3.0H\)-80DS-0.5V\(57\)](#) [DF17A\(1.0H\)-80DP-](#)
[0.5V\(57\)](#) [DF17C\(1.0H\)-80DP-0.5V\(57\)](#) [DF17A\(3.0\)-120DS-0.5V\(57\)](#) [DF17B\(3.0\)-120DS-0.5V\(57\)](#) [DF17C\(3.0\)-120DS-](#)
[0.5V\(57\)](#) [DF17A\(2.0\)-120DP-0.5V\(57\)](#) [DF17B\(2.0\)-120DP-0.5V\(57\)](#) [DF17C\(2.0\)-120DP-0.5V\(57\)](#) [DF17D\(2.0\)-120DP-](#)
[0.5V\(57\)](#) [DF17E\(2.0\)-120DP-0.5V\(57\)](#) [DF17F\(2.0\)-120DP-0.5V\(57\)](#) [DF17G\(2.0\)-120DP-0.5V\(57\)](#) [DF17A\(3.0H\)-70DS-](#)
[0.5V\(57\)](#) [DF17C\(3.0H\)-70DS-0.5V\(57\)](#) [DF17A\(1.0H\)-70DP-0.5V\(57\)](#) [DF17C\(1.0H\)-70DP-0.5V\(57\)](#) [DF17F\(1.0H\)-](#)
[60DP-0.5V\(57\)](#) [DF17A\(2.0\)-50DP-0.5V\(51\)](#) [DF17A\(2.0\)-60DP-0.5V\(51\)](#) [DF17A\(2.0\)-70DP-0.5V\(51\)](#) [DF17A\(2.0\)-](#)
[80DP-0.5V\(51\)](#) [DF17A\(4.0\)-20DP-0.5V\(51\)](#) [DF17A\(4.0\)-40DP-0.5V\(51\)](#) [DF17A\(4.0\)-40DS-0.5V\(51\)](#) [DF17A\(4.0\)-](#)
[50DP-0.5V\(51\)](#) [DF17A\(4.0\)-60DP-0.5V\(51\)](#) [DF17A\(4.0\)-70DP-0.5V\(51\)](#) [DF17A\(4.0\)-70DS-0.5V\(51\)](#) [DF17A\(3.0\)-](#)
[30DS-0.5V\(51\)](#) [DF17A\(3.0\)-60DS-0.5V\(51\)](#)