


YG901C2 (5A)

LOW LOSS SUPER HIGH SPEED RECTIFIER

■ Outline Drawing




■ Features

- Insulated package by fully overmolding
- Low V_F
- Super high speed switching
- High reliability by planer design

■ Applications

- High speed power switching

■ Connection Diagram



■ Maximum Ratings & Characteristics

• Absolute Maximum Ratings

Items	Symbols	Conditions	Ratings	Units
Repetitive Peak Reverse Voltage	V_{RRM}		200	V
Average Output Current	I_o	$T_C = 120^\circ\text{C}$, Sq. Wave, duty = 1/2	5*	A
Surge Current	I_{FSM}	Sine Wave, 10ms	25	A
Operating Junction Temperature	T_J		-40 to +150	$^\circ\text{C}$
Storage Temperature	T_{stg}		-40 to +150	$^\circ\text{C}$

*Average forward current of centertap full wave connection

• Electrical Characteristics ($T_a = 25^\circ\text{C}$ Unless otherwise specified)

Items	Symbols	Conditions	Ratings	Units
Forward Voltage Drop	V_F	$I_F = 2.5\text{A}$	0.95	V
Reverse Current	I_R	$V_R = V_{RRM}$	100	μA
Reverse Recovery Time	t_r	$I_F = 0.1\text{A}$, $I_R = 0.2\text{A}$, $I_{rec} = 0.05\text{A}$	35	ns
Thermal Resistance	$R_{th(j-c)}$	Junction to case	5.0	$^\circ\text{C/W}$

Collmer Semiconductor, Inc.
Phone: (214) 233-1589 - Fax: (214) 233-0481

■ 2238792 0003864 196 ■

YG901C2 (5A)

