


Precision Thin Film Chip Resistor Array Superior Moisture Resistivity



ACAS 0606 AT and ACAS 0612 AT precision automotive grade thin film chip resistor arrays with convex terminations combine the proven reliability of discrete chip resistors with the advantages of chip resistor arrays. Defined relative tolerance (matching) and relative TCR (tracking) make this product perfectly suited for applications with outstanding requirements towards stable fixed resistor ratios. The ACAS AT is available with equal or different resistor values. Find out more about Vishay's automotive grade product requirements at: www.vishay.com/applications

FEATURES

- Superior moisture resistivity, $|\Delta R/R| < 0.5\% (85^\circ\text{C}; 85\% \text{RH}; 1000 \text{h})$
- Rated dissipation P_{70} up to 125 mW per resistor
- ESD stability 1000 V, human body model
- Relative TCR down to $\pm 5 \text{ ppm/K}$ (tracking)
- Relative tolerance down to $\pm 0.05\%$ (matching)
- AEC-Q200 qualified
- Material categorization: For definitions of compliance please see www.vishay.com/doc?99912



APPLICATIONS

- Precision analogue circuits
- Voltage divider
- Feedback circuits
- Signal conditioning

TECHNICAL SPECIFICATIONS		
DESCRIPTION	ACAS 0606 AT	ACAS 0612 AT
EIA size	0606	0612
Metric size	RR1616M	RR1632M
Configuration, isolated	2 x 0603	4 x 0603
Design:		
All equal values (AE)	AE	AE
Two pairs of values (TP)		TP
Different values (DF)	DF	
Resistance values	47 Ω to 150 k Ω ⁽¹⁾	
Absolute tolerance	$\pm 0.1\%$	
Relative tolerance	$\pm 0.05\%$	
Absolute temperature coefficient	$\pm 25 \text{ ppm/K}; \pm 15 \text{ ppm/K}; \pm 10 \text{ ppm/K}$	
Relative temperature coefficient	$\pm 15 \text{ ppm/K}; \pm 10 \text{ ppm/K}; \pm 5 \text{ ppm/K}$	
Max. resistance ratio $R_{\min.}/R_{\max.}$	1:20	
Rated dissipation: P_{70}		
Element	0.125 W	0.125 W
Package	0.2 W	0.4 W
Operating voltage, $U_{\max.}$ AC/DC	75 V	
Operating temperature range	- 55 $^\circ\text{C}$ to 155 $^\circ\text{C}$	
Permissible film temperature	155 $^\circ\text{C}$	
Insulation voltage (U_{ins}) against ambient and between integrated resistors, continuous	75 V	

Notes

- The relative figures of tolerance, TCR and drift are related to a medial axis between the maximum and minimum permissible deviation of the resistor array. For detailed information please refer to the application note: Increasing Accuracy in Feedback Circuits and Voltage Dividers with Thin Film Chip Resistor Arrays (www.vishay.com/doc?28194)

⁽¹⁾ Resistance values to be selected from E24; E192.

APPLICATION INFORMATION



The power dissipation on the resistor generates a temperature rise against the local ambient, depending on the heat flow support of the printed-circuit board (thermal resistance). The rated dissipation applies only if the permitted film temperature is not exceeded. These resistors do not feature a limited lifetime when operated within the permissible limits.

MAXIMUM RESISTANCE CHANGE AT RATED POWER (1)				
DESCRIPTION	ACAS 0606 AT		ACAS 0612 AT	
Configuration, isolated	2 x 0603		4 x 0603	
Operation mode	Standard	Power	Standard	Power
Rated power per element, P_{70}	0.1 W	0.125 W	0.1 W	0.125 W
Rated power per package, P_{70}	0.15 W	0.2 W	0.3 W	0.4 W
Film temperature	125 °C	155 °C	125 °C	155 °C
Max. resistance change at P_{70}				
$\Delta R/R$ max., after:				
1000 h	± 0.1 %	± 0.25 %	± 0.1 %	± 0.25 %
8000 h	± 0.25 %	± 0.5 %	± 0.25 %	± 0.5 %
Max. relative resistance change (relative drift) at P_{70}				
$\Delta R/R$ max., after:				
1000 h	± 0.05 %	± 0.125 %	± 0.05 %	± 0.125 %
8000 h	± 0.125 %	± 0.25 %	± 0.125 %	± 0.25 %

Note

(1) Figures are given for arrays with equal values, design type AE.

CIRCUITS



Marking on ACAS 0606 AT: For types with different resistor values pin 1 is marked.

DESIGN		
	ACAS 0606 AT	ACAS 0612 AT
AE	$R_1 = R_2$	$R_1 = R_2 = R_3 = R_4$
TP		$R_1 = R_4 < R_2 = R_3$
DF	$R_1 < R_2$	

PART NUMBER AND PRODUCT DESCRIPTION
Part Number: ACASA1100S2200P5AT

A	C	A	S	A	1	1	0	0	S	2	2	0	0	P	5	A	T
MODEL/ SIZE	TERMINAL	SIZE		RESISTANCE ⁽¹⁾	ACCURACY GRADE ⁽²⁾		RESISTANCE ⁽¹⁾		PACKAGING					PACKAGING		Special	
ACA	S = Convex square	N = 0606 A = 0612		3 digit resistance value R_1, R_4 1 digit multiplier MULTIPLIER 9 = $*10^{-1}$ 0 = $*10^0$ 1 = $*10^1$ 2 = $*10^2$ 3 = $*10^3$	TCR, Tracking, Tolerance and Matching S, T, or U		3 digit resistance value R_2, R_3 1 digit multiplier MULTIPLIER 9 = $*10^{-1}$ 0 = $*10^0$ 1 = $*10^1$ 2 = $*10^2$ 3 = $*10^3$		P1 P5				AT = Automotive				

Product Description: ACAS 0612 110R S 220R AT P5

ACA	S	0612	110R	S	220R	AT	P5
MODEL/ SIZE	TERMINAL	SIZE	RESISTANCE R_1, R_4 ⁽¹⁾	ACCURACY GRADE ⁽²⁾	RESISTANCE R_2, R_3 ⁽¹⁾	SPECIAL	PACKAGING
ACA = Chip Array	S = Convex square	0606 0612	110R = 110 Ω 1K1 = 1.1 k Ω 22K1 = 22.1 k Ω	TCR, Tracking, Tolerance and Matching S, T, or U	220R = 220 Ω 1K1 = 1.1 k Ω 22K1 = 22.1 k Ω	AT = Automotive	P1 P5

Notes

- Products can be ordered using either the PART NUMBER or the PRODUCT DESCRIPTION.
- ⁽¹⁾ $R_1 = R_4 \leq R_2 = R_3$.
- ⁽²⁾ For historical temperature coefficient and resistance ranges please refer to the end of the data sheet.



TEMPERATURE COEFFICIENT AND RESISTANCE RANGE

TYPE	ACCURACY GRADE	ABSOLUTE		RELATIVE		RESISTANCE VALUE
		TCR	TOLERANCE	TCR	TOLERANCE	
ACAS 0606 AT ACAS 0612 AT	S	± 25 ppm/K	± 0.1 %	± 15 ppm/K	± 0.05 %	47 Ω to 150 k Ω
	T	± 15 ppm/K	± 0.1 %	± 10 ppm/K	± 0.05 %	47 Ω to 150 k Ω
	U	± 10 ppm/K	± 0.1 %	± 5 ppm/K	± 0.05 %	47 Ω to 100 k Ω


Notes

- For historical temperature coefficient and resistance range please refer to the end of the data sheet.
- Relative TCR (tracking) down to ± 2.5 ppm/K on request.
- Relative tolerance for resistance values $< 80 \Omega$ on request.

PACKAGING						
TYPE	CODE	QUANTITY	PACKAGING STYLE	WIDTH	PITCH	REEL DIAMETER
ACAS 0606 AT ACAS 0612 AT	P1	1000	Tape and reel cardboard tape acc. IEC 60286-3 Type I	8 mm	4 mm	180 mm/7"
	P5	5000				

DIMENSIONS
ACAS 0606 AT

ACAS 0612 AT


DIMENSION AND MASS									
TYPE	L (mm)	W (mm)	H (mm)	P (mm)	A₁ (mm)	A (mm)	T₁ (mm)	T₂ (mm)	MASS (mg)
ACAS 0606 AT	1.5 ± 0.15	1.6 ± 0.15	0.45 ± 0.1	-	0.6 ± 0.1	0.4 ± 0.1	0.3 ± 0.15	0.4 ± 0.15	3.6
ACAS 0612 AT	1.5 ± 0.15	3.2 ± 0.15	0.45 ± 0.1	0.8 ± 0.1	0.6 ± 0.1	0.4 ± 0.1	0.3 ± 0.15	0.4 ± 0.15	6.8

PATTERN STYLES FOR CHIP RESISTOR ARRAYS


RECOMMENDED SOLDER PAD DIMENSIONS							
TYPE	G (mm)	Y (mm)	X (mm)	U (mm)	Z (mm)	I (mm)	P (mm)
ACAS 0606 AT	0.7	0.7	0.64	-	2.1	0.3	0.8
ACAS 0612 AT	0.7	0.7	0.64	0.5	2.1	0.3	0.8

DESCRIPTION

The production of the components is strictly controlled and follows an extensive set of instructions established for reproducibility. A homogeneous film of metal alloy is deposited on a high grade (Al_2O_3) ceramic substrate using a mask to separate the adjacent resistors and conditioned to achieve the desired temperature coefficient. Specially designed inner contacts are realized on both sides. A special laser is used to achieve the target value by smoothly cutting a meander groove in the resistive layer without damaging the ceramics.

The resistor elements are covered by a protective coating designed for electrical, mechanical and climatic protection. The terminations receive a final pure tin on nickel plating.

The result of the determined production is verified by an extensive testing procedure and optical inspection performed on 100 % of the individual chip resistors. Only accepted products are laid directly into the paper tape in accordance with **IEC 60286-3** ⁽³⁾.

ASSEMBLY

The resistors are suitable for processing on automatic SMD assembly systems. They are suitable for automatic soldering using reflow or vapour phase as shown in **IEC 61760-1** ⁽³⁾. The encapsulation is resistant to all cleaning solvents commonly used in the electronics industry, including alcohols, esters and aqueous solutions.


Notes

⁽¹⁾ Global Automotive Declarable Substance List, see www.gadsl.org.

⁽²⁾ CEFIC (European Chemical Industry Council), EECA (European Electronic Component Manufacturers Association), EICTA (European trade organisation representing the information and communications technology and consumer electronics), see www.eicta.org → policy → environmental policy group → chemicals → jig → Joint Industry Guide (JIG-101 Ed 2.0).

⁽³⁾ The quoted IEC standards are also released as EN standards with the same number and identical contents.

FUNCTIONAL PERFORMANCE



For permissible resistance change please refer to table MAXIMUM RESISTANCE CHANGE AT RATED POWER, above

Derating

TESTS AND REQUIREMENTS

Essentially all tests are carried out in accordance with the following specifications:

EN 60115-1, generic specification

EN 140400, sectional specification

EN 140401-801, detail specification

The testing also covers most of the requirements specified by EIA/IS-703 and JIS-C-5202.

The tests are carried out under standard atmospheric conditions according to **IEC 60068-1** ⁽¹⁾, 5.3. Climatic category LCT/UCT/56 (rated temperature range:

Lower category temperature, upper category temperature; damp heat, long term, 56 days) is valid (LCT = - 55 °C/ UCT = 125 °C).

Unless otherwise specified the following values apply:

Temperature: 15 °C to 35 °C

Relative humidity: 45 % to 75 %

Air pressure: 86 kPa to 106 kPa (860 mbar to 1060 mbar)

The requirements stated in the "Test Procedures and Requirements" table are based on the required tests and permitted limits of EN 140401-801 where applicable.

TEST PROCEDURES AND REQUIREMENTS				
EN 60115-1 CLAUSE	IEC 60068-2 ⁽¹⁾ TEST METHOD	TEST	PROCEDURE	REQUIREMENTS PERMISSIBLE CHANGE ⁽²⁾ (ΔR)
			Stability for product types: ACAS 0606 AT ACAS 0612 AT	47 Ω to 150 kΩ 47 Ω to 150 kΩ
4.5	-	Resistance	-	± 0.1 %
4.8.4.2	-	Temperature coefficient	At (20/- 55/ 20) °C and (20/125/20) °C	± 25 ppm/K; ± 15 ppm/K; ± 10 ppm/K
4.25.1	-	Endurance at 70 °C: Standard operation mode	$U = \sqrt{P_{70} \times R}$ or $U = U_{\max.}$; 1.5 h on; 0.5 h off; whichever is the less severe; 1000 h: Absolute Relative 8000 h: Absolute Relative	± (0.1 % $R + 0.05 \Omega$) ± (0.05 % $R + 0.05 \Omega$) ± (0.25 % $R + 0.05 \Omega$) ± (0.125 % $R + 0.05 \Omega$)
		Endurance at 70 °C: Power operation mode	$U = \sqrt{P_{70} \times R}$ or $U = U_{\max.}$; 1.5 h on; 0.5 h off; whichever is the less severe; 1000 h: Absolute Relative 8000 h: Absolute Relative	± (0.25 % $R + 0.05 \Omega$) ± (0.125 % $R + 0.05 \Omega$) ± (0.5 % $R + 0.05 \Omega$) ± (0.25 % $R + 0.05 \Omega$)
4.25.3	-	Endurance at upper category temperature	125 °C; 1000 h: Absolute Relative 125 °C; 8000 h: Absolute Relative 155 °C; 1000 h: Absolute Relative	± (0.25 % $R + 0.05 \Omega$) ± (0.125 % $R + 0.05 \Omega$) ± (0.5 % $R + 0.05 \Omega$) ± (0.25 % $R + 0.05 \Omega$) ± (0.4 % $R + 0.05 \Omega$) ± (0.2 % $R + 0.05 \Omega$)
4.24	78 (Cab)	Damp heat, steady state	(40 ± 2) °C; 56 days; (93 ± 3) % RH	± (0.25 % $R + 0.05 \Omega$)
4.39	67 (Cy)	Damp heat, steady state, accelerated	$(85 \pm 2) ^\circ C$ $(85 \pm 5) \% RH$ $U = \sqrt{0.1 \times P_{70} \times R}$ $U \leq 0.3 \times U_{\max.}$ 1000 h	± (0.5 % $R + 0.05 \Omega$)

TEST PROCEDURES AND REQUIREMENTS				
EN 60115-1 CLAUSE	IEC 60068-2 (1) TEST METHOD	TEST	PROCEDURE	REQUIREMENTS PERMISSIBLE CHANGE (2) (ΔR)
			Stability for product types:	47 Ω to 150 k Ω 47 Ω to 150 k Ω
			ACAS 0606 AT ACAS 0612 AT	
4.13	-	Short time overload (3) Standard operation mode	$U = 2.5 \times \sqrt{P_{70} \times R}$ or $U = 2 \times U_{\max.}$ 5 s	$\pm (0.1 \% R + 0.01 \Omega)$ no visible damage
4.40	-	Electrostatic discharge (human body model) (3)	IEC 61340-3-1; 3 pos. + 3 neg. (equivalent to MIL-STD-883, Method 3015); 1000 V	$\pm (0.5 \% R + 0.05 \Omega)$
4.19	14 (Na)	Rapid change of temperature	30 min at - 55 °C and 30 min at 125 °C; 1000 cycles	$\pm (0.25 \% R + 0.05 \Omega)$ no visible damage
4.18.2	58 (Td)	Resistance to soldering heat	Reflow method 2 (IR/forced gas convection); (260 \pm 5) °C; (10 \pm 1) s	$\pm (0.1 \% R + 0.01 \Omega)$ no visible damage
4.17.2	58 (Td)	Solderability	Solder bath method; SnPb; non-activated flux accelerated aging 4 h/155 °C (215 \pm 3) °C; (3 \pm 0.3) s	Good tinning (\geq 95 % covered); no visible damage
			Solder bath method; SnAgCu; non-activated flux accelerated aging 4 h/155 °C (235 \pm 3) °C; (2 \pm 0.2) s	
4.32	21 (Ue ₃)	Shear (adhesion)	45 N	No visible damage
4.33	21 (Ue ₁)	Substrate bending	Depth 2 mm, 3 times	$\pm (0.1 \% R + 0.01 \Omega)$ no visible damage; no open circuit in bent position
4.35	-	Flammability	IEC 60695-11-5, needle flame test; 10 s	No burning after 30 s
4.22	6 (Fc)	Vibration	Endurance by sweeping; 10 Hz to 2000 Hz; no resonance; amplitude \leq 1.5 mm or \leq 200 m/s ² ; 7.5 h	$\pm (0.1 \% R + 0.01 \Omega)$ no visible damage
4.7	-	Voltage proof	$U_{\text{RMS}} = U_{\text{ins}}$ 60 s \pm 5 s; against ambient, between adjacent resistors	No flashover or breakdown

Notes

(1) The quoted IEC standards are also released as EN standards with the same number and identical contents.

(2) Figures are given for arrays with equal values, design type AE.

(3) For a single element.

HISTORICAL TEMPERATURE COEFFICIENT AND RESISTANCE RANGES					
DESCRIPTION					RESISTANCE VALUE
ACCURACY GRADE	ABSOLUTE TCR	TCR TRACKING	ABSOLUTE TOLERANCE	TOLERANCE MATCHING	ACAS 0606 AT ACAS 0612 AT
A	± 25 ppm/K	10 ppm/K	$\pm 0.25 \%$	0.1 %	47 Ω to 150 k Ω
B	± 25 ppm/K	10 ppm/K	$\pm 0.5 \%$	0.25 %	47 Ω to 150 k Ω
E	± 25 ppm/K	15 ppm/K	$\pm 0.25 \%$	0.1 %	47 Ω to 150 k Ω
F	± 25 ppm/K	15 ppm/K	$\pm 0.5 \%$	0.25 %	47 Ω to 150 k Ω
J	± 25 ppm/K	25 ppm/K	$\pm 0.25 \%$	0.1 %	47 Ω to 150 k Ω
K	± 25 ppm/K	25 ppm/K	$\pm 0.5 \%$	0.25 %	47 Ω to 150 k Ω
N	± 50 ppm/K	25 ppm/K	$\pm 0.5 \%$	0.5 %	47 Ω to 150 k Ω
P	± 50 ppm/K	50 ppm/K	$\pm 0.5 \%$	0.5 %	47 Ω to 150 k Ω

Note

- Special temperature coefficient and resistance combinations remain available. For optimized availability please refer to the table TEMPERATURE COEFFICIENT AND RESISTANCE.

Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and/or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

Material Category Policy

Vishay Intertechnology, Inc. hereby certifies that all its products that are identified as RoHS-Compliant fulfill the definitions and restrictions defined under Directive 2011/65/EU of The European Parliament and of the Council of June 8, 2011 on the restriction of the use of certain hazardous substances in electrical and electronic equipment (EEE) - recast, unless otherwise specified as non-compliant.

Please note that some Vishay documentation may still make reference to RoHS Directive 2002/95/EC. We confirm that all the products identified as being compliant to Directive 2002/95/EC conform to Directive 2011/65/EU.

Vishay Intertechnology, Inc. hereby certifies that all its products that are identified as Halogen-Free follow Halogen-Free requirements as per JEDEC JS709A standards. Please note that some Vishay documentation may still make reference to the IEC 61249-2-21 definition. We confirm that all the products identified as being compliant to IEC 61249-2-21 conform to JEDEC JS709A standards.