




MARKETING SALES DRAWING
DIMENSIONS IN INCHES - DO NOT SCALE THIS DRAWING
DIMENSIONS IN METRIC - []

Electrical Testing
per Tusonix standard
test plans and Mil-Std-202
Test Methods.



SPECIFICATIONS

TUSONIX PART NO.		848-040-X5U0-103 M
D (Diameter):		.660 +.030, -.050 [16.76 +0.76,-1.27]
T (Thickness):		.120 ± .040 [3.05 ±1.02]
S (Lead Wire Spacing):		.375 ±.060 [9.52 ±1.52]
L (Lead Wire Length):		1.25 [31.75] MIN.
E (Lead Wire Diameter):		.032 [0.81] (20 AWG.)
P (Coating on Leads Max.):		.125 [3.18]
Capacitance Value:		10,000 pF
Capacitance Tolerance:		± 20%
Temperature Coefficient:		X5U
Voltage:	Working:	1000 VDC
	Test:	2500 VDC
	Life:	2000 VDC

NOTE:
MIL - P/N CK63AY103M
(MIL-C-11015/12)

Marking: TMK, MIL PART NO., DATE CODE.

REVISION RECORD		Original Release C.O. 19990813-3-01 ADDED METRIC, PROJECTION & CIRCUIT. CORRECTED VOLTAGE. S.M. 08-02-01 20010802-1-01	1				
0				--TOLERANCES-- Unless Otherwise Specified		Title DISC	
DECIMAL ± 				Drawn S.M. 08-13-99			
ANGLES ± 				Approved E.F. 08-13-99			
TUSONIX TUCSON, ARIZONA				A	848-040-X5U0-103M		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Tusonix:

[0848-040-X5U0-103M](#)