



| LOC<br>J | DIST<br>— | REVISIONS |     |                           |         |     |      |
|----------|-----------|-----------|-----|---------------------------|---------|-----|------|
|          |           | P         | LTR | DESCRIPTION               | DATE    | DWN | APVD |
|          |           |           | E   | REVISED PER ECR—11—008941 | 28JUL11 | T.T | T.M  |


リール引出し方向  
DIRECTION OFF TOP OF REEL




VIEW W  
テープ幅 32mm以上に適用  
APPLIED TAPE WIDTH 32MM,MORE.



VIEW W  
テープ幅 12mm, 16mm, 24mm に適用  
APPLIED TAPE WIDTH 12MM, 16MM AND 24MM.



DETAIL X



- ① GENERAL TOLERANCE

10 $\geq$ :  $\pm 0.2$   
30 $\geq$  > 10:  $\pm 0.25$   
100 $\geq$  > 30:  $\pm 0.3$   
ANGLES:  $\pm 3^\circ$

② DIM. B AND DETAIL "X" APPLIED  
TAPE WIDE, 32mm MORE.
- ① 一般公差

10以下:  $\pm 0.2$   
10を越え 30以下:  $\pm 0.25$   
30を越え 100以下:  $\pm 0.3$   
角 度:  $\pm 3^\circ$

② B寸法及び "X" 詳細図は、  
テープ幅 32mm以上に適用

|          |           |                  |      |      |       |    |   |      |                    |         |                                      |
|----------|-----------|------------------|------|------|-------|----|---|------|--------------------|---------|--------------------------------------|
| OBSOLETE | AVAILABLE | 0.102g           | 30.4 | 24.4 | 17.35 | 24 | — | 11.5 | 4000               | 51      | 2-2013496-1                          |
|          | AVAILABLE | 0.090g           | 30.4 | 24.4 | 15.55 | 24 | — | 11.5 | 4000               | 45      | 1-2013496-8                          |
|          | AVAILABLE | 0.083g           | 30.4 | 24.4 | 14.35 | 24 | — | 11.5 | 4000               | 41      | 1-2013496-6                          |
|          | AVAILABLE | 0.080g           | 30.4 | 24.4 | 13.75 | 24 | — | 11.5 | 4000               | 39      | 1-2013496-5                          |
|          | AVAILABLE | 0.066g           | 30.4 | 24.4 | 11.35 | 24 | — | 11.5 | 4000               | 31      | 1-2013496-1                          |
|          | AVAILABLE | 0.062g           | 30.4 | 24.4 | 10.75 | 24 | — | 11.5 | 4000               | 29      | 1-2013496-0                          |
|          | AVAILABLE | 0.059g           | 30.4 | 24.4 | 10.15 | 24 | — | 11.5 | 4000               | 27      | 2013496-9                            |
| OBSOLETE | AVAILABLE | 0.048g           | 22.4 | 16.4 | 8.35  | 16 | — | 7.5  | 4000               | 21      | 2013496-6                            |
|          | STATUS    | CONNECTOR WEIGHT | F    | E    | D     | C  | B | A    | 数量 (ヶ)<br>QTY/REEL | POS.(N) | EMBOSS TAPE PACKAGING<br>PART NUMBER |

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:  
mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

|        |               |
|--------|---------------|
| 0 PLC  | $\pm 0.3$     |
| 1 PLC  | $\pm 0.3$     |
| 2 PLC  | $\pm 0.3$     |
| 3 PLC  | $\pm 0.3$     |
| 4 PLC  | $\pm 0.3$     |
| ANGLES | $\pm 3^\circ$ |

MATERIAL

SEE NOTE 3

FINISH

SEE NOTE 4

DWN  
Y.KODAIRA  
29NOV2007

CHK  
T.KUSUHARA  
29NOV2007

APVD  
T.KUSUHARA  
29NOV2007

PRODUCT SPEC  
108-78351

APPLICATION SPEC  
411-78302

WEIGHT  
SEE TABLE

CUSTOMER DRAWING

TE Connectivity

NAME  
0.3FPC Narrow BF-L-1.2H  
1.2mmH, 2.9mmW, GOLD PLATE

SIZE  
A3

CAGE CODE  
00779

DRAWING NO  
C=2013496

RESTRICTED TO  
—

SCALE  
10:1

SHEET  
1 OF 2

REV  
E

