

CTE8000 / CTU8000 Series

OEM pressure transmitters for industrial media

FEATURES

- 250 mbar to 100 bar, 5 to 1500 psi gage¹ or absolute¹⁰ pressure
- 0...10 V, 0.5...4.5 V, 0...5 V, 1...6 V or 4...20 mA output
- Field interchangeable
- For many industrial gases and liquids
- EMC according to EN 61326-1⁸

MEDIA COMPATIBILITY

Wetted materials:

Stainless steel 1.4404 (316L)⁹, ceramic Al_2O_3 , NBR (FKM)

Housing:

Stainless steel 1.4404 (316L), protection class IP 67 (according to DIN EN 60529) respectively NEMA 6¹



SPECIFICATIONS^{11,12}

Maximum ratings

Supply voltage (reverse polarity protection)

CTE(M)/CTU8...0	12...32 V
CTE(M)/CTU8...1	9...32 V
CTE(M)/CTU8...6, ...7	8...32 V
CTE(M)/CTU8...4 ²	7...32 V

Maximum load current (source)

CTE(M)/CTU8...0, ...1, ...6, ...7	1 mA
-----------------------------------	------

Proof pressure³ 2 x rated pressure

Environmental

Temperature limits


Storage	-40...85 °C
Operating (media)	-25...85 °C
Electronic (ambient)	-25...85 °C
Compensated	0...70 °C

Vibration (5 to 500 Hz) 10 g_{RMS}


Mechanical shock 50 g

ELECTRICAL CONNECTION

Voltage output device



Current output device



CTE8000 / CTU8000 Series

OEM pressure transmitters for industrial media

COMMON PERFORMANCE CHARACTERISTICS

($V_S=15\text{ V} \pm 0.1\text{ V}$, $T_A=25\text{ °C}$, RH=50 %)

Characteristics			Min.	Typ.	Max.	Unit
Thermal effects (0...70 °C) ⁴	Offset	devices up to 1 bar/15 psi		±0.03	±0.06	%FSO/°C
		all others		±0.02	±0.04	
	Span			±0.02	±0.04	
Thermal effects (-25...0 °C, 70...85 °C) ⁴	Offset			±0.03		%FSO/°C
	Span			±0.03		
Non-linearity (BSL), hysteresis and repeatability ⁵	CT...8N...			±0.2	±0.5	%FSO
	all others			±0.1	±0.3	
Long term stability ⁶				±0.1	±0.3	
Output noise (0< f <1 kHz)				±0.1		
Response time (10 to 90 %)	devices up to 350 mbar/5 psi			35		ms
	all others			5		
D/A resolution					11	bit
Power supply rejection	Offset			±0.01		%FSO/V
	Span			±0.02		

INDIVIDUAL PERFORMANCE CHARACTERISTICS

($V_S=15\text{ V} \pm 0.1\text{ V}$, $T_A=25\text{ °C}$, RH=50 %)

0...10 V output ($R_L > 100\text{ k}\Omega$)

Characteristics		Min.	Typ.	Max.	Unit
Zero pressure offset	CT...8N...		5		V
	all others		0	0.1	
Full scale span ⁷		9.9	10	10.1	
Output impedance				25	Ω
Current consumption (no load)			4		mA

0.5...4.5 V output ($R_L > 100\text{ k}\Omega$)

Characteristics		Min.	Typ.	Max.	Unit
Zero pressure offset	CT...8N...		2.5		V
	all others	0.45	0.5	0.55	
Full scale span ⁷		3.95	4	4.05	
Output impedance				25	Ω
Current consumption (no load)			4		mA

CTE8000 / CTU8000 Series

OEM pressure transmitters for industrial media

INDIVIDUAL PERFORMANCE CHARACTERISTICS (cont.)

($T_A = 25\text{ °C}$, $RH = 50\%$, $V_S = 15\text{ V} \pm 0.1\text{ V}$)

0...5 V output ($R_L > 100\text{ k}\Omega$)

Characteristics		Min.	Typ.	Max.	Unit
Zero pressure offset	CT...8N...		2.50		V
	all others		0	0.05	
Full scale span ⁷		4.95	5.00	5.05	
Output impedance				25	W
Current consumption (no load)			4		mA

1...6 V output ($R_L > 100\text{ k}\Omega$)


Characteristics		Min.	Typ.	Max.	Unit
Zero pressure offset	CT...8N...		3.50		V
	all others	0.95	1.00	1.05	
Full scale span ⁷		4.95	5.00	5.05	
Output impedance				25	Ω
Current consumption (no load)			4		mA

4...20 mA output ($R_L = 100\text{ }\Omega$)

Characteristics		Min.	Typ.	Max.	Unit
Zero pressure offset	CT...8N...		12.0		mA
	all others	3.9	4.0	4.1	
Full scale span ⁷		15.9	16.0	16.1	
Power consumption ($I_L = 20\text{ mA}$)			250		mW

LOAD LIMITATION


4...20 mA output version



CTE8000 / CTU8000 Series

OEM pressure transmitters for industrial media

OUTLINE DRAWING



mass: approx. 70 g


Note: O-ring included in delivery

dimensions in mm (inches)

RECOMMENDED ACCESSORY (not included in delivery)

ZP000112-B: Mating Connector (without cable)

ZK000101-x: Connector/cable assembly (x=cable lengths in m, max. 10 m)



PIN CONNECTION	
Pin	Flying lead end
1	Brown
2	Green
3	White and shield
4	Yellow


dimensions in mm

CTE8000 / CTU8000 Series


OEM pressure transmitters for industrial media

OPTIONAL PRESSURE FITTINGS (brass, nickel plated)

Male fittings



Female fittings



Dimensions in mm (inches)			
A	B	C	D (Hex.)
1/8" BSPT	8 (0.315)	13 (0.512)	14 (9/16")
1/4" BSPT	12 (0.472)	5.5 (0.217)	14 (9/16")
3/8" BSPT	11.5 (0.453)	5 (0.197)	17 (11/16")
1/2" BSPT	16 (0.630)	7 (0.276)	22 (7/8")
1/8" BSP	12.5 (0.492)	11 (0.433)	14 (9/16")
1/4" BSP	8.5 (0.335)	5 (0.197)	19 (3/4")
3/8" BSP	12.5 (0.492)	7 (0.276)	22 (7/8")
1/8" NPT	10 (0.394)	13 (0.512)	17 (11/16")
1/4" NPT	14 (0.551)	6 (0.236)	22 (7/8")

Dimensions in mm (inches)			
E	F	G	H (Hex.)
1/8" BSP	5 (0.197)	15 (0.591)	14 (9/16")
1/4" BSP	7 (0.276)	20 (0.787)	17 (11/16")
3/8" BSP	6 (0.236)	20 (0.787)	22 (7/8")
1/2" BSP	18 (0.707)	23 (0.906)	24 (15/16")

Specification notes:

1. IP 67 protection is given when the connector is locked. For proper function the gage port is vented to the atmosphere through the connector/cable assembly. Thus the cable end must have access to the ambient pressure.
2. The minimum supply voltage is directly proportional to the load resistance seen by the transmitter. For more details see the load limitation diagram.
3. Proof pressure is the maximum pressure which may be applied without causing damage to the sensing element.
4. Thermal effects are relative to 25 °C. Signal is clamped at 0 V.
5. Non-linearity refers to **Best Straight Line** fit. Hysteresis is the maximum output difference at any point within the operating pressure range for increasing and decreasing pressure.
6. Long term stability is the change in output after one year.
7. Span is the arithmetic difference in transmitter output signal measured at zero pressure and the maximum operating pressure.
8. Surge immunity according to EN 61000-4-5 on request for current output devices.
9. When using devices with optional nickel plated fittings, consider the media compatibility of the fittings also.
10. Available for pressure ranges from 1 bar (15 psi) absolute upwards only.
11. CE-labelling is in accordance with 2004/108/EC.
12. The pressure transmitters must not be used as safety accessories according to article 1, 2.1.3 of the directive 97/23/EC.

CTE8000 / CTU8000 Series

OEM pressure transmitters for industrial media

ORDERING INFORMATION

		CTx	(M)	8xxx	x	x	x	x		
Calibration										Sealing material
E: bar calibration										V: Viton (FKM)
U: psi calibration										N: NBR
For mbar ranges only										Note: Older part no. do not contain this digit. Without this digit NBR will be used.
Pressure range										Output signal
<u>CTE8000 series</u>										0: 0...10 V
250: 0...250 mbar										1: 1...6 V
350: 0...350 mbar										4: 4...20 mA
500: 0...500 mbar										6: 0.5...4.5 V
001: 0...1 bar										7: 0...5 V
N01: -1...+1 bar										
P01: 0...-1 bar										Pressure connection
002: 0...2 bar										<u>Standard thread</u>
005: 0...5 bar										Y: G 1/8" (BSP) male, SS 1.4404 (316L)
010: 0...10 bar										<u>Optional pressure fittings</u>
016: 0...16 bar										D: 1/8" BSPT male, brass, nickel plated
020: 0...20 bar										E: 1/4" BSPT male, brass, nickel plated
025: 0...25 bar										F: 3/8" BSPT male, brass, nickel plated
035: 0...35 bar										G: 1/2" BSPT male, brass, nickel plated
050: 0...50 bar										K: 1/8" NPT male, brass
070: 0...70 bar										L: 1/4" NPT male, brass
100: 0...100 bar										M: 1/8" NPT male, SS 1.4305 (303)
										N: 1/4" NPT male, SS 1.4305 (303)
										P: G 1/8" (BSP) male, brass, nickel plated
										Q: G 1/4" (BSP) male, brass, nickel plated
										R: G 3/8" (BSP) male, brass, nickel plated
										S: G 1/2" (BSP) male, brass, nickel plated
										U: G 1/8" (BSP) female, brass, nickel plated
										V: G 1/4" (BSP) female, brass, nickel plated
										W: G 3/8" (BSP) female, brass, nickel plated
										X: G 1/2" (BSP) female, brass, nickel plated
Pressure mode										
G: gage pressure ¹										
(up to 50 bar/750 psi)										
S: sealed gage										
(above 50 bar/750 psi)										
A: absolute pressure										
(from 1 bar/15 psi up to 50 bar/750 psi)										

Other pressure ranges and options are widely available. Please contact Sensortektechnics.

Sensortektechnics reserves the right to make changes to any products herein. Sensortektechnics does not assume any liability arising out of the application or use of any product or circuit described herein, neither does it convey any license under its patent rights nor the rights of others.