





REV.	DATE	DESCRIPTION
A	12/01/99	UPDATE DRAWING ADD DOUBLE BRAID
B	05/23/03	UPDATE DRAWING FORMAT / MODIFY FERRULE



- NOTES:
1. CRIMPED FERRULE  
HEX SIZE .151"
  2. CRIMPED CONTACT PIN  
SQ. CRIMP SIZE 0.7mm

**Amphenol Connex**

PART DESCRIPTION  
TNC CRIMP PLUG - DOUBLE BRAID  
(RG-174/U, 188A/U, 316/U CABLE)

NO.	DESCRIPTION	MATERIAL	FINISH	QTY	DO NOT SCALE DRAWING	APPROVALS	DATE	DWG. NO.	REV.	SIZE	SCALE
8								122375.DWG	B	A	NA
7											
6											
5	CONTACT PIN	BRASS	GOLD	1							
4	FERRULE	COPPER	NICKEL	1							
3	CONTACT PIN	PHOS. BRONZE	GOLD	1							
2	INSULATOR	DELRIIN	NATURAL	1							
1	BODY	BRASS	NICKEL	1							
	DESCRIPTION										

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [ ] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY.

UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE:

0.5 - 8mm ± 0.20mm  
8 - 30mm ± 0.40mm  
30 - 120mm ± 0.50mm

UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE:

.020 - .315 = ± 0.007"  
.315 - 1.180 = ± 0.015"  
1.180 - 4.724 = ± 0.020"

DO NOT SCALE DRAWING

APPROVALS	DATE	CAD FILE
G.R.S.	05/23/03	C:/122/122375.DWG
CHECKED		
ISSUED		
SHEET	1 OF 1	
PART NO.		122375