



Copyright FCI

D

C

B

A

TIN LEAD PART NUMBER

SHELL	A±0.38	B±0.12	C±0.10	D±0.25	E±0.07	PART NUMBER
09	30.81	24.99	16.96	16.79	10.96	D09P91C*GL00
15	39.14	33.32	25.18	25.12	19.18	D15P91C*GL00
25	53.03	47.04	39.12	38.84	33.12	D25P91C*GL00
37	69.32	63.50	55.68	55.30	49.68	D37P91C*GL00

Plating: 4 --> 200 Mating
Plating: 6 --> 500 Mating
Plating: 8 --> 1.25µ Equivalent PdNi/Au


LEAD FREE PART NUMBER

SHELL	A±0.38	B±0.12	C±0.10	D±0.25	E±0.07	PART NUMBER
09	30.81	24.99	16.96	16.79	10.96	D09P91C*GL00LF
15	39.14	33.32	25.18	25.12	19.18	D15P91C*GL00LF
25	53.03	47.04	39.12	38.84	33.12	D25P91C*GL00LF
37	69.32	63.50	55.68	55.30	49.68	D37P91C*GL00LF

Plating: 4 --> 200 Mating
Plating: 6 --> 500 Mating
Plating: 8 --> 1.25µ Equivalent PdNi/Au

rev	ecn no	dr	date
E	-	JOU	1998/03/20
F	LS05-004	MPE	2005/02/08
G	LS06-0097	LGO	2006/07/29
H	LS06-0140	LGO	2006/09/25
J	I09-0268	NG	2009-11-24
K	I11-0062	RPK	2011-04-05
-	-	-	-

PC board drilling dimensions(after plating)
(thickness ≤ 3.20±0.30mm)



GENERAL CHARACTERISTICS AND ROHS INFORMATIONS:

SEE DRAWING C01-8646-0001

European Views

www.fciconnect.com			surface ISO 1302		tolerance std ISO 406 ISO 1101		projection 		mm 	
			TOLERANCES UNLESS OTHERWISE SPECIFIED							
Dr	JARRY	1994-09-21	ANGULAR		LINEAR		0.X	±0.1	size	Scale
Eng	PESSON	1994-09-21					0.XX	±0.1	A3	2
Chr	NIRMAL GEORGE	2009-11-24	0.XX' ±2				0.XXX	±0.1	ECN	I11-0062
Appr	SUDHIR VARMA	2009-11-24	Product family				D-SUB		Spec ref -	
			title MALE CONNECTOR DELTA D STD EUROPE straight press-fit				dwg no C01-8646-0311			Rev. K
			catalog no				CUSTOMER		sheet 1 of 1	

REV F - 2006-04-17

PDM: Rev:K

STATUS: Released

Printed: Oct 11, 2011