





|                   |                   |    |                   |    |                    |                    |                    |      |                      |
|-------------------|-------------------|----|-------------------|----|--------------------|--------------------|--------------------|------|----------------------|
| 149.22<br>[5.875] | 137.16<br>[5.400] | 54 | 137.16<br>[5.400] | 54 | 288.29<br>[11.350] | 298.45<br>[11.750] | 306.07<br>[12.050] | 330  | 5533294-6            |
| 141.60<br>[5.575] | 129.54<br>[5.100] | 51 | 129.54<br>[5.100] | 51 | 273.05<br>[10.750] | 283.21<br>[11.150] | 290.83<br>[11.450] | 312  | <del>5533294-5</del> |
| 111.12<br>[4.375] | 99.06<br>[3.900]  | 39 | 99.06<br>[3.900]  | 39 | 212.09<br>[8.350]  | 222.25<br>[8.750]  | 229.87<br>[9.050]  | 240  | 5533294-1            |
| K                 | G                 | F  | E                 | D  | C                  | B                  | A                  | POSN | PART NUMBER          |

## RECOMMENDED P.C. BOARD LAYOUT

|                                                                                                   |  |                                                                                                                           |  |                                                                                                                              |  |
|---------------------------------------------------------------------------------------------------|--|---------------------------------------------------------------------------------------------------------------------------|--|------------------------------------------------------------------------------------------------------------------------------|--|
| THIS DRAWING IS A CONTROLLED DOCUMENT.                                                            |  | DWN J. POLIGNONE<br>CHK A. SHARPE<br>11MAY05<br>11MAY05                                                                   |  |  TE Connectivity                        |  |
| DIMENSIONS:<br>mm [INCHES]                                                                        |  | TOLERANCES UNLESS OTHERWISE SPECIFIED:<br>0. PLC ± —<br>1. PLC ± —<br>2. PLC ± 0.13 [.005]<br>3. PLC ± —<br>4. ANGLES ± — |  | NAME<br>ASSEMBLY, PIN, VERTICAL, HDI, 3 ROW,<br>ONE CENTER GUIDE PIN, 6.35[.250] ACTION PINS,<br>0.00076[.000030] GOLD PLATE |  |
|              |  | APVD A. SHARPE<br>PRODUCT SPEC<br>APPLICATION SPEC                                                                        |  | SIZE<br>A1                                                                                                                   |  |
| MATERIAL<br> |  | WEIGHT<br>—                                                                                                               |  | CAGE CODE<br>00779                                                                                                           |  |
| FINISH<br>   |  | CUSTOMER DRAWING                                                                                                          |  | DRAWING NO<br>C-5533294                                                                                                      |  |
|                                                                                                   |  |                                                                                                                           |  | SCALE 4:1<br>SHEET 1 of 1<br>REV 0                                                                                           |  |