


★★★★ Lightweight Cutting Tweezers

Made In Switzerland

High-Grade Carbon Steel



14A-GW ★★★

4 3/8"

Three Star Slim High Precision Cutting Tweezers .

New thinner body designed for lightweight and easy handling. Cutting capacity .010" (0,25mm) soft wire.

A:	0.375"	(9.5 mm)
B:	4.375"	(111 mm)
C:	0.210"	(5.4 mm)
D:	0.285"	(7.2 mm)
E:	80°	



14A-N ★★★

4 1/2"

Three Star Long Thin Precision Cutting Blades.

Angled Tips can be used horizontally or vertically. Cutting capacity .005" (0,12mm) soft wire.

A:	0.375"	(9.5 mm)
B:	4.500"	(115 mm)
C:	0.138"	(3.5 mm)
D:	0.492"	(12.5 mm)
E:	75°	



52-MW ★★★

4 1/2"

Three Star High Precision Micro Straight Tips.

ESD safe epoxy handle. Excellent for working in dense access areas. Cutting capacity .005" (0,12mm) soft wire.

A:	0.375"	(9.5 mm)
B:	4.500"	(115 mm)
C:	0.149"	(3.8 mm)
D:	0.276"	(5.2 mm)
E:	40°	



54-MW ★★★

4 1/4"

Three Star High Precision Micro Angled Tips.

ESD safe epoxy handle. Designed for maximum visibility when working under magnification. Cutting capacity .008" (0,2mm) soft wire.

A:	0.375"	(9.5 mm)
B:	4.250"	(108 mm)
C:	0.122"	(3.1 mm)
D:	0.303"	(7.7 mm)
E:	80°	



★★ Traditional Cutting Tweezers

15A-RW-PI ★★

4 1/2"

Fine radius face tip cutting tweezers with flush cutting blades. For use on .010" or smaller soft wire.

A:	0.393"	(10 mm)
B:	4.500"	(115 mm)
C:	0.095"	(2.5 mm)
D:	0.200"	(5.2 mm)
E:	70°	



15A-GW-PI ★★

4 1/2"

General purpose cutting tweezers for use on .010" or smaller soft wire.

A:	0.393"	(10 mm)
B:	4.500"	(115 mm)
C:	0.215"	(5.5 mm)
D:	0.375"	(9.5 mm)
E:	70°	

