




BCM1255

PRODUCT Brief



DUAL-CORE 64-BIT MIPS® PROCESSOR (NEW!)

FEATURES

- Two 64-bit MIPS® CPUs, scalable from 800 MHz–1.2 GHz
 - Quad issue in-order pipeline with dual-execute and dual-memory pipes
 - Enhanced skew pipeline enables a zero load-to-use penalty
 - 32-KB instruction cache and 32-KB data cache (ECC protected)
- Fast on-chip multiprocessor bus
 - Connects the CPUs, L2 cache, memory controller, and I/O bridges
 - Runs at half the CPU core frequency and is 256 bits wide
- On-chip L2 cache
 - 512 KB shared by two CPUs and I/O agents
 - Eight-way associative, ECC protected
 - Any way can be programmed as fast on-chip RAM
- DDR memory controller
 - Memory bandwidth as high as 100 Gbps
 - Configurable as 2x64-bit or 4x32-bit wide channels
 - Runs up to 400-MHz clock rate, 800-MHz data rate
 - Support for DDR1, DDR2, and FCRAM
- Integrated network and system I/O
 - Four Gigabit-Ethernet MACs configurable as packet FIFO interfaces
 - 64-bit PCI-X interface at 133 MHz
 - Generic I/O for direct connect to boot ROM, flash memory
 - Two SMBus serial configuration interfaces
 - PCMCIA control interface and up to 16 interrupts
 - Four UART interfaces
- On-chip debug capability
 - EJTAG
 - Bus trace unit (internal logic analyzer)
- Support for leading operating systems, including VxWorks®, Linux®, QNX®, and NetBSD
- Evaluation board platform available with samples (includes tools, firmware, and software drivers)


SUMMARY OF BENEFITS

- **Industry-leading performance**
 - 2.5 Dhystone MIPS/MHz per CPU
 - 10 Million packets per second of L3 forwarding
 - 128 Gbps on-chip bus bandwidth, with 100 Gbps memory bandwidth and 31 Gbps I/O bandwidth
- **Low-power dissipation of 13W @ 1 GHz**
- **High functional integration, reducing overall system cost**
- **Programming ease and flexibility based on MIPS64™ instruction set architecture (ISA)**
- **Software compatible with BCM1250 and BCM112x**
- **Broad tools and system software support**


APPLICATIONS


- Because of its world-class performance, power efficiency, and integration, the **BCM1255** processor is ideal for a broad variety of applications, including:
 - Enterprise-class routers and switches
 - Multifunction security platforms (VPN/SSL/IDS)
 - Compact NAS platforms
 - SAN routers/gateways/switches
 - Video servers and systems

VPN/Firewall Application



Storage System or Video Server





The **BCM1255** device is an MIPS64 processor core-based system-on-a-chip (SOC) that offers industry-leading performance, high functional integration, and low-power levels required by next-generation computing, storage, and networking applications.

The **BCM1255** is a chip multiprocessor (CMP) system consisting of two Broadcom SB-1 high-performance MIPS64 CPUs, a shared 512-KB L2 cache, a DDR memory controller, and integrated I/O. All major blocks of the processor are connected together via the ZBbus, a high-speed, split-transaction multiprocessor bus. The bus implements the standard MESI protocol to ensure coherency between the two CPUs, L2 cache, I/O agents, and memory. Four Gigabit-Ethernet MACs (10/100/1000) enable easy interfacing to LANs or control backplanes. To enable higher data rates (or in cases where Ethernet protocol processing is not required), the Gigabit-Ethernet MACs can be configured as 8-bit and/or 16-bit packet FIFOs. The **BCM1255** also integrates a 64-bit, 133-MHz PCI-X local bus for direct connection to I/O devices. Four serial ports are available for use as UARTs for console ports.

To enable low-chip count systems, the **BCM1255** also includes a configurable generic bus that allows glueless connection of a boot ROM or flash memory and simple I/O peripherals. On-chip debug, trace, and performance monitoring functions assist both hardware and software designers in debugging and tuning the system. The system can be run in either big-endian or little-endian mode.

Implementation of MIPS64 ISA

The SB-1 CPU core is a high-performance implementation of the standard MIPS64 ISA that incorporates the MIPS-3D and MIPS-MDMX application-specific extensions (ASEs). The core supports a 4-issue enhanced skew pipeline and can dispatch up to two memory and two ALU (integer, floating point, MDMX, or MIPS-3D) instructions per cycle.

Next Generation Broadband Processors

	BCM1255	BCM1280	BCM1455	BCM1480
# of CPUs	2	2	4	4
L2 Cache	512 KB	1 MB	1 MB	1 MB
DDR2 Support	Yes	Yes	Yes	Yes
# of MACs	4 GMII	4 GMII	4 GMII	4 GMII
PCI-X	1 x 64-bit	1 x 64-bit	1 x 64-bit	1 x 64-bit
# of SPI-4/HT Ports	0	3	0	3

Broadcom[®], the pulse logo, and **Connecting everything**[®] are trademarks of Broadcom Corporation and/or its subsidiaries in the United States and certain other countries. All other trademarks mentioned are the property of their respective owners.

Connecting
everything®

BROADCOM CORPORATION

16215 Alton Parkway, P.O. B
Irvine, California 92619-7013

© 2004 by BROADCOM CORPORATION. All rights reserved.

1255-PB01-R 09/30/04

The Broadcom logo consists of a red stylized 'A' shape above the word "BROADCOM" in a bold, black, sans-serif font. Below the word is a red wavy line.

Phone: 949-450-8700
Fax: 949-450-8710
E-mail: info@broadcom.com
Web: www.broadcom.com