

PPC-103T

10.4" Panel PC with Intel® Pentium® III/ Celeron® Processor



Features

- 10.4" TFT SVGA LCD
- Intel® Pentium® III and Celeron® CPU up to 850 MHz
- System memory up to 512 MB SDRAM
- One optional PCI/ISA expansion slot
- One CompactFlash® Type I and II socket (True IDE Mode)
- 10/100Base-T Ethernet
- External IDE/FDD connectors



Introduction


The Panel PC, PPC-103T, integrates a 10.4" SVGA TFT LCD display into a stylish and flame-resistant chassis with a depth of 61.5 mm (2.4"). It can support high performance Intel Celeron and Pentium III processors. The PPC-103T's high-brightness 800 x 600 SVGA LCD display, built-in 16-bit Sound Blaster® compatible audio controller, up to 512 MB SDRAM capacity and 10/100Base-T Ethernet controller provide integration capability to meet different application needs.

Specifications

Processor System		Display	10.4" SVGA TFT LCD	
		CPU	Supports Intel Pentium III and Intel Celeron processors, up to 850 MHz	
		Memory	Up to 512 MB SODIMM	
		HDD	1 x EIDE interface, 2.5" type	
		FDD	Supports 1 x external FDD connector	
		SSD	Supports 1 x CompactFlash Type I and II Socket (True IDE Mode)	
		I/O ports	- 4 x serial ports: 3 x RS-232, 1 x RS-232/422/485 - 1 x parallel port, 2 x USB - External VGA port - PS/2 mouse and keyboard - Built-in Mic-in / Line-out jacks	
			Network	10/100Base-T Ethernet interface
			Dimensions (W x H x D)	342 x 265 x 92.4 mm (13.5" x 10.4" x 3.64")
			Weight	3.5 kg (7.7 lb)
LCD Display		Display Type	10.4" SVGA TFT LCD	
		Max. Resolution/Colors	800 x 600 @ 256 K	
		Pixel Pitch (mm)	0.264 x 0.264	
		Luminance (cd/m ²)	230	
		Viewing Angle	60/60/35/65 (L/R/U/D)	
		Temperature	0 ~ 50° C	
		VR Controls	Yes	
		Simultaneous Mode	Yes	
		LCD MTBF	50,000 hrs	
Power Supply		Contrast	500 : 1	
		AC model	Output Rating	60 W
			Input Voltage	100 ~ 240 V _{AC} @ 50/60 Hz, autoranging
			Output Voltage	+5 V @ 5 A, +12 V @ 3 A
		DC model	Output Rating	75 W
			Input Voltage	18 V _{DC} ~ 36 V _{DC} , typical 24 V _{DC} , 4.2 A max
			Output Voltage	+5 V @ 8 A, +12 V @ 2.5 A
		DC model (optional)	Output Rating	65 W
			Input Voltage	9.5 V _{DC} ~ 18 V _{DC} , typical 12 V _{DC} , 6.8 A max
		Output Voltage	+5 V @ 7 A, +12 V @ 2 A	
Touchscreen (optional)		Type	Analog resistive	Infrared
		Resolution	Continuous	4096 x 4096
		Light Transmission	75%	91%
		Controller	RS-232 interface (COM 4)	RS-232 interface (COM4)
		Power Consumption	+5 V @ 200 mA	+5 V @ 150 mA
		Software Driver	Supports both DOS and Windows	
		Durability	10 million touches	100,000 hrs

Dimensions

Unit: mm (inch)




Environmental Specifications	Operating Temperature	0 ~ 45° C (32 ~ 113° F)
	Relative Humidity	10 ~ 95% @ 40° C (non-condensing)
	Shock (Operating)	10 G peak acceleration (11 ms. duration)
	EMC	CE, FCC Class B, VCCI, CCC
	Safety	UL, CE
	Front Panel Protection	IP 65/NEMA 4 compliant

Ordering Information

Part No.	Description
PPC-103T-BBARE	Bare BOM: PPC-103T-BBARE Intel Pentium III, Intel Celeron Panel PC with 10.4" TFT SVGA LCD display
PPC-103DC-BBARE	Bare BOM: PPC-103DC-BBARE PPC-103T with 24VDC power supply (12 VDC is optional)
PPC-103T-BBAR-TE	Bare BOM: PPC-103T-BBAR-TE PPC-103T with resistive touchscreen
PPC-103DC-BBA-TE	Bare BOM: PPC-103DC-BBA-TE PPC-103T-RT with 24VDC power supply (12 VDC is optional)
PPC-100 STAND	Stand kit for PPC-100/103 series
PPC-100 SWINARM	Swingarm kit for PPC-100/103 series
PPC-100 WALL-MT	Wall mount kit for PPC-100/103 series
PPC-EXP-103	PCI/ISA expansion kit for PPC-103
1702002600	POWER Cable UL/CSA(USA) 180D 125V10A 1.83M

* Infrared touchscreen with sunlight readable panel can be ordered via the OEM process, and both items can be ordered separately

Fully-Integrated I/O



Applications

- Point-of-information/Point-of-sales terminals
- Interactive kiosks
- Entertainment terminals
- Banking/Office automation
- Production process control
- Factory automation systems