

NOTES :

1. MATERIAL:-



- PIN:- (0.65)/.0255 SQ. BRASS WIRE.
- HOUSING:- 15% GLASS FILLED POLYESTER
- UL 94 V-0 COLOUR BLACK

2. FOR PLATING VERSIONS AND VOID VERSIONS SEE SHEET 2.



3. MEASUREMENT POINT FOR MINIMUM PLATING THICKNESS.

4. FOR PRODUCT SPEC SEE PS-99020-0001

5. RECOMMENDED PCB THICKNESS: 1.60mm



SECTION K-K




RECOMMENDED P.C. BOARD
HOLE PATTERN


CKT	DIM A	DIM B	DIM C
6	(5.08)/.200	(9.96)/.392	(8.12)/.320
8	(7.62)/.300	(12.50)/.492	(10.66)/.420
10	(10.16)/.400	(15.04)/.592	(13.20)/.520
12	(12.70)/.500	(17.58)/.692	(15.74)/.620
14	(15.24)/.600	(20.12)/.792	(18.28)/.720
16	(17.78)/.700	(22.66)/.892	(20.82)/.820
18	(20.32)/.800	(25.20)/.992	(23.36)/.920
20	(22.86)/.900	(27.74)/.1092	(25.90)/.1020
22	(25.40)/.1000	(30.28)/.1192	(28.44)/.1120
24	(27.94)/.1100	(32.82)/.1292	(30.98)/.1220
26	(30.48)/.1200	(35.36)/.1392	(33.52)/.1320
28	(33.02)/.1300	(37.90)/.1492	(36.06)/.1420
30	(35.56)/.1400	(40.44)/.1592	(38.60)/.1520
32	(38.10)/.1500	(42.98)/.1692	(41.15)/.1620
34	(40.64)/.1600	(45.52)/.1792	(43.68)/.1720
36	(43.18)/.1700	(48.06)/.1892	(46.22)/.1820
38	(45.72)/.1800	(50.60)/.1992	(48.76)/.1920
40	(48.26)/.1900	(53.14)/.2092	(51.30)/.2020
42	(50.80)/.2000	(55.68)/.2192	(53.84)/.2120
44	(53.34)/.2100	(58.22)/.2292	(56.38)/.2220
46	(55.88)/.2200	(60.76)/.2392	(58.92)/.2320
48	(58.42)/.2300	(63.30)/.2492	(61.46)/.2420
50	(60.96)/.2400	(65.84)/.2592	(64.00)/.2520
52	(63.50)/.2500	(68.38)/.2692	(66.54)/.2620
54	(66.04)/.2600	(70.92)/.2792	(69.08)/.2720
56	(68.58)/.2700	(73.46)/.2892	(71.62)/.2820
58	(71.12)/.2800	(76.00)/.2992	(74.16)/.2920
60	(73.66)/.2900	(78.54)/.3092	(76.70)/.3020
62	(76.20)/.3000	(81.08)/.3192	(79.24)/.3120
64	(78.74)/.3100	(83.62)/.3292	(81.78)/.3220
66	(81.28)/.3200	(86.16)/.3392	(84.32)/.3320
68	(83.82)/.3300	(88.70)/.3492	(86.86)/.3420

ADD DATUMS		QUALITY SYMBOLS		GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE		SCALE		DESIGN UNITS		THIRD ANGLE PROJECTION	
EC NO:	REV	DESCRIPTION	REV	mm	INCH	MM/IN	NTS	INCH	NTS	INCH	NTS	INCH	NTS
S2015-0152	CA2	DRWN:ATSEE		4 PLACES	± ---	± ---	DRAWN BY	DATE	KS	1988/08/23	TITLE	C-GRID III DUAL ROW STRAIGHT SHROUDED HEADER MOLEX INCORPORATED	
2014/08/18		CHKD:FANNYONG		3 PLACES	± ---	± .004	CHECKED BY	DATE	ATSEE	2010/02/11			
2014/08/19		APPR:LBLEE		2 PLACES	± 0.10	± ---	APPROVED BY	DATE	MLONG	2010/02/19			
				1 PLACE	± ---	± ---	MATERIAL NO.						
				ANGULAR ±1/2°		SEE TABLE		DOCUMENT NO.		SDA-90130		SHEET NO.	
				DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION						1 OF 4	

		10		9		8		7		6		5		4		3		2		1		
VERSION FULLY LOADED																						
F	NO OF CKTS	HSG CKT SIZE	PART NUMBER																			
			PLATING TYPE A	PLATING TYPE E	PLATING TYPE F	PLATING TYPE G																
	6	6	90130-X106	90130-X206	90130-X306	90130-X406																
	8	8	X108	X208	X308	X408																
	10	10	X110	X210	X310	X410																
	12	12	X112	X212	X312	X412																
	14	14	X114	X214	X314	X414																
	16	16	X116	X216	X316	X416																
E	18	18	X118	X218	X318	X418																
	20	20	X120	X220	X320	X420																
	22	22	X122	X222	X322	X422																
	24	24	X124	X224	X324	X424																
	26	26	X126	X226	X326	X426																
	28	28	X128	X228	X328	X428																
	30	30	X130	X230	X330	X430																
	32	32	X132	X232	X332	X432																
D	34	34	X134	X234	X334	X434																
	36	36	X136	X236	X336	X436																
	38	38	X138	X238	X338	X438																
	40	40	X140	X240	X340	X440																
	42	42	X142	X242	X342	X442																
	44	44	X144	X244	X344	X444																
	46	46	X146	X246	X346	X446																
C	48	48	X148	X248	X348	X448																
	50	50	X150	X250	X350	X450																
	52	52	X152	X252	X352	X452																
	54	54	X154	X254	X354	X454																
	56	56	X156	X256	X356	X456																
	58	58	X158	X258	X358	X458																
	60	60	X160	X260	X360	X460																
	62	62	X162	X262	X362	X462																
B	64	64	X164	X264	X364	X464																
	66	66	X166	X266	X366	X466																
	68	68	90130-X168	90130-X268	90130-X368	90130-X468																
A					ADD DATUMS		EC NO: S2015-0152		2014/08/18		2014/08/18		2014/08/19		2014/08/19		2014/08/19		2014/08/19		2014/08/19	
					DRWN:ATSEE		2014/08/18		2014/08/18		2014/08/18		2014/08/18		2014/08/18		2014/08/18		2014/08/18		2014/08/18	
					CHKD:FANNY WONG		2014/08/18		2014/08/18		2014/08/18		2014/08/18		2014/08/18		2014/08/18		2014/08/18		2014/08/18	
					APPR:BLEE		2014/08/19		2014/08/19		2014/08/19		2014/08/19		2014/08/19		2014/08/19		2014/08/19		2014/08/19	
					REV		DESCRIPTION		QUALITY SYMBOLS		GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE		SCALE		DESIGN UNITS		THIRD ANGLE PROJECTION			



VERSION FULLY LOADED



NOTES :


1. MATERIAL:-
- PIN:- (.065)/.0255 SQ. BRASS WIRE.
- HOUSING:- 15% GLASS FILLED POLYESTER
- UL 94 V-0 COLOUR BLACK

2. FOR PLATING VERSIONS AND VOID VERSIONS
SEE SHEET 2.


△ MEASUREMENT POINT FOR MINIMUM PLATING THICKNESS.

4. FOR PRODUCT SPEC SEE PS-99020-0001

5. RECOMMENDED PCB THICKNESS: 1.60mm



RECOMMENDED P.C. BOARD
HOLE PATTERN



SECTION K-K

CKT	DIM A	DIM B	DIM C
6	(5.08)/ .200	(9.96)/ .392	(8.12)/ .320
8	(7.62)/ .300	(12.50)/ .492	(10.66)/ .420
10	(10.16)/ .400	(15.04)/ .592	(13.20)/ .520
12	(12.70)/ .500	(17.58)/ .692	(15.74)/ .620
14	(15.24)/ .600	(20.12)/ .792	(18.28)/ .720
16	(17.78)/ .700	(22.66)/ .892	(20.82)/ .820
18	(20.32)/ .800	(25.20)/ .992	(23.36)/ .920
20	(22.86)/ .900	(27.74)/ 1.092	(25.90)/ 1.020
22	(25.40)/ 1.000	(30.28)/ 1.192	(28.44)/ 1.120
24	(27.94)/ 1.100	(32.82)/ 1.292	(30.98)/ 1.220
26	(30.48)/ 1.200	(35.36)/ 1.392	(33.52)/ 1.320
28	(33.02)/ 1.300	(37.90)/ 1.492	(36.06)/ 1.420
30	(35.56)/ 1.400	(40.44)/ 1.592	(38.60)/ 1.520
32	(38.10)/ 1.500	(42.98)/ 1.692	(41.15)/ 1.620
34	(40.64)/ 1.600	(45.52)/ 1.792	(43.68)/ 1.720
36	(43.18)/ 1.700	(48.06)/ 1.892	(46.22)/ 1.820
38	(45.72)/ 1.800	(50.60)/ 1.992	(48.76)/ 1.920
40	(48.26)/ 1.900	(53.14)/ 2.092	(51.30)/ 2.020
42	(50.80)/ 2.000	(55.68)/ 2.192	(53.84)/ 2.120
44	(53.34)/ 2.100	(58.22)/ 2.292	(56.38)/ 2.220
46	(55.88)/ 2.200	(60.76)/ 2.392	(58.92)/ 2.320
48	(58.42)/ 2.300	(63.30)/ 2.492	(61.46)/ 2.420
50	(60.96)/ 2.400	(65.84)/ 2.592	(64.00)/ 2.520
52	(63.50)/ 2.500	(68.38)/ 2.692	(66.54)/ 2.620
54	(66.04)/ 2.600	(70.92)/ 2.792	(69.08)/ 2.720
56	(68.58)/ 2.700	(73.46)/ 2.892	(71.62)/ 2.820
58	(71.12)/ 2.800	(76.00)/ 2.992	(74.16)/ 2.920
60	(73.66)/ 2.900	(78.54)/ 3.092	(76.70)/ 3.020
62	(76.20)/ 3.000	(81.08)/ 3.192	(79.24)/ 3.120
64	(78.74)/ 3.100	(83.62)/ 3.292	(81.78)/ 3.220
66	(81.28)/ 3.200	(86.16)/ 3.392	(84.32)/ 3.320
68	(83.82)/ 3.300	(88.70)/ 3.492	(86.86)/ 3.420

ADD DATUMS		QUALITY SYMBOLS		GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE		SCALE		DESIGN UNITS		THIRD ANGLE PROJECTION	
EC NO:	REV	DESCRIPTION	SYMBOL	mm	INCH	MM/IN	DATE	NTS	INCH	INCH	INCH	INCH	INCH
S2015-0152	1	DRINKATSEE	F _A =0	4 PLACES	± ---	± ---	1988/08/23	KS	DATE	DATE	DATE	DATE	DATE
2014/08/18	2	CHYD-FANNYONG	F _G =0	3 PLACES	± ---	± .004	2010/02/11	ATSEE	DATE	DATE	DATE	DATE	DATE
2014/08/19	3	APPR:BLEE	F _P =0	2 PLACES	± 0.10	± ---	2010/02/19	MLONG	DATE	DATE	DATE	DATE	DATE
				1 PLACE	± ---	± ---							
				ANGULAR ± 1/2°									
				DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS									
				SEE TABLE									
				THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION									

tb_frame_A3_P_AM_T
Rev. F 2009/06/18