


3 Amp Schottky Rectifiers SK32B — SK310B



Dim.	Inches		Millimeter		Notes
	Minimum	Maximum	Minimum	Maximum	
A	.068	.087	1.73	2.21	
B	.157	.177	3.99	4.50	
C	.130	.155	3.30	3.94	
D	.194	.228	4.93	5.79	
E	.078	.115	1.98	2.92	
F	.030	.060	.760	1.52	

SMB
DO-214AA

Microsemi
Catalog Number

Working Peak
Reverse Voltage

Repetitive Peak
Reverse Voltage

SK32B
SK33B
SK34B
SK36B
SK38B
SK310B

20V
30V
40V
60V
80V
100V

20V
30V
40V
60V
80V
100V

- Schottky Barrier Rectifier
- Low Forward Voltage Drop
- 20-100 Volts
- Low switching losses
- Round lead design

Electrical Characteristics

Average forward current	$I_F(AV)$	3.0A	$T_J = 120^\circ C$
Maximum surge current	I_{FSM}	100A	8.3ms half-sine
Max repetitive reverse current	$I_{R(OV)}$	2A	$f = 1KHZ, 25^\circ C, 1\mu s$ square wave
Max peak forward voltage (SK32B-SK34B)	V_{FM}	.50V	$I_{FM} = 3.0A; T_J = 25^\circ C^*$
Max peak forward voltage (SK36B)	V_{FM}	.75V	$I_{FM} = 3.0A; T_J = 25^\circ C^*$
Max peak forward voltage (SK38B-SK310B)	V_{FM}	.85V	$I_{FM} = 3.0A; T_J = 25^\circ C^*$
Max peak reverse current	I_{RM}	.5mA	$V_{RRM}, T_J = 25^\circ C$
Max peak reverse current	I_{RM}	20mA	$V_{RRM}, T_J = 100^\circ C^*$
Typical junction capacitance	C_J	250pF	$V_R = 5.0V, T_J = 25^\circ C$

*Pulse test: Pulse width 300 μsec , Duty cycle 2%

Thermal and Mechanical Characteristics

Storage temperature range	T_{STG}	$-55^\circ C$ to $150^\circ C$
Operating junction temp range	T_J	$-55^\circ C$ to $125^\circ C$
Maximum thermal resistance	$R_{\theta JC}$	$10^\circ C/W$



8700 East Thomas Road, P.O. Box 1390
Scottsdale, AZ 85252
PH: (480) 941-6300
FAX: (480) 947-1503
www.microsemi.com

05-30-07 Rev. 2

SK32B — SK310B

Figure 1
Typical Forward Characteristics




Figure 2
Typical Reverse Characteristics @ 100°C




Figure 3
Typical Junction Capacitance

