





LE Series

microSDHC Memory Card, Consumer Plus MLC Model

■ Product Outline

LE series are microSDHC memory cards adopting built-in consumer type MLC NAND flash memory. They are formatted complying with SD card specification.

■ Product Specification (specifications and appearances may be changed without notice.)

		4GB	8GB	16GB	32GB
Appearance					
Part Number		RP-SMLE04DA1	RP-SMLE08DA1	RP-SMLE16DA1	RP-SMLE32DA1
Capacity	Available user data area capacity *1)	3,971,973,120 byte	7,960,756,224 byte	16,013,819,904 byte	32,098,975,744 byte
Compliant Specification	SD Physical Specification	Ver. 4.20			
	SD speed class	CLASS10			
	UHS speed grade	I U1		I U3	
	Speed mode	Default Speed Mode, High Speed Mode, SDR12/SDR25/SDR50/DDR50/SDR104			
Backside mark	Control Code	---			
Read/Write Performance (up to)	Read	90MB/s (SDR104 mode)	90MB/s (SDR104 mode)	95MB/s (SDR104 mode)	95MB/s (SDR104 mode)
	Write	25MB/s (SDR104 mode)	25MB/s (SDR104 mode)	45MB/s (SDR104 mode)	90MB/s (SDR104 mode)
Absolute Maximum Ratings	Supply Voltage	Min : -0.3 V ; Max : +4.6 V			
	Input Voltage	Min : -0.3 V ; Max : VDD +0.3 V			
	Output Voltage	Min : -0.3 V ; Max : VDD +0.3 V			
	Output Current	Min : -24 mA ; Max : +24 mA			
Environmental Specification	Operating Temperature	-25 degree C to +85 degree C			
	Storage Temperature	-40 degree C to +85 degree C			
	Humidity	5 % RH to 95 % RH			
	Vibration	15 Gp-p			
	Shock	1,000 G			
	Mating Cycles	10,000 cycles			

*1) Free user area capacity after formatted.

Absolute Maximum Ratings are the values of limitation, which do not damage the card. So those values do not define the operational range.


Products comply with EU RoHS directives.

■Marking Specification (example; 4GB)



“4GB”
“MADE IN TAIWAN”

Card Capacity
Country of origin



“00YM0000000”
Y
M
“0000000000”,
“0000000000000000”

Serial Number
Last digit of Manufacture year
Manufacture month
(January->A, February->B,)
Internal control code
Internal control code

■ System Reliability

- a. Error detect and corrective function
- b. Static wear leveling
- c. Bad block management

■ Notice and Caution

If you think about the usage for which special quality or reliability of the products is needed and failure or malfunction of the products may directly threaten life or injury for the special usage (aeronautic or cosmic usage, military usage, combustion machine, life support applications or safety applications), please counsel with our contacts in advance.

Write frequency and storage temperature will affect data retention time. Please make a backup for important data.

■ Warranty

If the product cannot be used because of failure which is determined as defect in design or in production of the product, it is replaced by same product or equivalent one within 12 months from the delivery date of product.