



## IN-WALL SPEAKER WIRE

### Applications:

Audio/Stereo/Sound System Conductivity. Intercom Systems. Public Address Systems.

### Features:

Stranded Bare Copper Conductors PVC Insulated Conductors. Shielded For Better Performance. Flame Retardant Jacket.



### In-Wall Speaker Wire

| Part Number  | Color | Length | No. of Conductor | AWG | Conductor Material (Stranding)  | Insulation Material | Insulation ID/ Nominal Thickness | Shield        | Material (Nominal Thickness) | Cable O.D. |
|--------------|-------|--------|------------------|-----|---------------------------------|---------------------|----------------------------------|---------------|------------------------------|------------|
| 14-1214-2Q89 | Gray  | 1000'  | 2                | 14  | Stranded Bare Copper (19/0.36)  | SR-PVC              | 2.4/0.225mm                      | Aluminum/Foil | PVC (0.50mm)                 | 5.7mm      |
| 14-1216-2F89 | Gray  | 1000'  | 2                | 16  | Stranded Bare Copper (26/0.254) | SR-PVC              | 2.0/0.225mm                      | Aluminum/Foil | PVC (0.50mm)                 | 5mm        |
| 14-1216-4F89 | Gray  | 1000'  | 4                | 16  | Stranded Bare Copper (19/0.36)  | SR-PVC              | 2.0/0.225mm                      | Aluminum/Foil | PVC (0.50mm)                 | 6mm        |
| 14-1216-4F25 | Gray  | 25'    | 4                | 16  | Stranded Bare Copper (19/0.36)  | SR-PVC              | 2.0/0.225mm                      | Aluminum/Foil | PVC (0.50mm)                 | 6mm        |
| 14-1216-4F1C | Gray  | 100'   | 4                | 16  | Stranded Bare Copper (19/0.36)  | SR-PVC              | 2.0/0.225mm                      | Aluminum/Foil | PVC (0.50mm)                 | 6mm        |

- Temperature Rating: 80°C
- Voltage Rating: 300V
- UL Flammability Rating: VW-1
- Nom.= Nominal
- AWM 2547 (AWM= Appliance Wiring Material)

## COMPONENT SPEAKER WIRE

### Applications:

Low capacitance cable for use in high definition speaker systems. Rope lay designed to increase the conductive surface, reduce "skin effect", and maximum flexibility. Low capacitance, resistance, and inductance of these cables transfer music signals from amplifier to speakers with high clarity and definition.



### Oxygen Free Power Flex™ (10 gauge 2-Conductor)

#### Specifications:

Oxygen Free Copper

Conductor AWG: 10 gauge

Stranding: 413/36

Insulation Nominal Wall Thickness: .070

Voltage: 300V

Temperature Rating: -20°C to + 60°C

Construction: Bare Oxygen Free Copper Conductors; Flexible PVC Insulation and Rope Lay; Surface Print for Identification & Polarity

Nominal O.D.: .270 x .540

### Component Speaker Wire 10 AWG

| Part No.    | Color | Length  | Packaging |
|-------------|-------|---------|-----------|
| 14-210-9H43 | Clear | 100 ft. | Spool     |
| 14-210-9H53 | Clear | 250 ft. | Spool     |
| 14-210-9H63 | Clear | 500 ft. | Spool     |
| 30-581      | Clear | 25 ft.  | Hank      |

### Oxygen Free Power Flex™ (12 gauge 2-Conductor)

#### Specifications:

Oxygen Free Copper

Conductor AWG: 12 gauge

Stranding: 259/36

Insulation Nominal Wall Thickness: .055

Voltage: 300V

Temperature Rating: -20°C to + 60°C

Construction: Bare Oxygen Free Copper Conductors; Extra Flexible PVC Insulation and Rope Lay; Surface Print for Identification & Polarity


Nominal O.D.: .205 x .415

### Component Speaker Wire 12 AWG

| Part No.    | Color | Length  | Packaging |
|-------------|-------|---------|-----------|
| 14-212-9H43 | Clear | 100 ft. | Spool     |
| 14-212-9H53 | Clear | 250 ft. | Spool     |
| 14-212-9H63 | Clear | 500 ft. | Spool     |
| 30-583      | Clear | 25 ft.  | Hank      |

## COMPONENT SPEAKER WIRE (Cont.)

### 2 Conductor Parallel Zip Cord



Two conductor Parallel Zip Cord Wire for loudspeaker connection and other low voltage applications such as alarm, signal and telephone circuits. Temperature range:-20° to+60°. White Identification polarity stripe.

#### 24 Gauge (2-Conductor)

##### Specifications:

Oxygen Free Copper  
 Conductor AWG: 24 gauge  
 Stranding: 7/32  
 Insulation Nominal Wall Thickness: .016"  
 Voltage: 300V  
 Temperature Rating: -20°C to + 60°C  
 Construction: Bare Copper Conductors; Clear PVC;  
 1 Conductor Identified for Polarity  
 Nominal O.D.: .055" x .110"

##### Applications:

Automotive Speaker Wire, Juke Boxes,  
 Stereo Speaker Wire

| Part No.    | Color | Length   | Packaging |
|-------------|-------|----------|-----------|
| 14-224-2B13 | Clear | 25 ft.   | Spool     |
| 14-224-2B23 | Clear | 50 ft.   | Spool     |
| 14-224-2B43 | Clear | 100 ft.  | Spool     |
| 14-224-2B63 | Clear | 500 ft.  | Spool     |
| 14-224-2B83 | Clear | 1000 ft. | Spool     |
| 30-586      | Clear | 50 ft.   | Hank      |
| 30-588      | Clear | 100 ft.  | Hank      |

#### 22 Gauge (2-Conductor)

##### Specifications:

Oxygen Free Copper  
 Conductor AWG: 22 gauge  
 Stranding: 7/30  
 Insulation Nominal Wall Thickness: .020"  
 Voltage: 300V  
 Temperature Rating: -20°C to + 60°C  
 Construction: Bare Copper Conductors; Clear PVC;  
 1 Conductor Identified for Polarity  
 Nominal O.D.: .070" x .140"

##### Applications:

Automotive Speaker Wire, Juke Boxes,  
 Stereo Speaker Wire

| Part No.    | Color | Length   | Packaging |
|-------------|-------|----------|-----------|
| 14-222-2C13 | Clear | 25 ft.   | Spool     |
| 14-222-2C23 | Clear | 50 ft.   | Spool     |
| 14-222-2C43 | Clear | 100 ft.  | Spool     |
| 14-222-2C63 | Clear | 500 ft.  | Spool     |
| 14-222-2C83 | Clear | 1000 ft. | Spool     |

#### 20 Gauge (2-Conductor)

##### Specifications:

Oxygen Free Copper  
 Conductor AWG: 20 gauge  
 Stranding: 7/28  
 Insulation Nominal Wall Thickness: .025"  
 Voltage: 300V  
 Temperature Rating: -20°C to + 60°C  
 Construction: Bare Copper Conductors; Clear PVC;  
 1 Conductor Identified for Polarity  
 Nominal O.D.: .085" x .170"

##### Applications:

Automotive Speaker Wire, Juke Boxes,  
 Stereo Speaker Wire

| Part No.    | Color | Length   | Packaging |
|-------------|-------|----------|-----------|
| 14-220-2D13 | Clear | 25 ft.   | Spool     |
| 14-220-2D23 | Clear | 50 ft.   | Spool     |
| 14-220-2D63 | Clear | 500 ft.  | Spool     |
| 14-220-2D83 | Clear | 1000 ft. | Spool     |
| 30-553      | Clear | 50 ft.   | Hank      |

#### 18 Gauge (2-Conductor)

##### Specifications:

Oxygen Free Copper  
 Conductor AWG: 18 gauge  
 Stranding: 16/30  
 Insulation Nominal Wall Thickness: .025"  
 Voltage: 300V  
 Temperature Rating: -20°C to + 60°C  
 Construction: Bare Copper Conductors; Clear PVC;  
 1 Conductor Identified for Polarity  
 Nominal O.D.: .100" x .200"

##### Applications:

Automotive Speaker Wire, Juke Boxes,  
 Stereo Speaker Wire

| Part No.    | Color | Length   | Packaging |
|-------------|-------|----------|-----------|
| 14-218-2E13 | Clear | 25 ft.   | Spool     |
| 14-218-2E23 | Clear | 50 ft.   | Spool     |
| 14-218-2E43 | Clear | 100 ft.  | Spool     |
| 14-218-2E53 | Clear | 250 ft.  | Spool     |
| 14-218-2E63 | Clear | 500 ft.  | Spool     |
| 14-218-2E83 | Clear | 1000 ft. | Spool     |
| 30-584      | Clear | 50 ft.   | Hank      |
| 30-554      | Clear | 100 ft.  | Hank      |

#### 16 Gauge (2-Conductor)

##### Specifications:

Oxygen Free Copper  
 Conductor AWG: 16 gauge  
 Stranding: 19/29  
 Insulation Nominal Wall Thickness: .025"  
 Voltage: 300V  
 Temperature Rating: -20°C to + 60°C  
 Construction: Bare Copper Conductors; Clear PVC;  
 1 Conductor Identified for Polarity  
 Nominal O.D.: .105" x .205"

##### Applications:

Automotive Speaker Wire, Juke Boxes,  
 Stereo Speaker Wire

| Part No.    | Color | Length   | Packaging |
|-------------|-------|----------|-----------|
| 14-216-2F13 | Clear | 25 ft.   | Spool     |
| 14-216-2F23 | Clear | 50 ft.   | Spool     |
| 14-216-2F43 | Clear | 100 ft.  | Spool     |
| 14-216-2F53 | Clear | 250 ft.  | Spool     |
| 14-216-2F63 | Clear | 500 ft.  | Spool     |
| 14-216-2F83 | Clear | 1000 ft. | Spool     |

#### 14 Gauge (2-Conductor)

##### Specifications:

Oxygen Free Copper  
 Conductor AWG: 14 gauge  
 Stranding: 19/27  
 Insulation Nominal Wall Thickness: .025"  
 Voltage: 300V  
 Temperature Rating: -20°C to + 60°C  
 Construction: Bare Copper Conductors; Clear PVC;  
 1 Conductor Identified for Polarity  
 Nominal O.D.: .120" x .240"

##### Applications:

Automotive Speaker Wire, Juke Boxes,  
 Stereo Speaker Wire

| Part No.    | Color | Length  | Packaging |
|-------------|-------|---------|-----------|
| 14-214-2Q23 | Clear | 50 ft.  | Spool     |
| 14-214-2Q43 | Clear | 100 ft. | Spool     |
| 14-214-2Q63 | Clear | 500 ft. | Spool     |